



Product: [8780](#)

Audio Cable, #16-1pr, TC, O/A Shield, CM

Product Description
16 AWG stranded (19x29) tinned copper conductors, PVC insulation, twisted pair, tinned copper spiral wrapped shield (85% coverage), PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

Physical Characteristics (Overall)

Conductor				
AWG	Stranding	Material	Nominal Diameter	No. of Pairs
16	19x29	TC - Tinned Copper	0.059 in	1
Conductor Count:			2	
Total Number of Pairs:			1	

Insulation		
Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.105 in	0.023 in

Color Chart	
Color	
Black and White	

Outer Shield Material		
Type	Material	Coverage [%]
Spiral Serve / Screen	Tinned Copper (TC)	85%

Outer Jacket Material		
Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.28 in	0.030 in

Electrical Characteristics

Conductor DCR		
Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Outer Shield DCR
4.75 Ohm/1000ft	4.75 Ohm/1000ft	19 Ohm/1000ft

Capacitance	
Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
57 pF/ft	98 pF/ft

Inductance	
Nominal Inductance	
0.18 µH/ft	

Impedance

Nominal Characteristic Impedance
37 Ohm

Current

Max. Recommended Current [A]
7.1 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	60°C
Operating Temp Range:	-20°C To +60°C

Mechanical Characteristics

Bulk Cable Weight:	42 lbs/1000ft
Max. Pull Tension:	61 lbs
Min Bend Radius/Minor Axis:	3 in

Standards

NEC/(UL) Compliance:	CMG
CEC/C(UL) Compliance:	CMG

Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

CSA Flammability:	FT4
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
8780 060500	Chrome	Reel	500 ft	612825216322
8780 0601000	Chrome	Reel	1,000 ft	612825216315
8780 060U1000	Chrome	UnReel	1,000 ft	612825216339
8780 0605000	Chrome	Reel	5,000 ft	612825216292

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.249 Revision Date: 08-25-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[8780 060500](#) [8780 0601000](#) [8780 060U1000](#)