





| | | | |
|----------|-----------------|----------------------|------------------------|
| PAGE 1/2 | ISSUE 27-08-20C | SERIES ATTENUATOR | PART NUMBER R413305000 |
|----------|-----------------|----------------------|------------------------|



Scale 1:1

All dimensions are in mm. Tolerances according ISO 2768 m-H



| COMPONENTS | MATERIALS | PLATING (µm) |
|-----------------------|------------------|-----------------------|
| Body | STAINLESS STEEL | PASSIVATED |
| Male center contact | BERYLLIUM COPPER | GOLD 1.3 OVER NICKEL2 |
| Female center contact | BERYLLIUM COPPER | GOLD 1.3 OVER NICKEL2 |
| Outer contact | STAINLESS STEEL | PASSIVATED |
| Insulator | - | |
| Gasket | SILICONE RUBBER | |
| Substrate | ALUMINA | |
| Resistor | THIN FILM | |
| Others parts | | |

PAGE 2/2

ISSUE **27-08-20C**

SERIES
ATTENUATOR

PART NUMBER **R413305000**

ELECTRICAL CHARACTERISTICS

| | |
|----------------------|------------------------|
| Frequency (GHz) | DC - 40 |
| V.S.W.R (\leq) | 1.60 (1.4 typ.) |
| Deviation(\pm dB) | 0.8 |


| | | |
|------------------------------------|----------------|-----------------------|
| Operating Frequency Range | DC - 40 | GHz |
| Impedance | 50 | Ω |
| Nominal Attenuation | 5 | dB |
| Peak power at 25°C (1 μ s, 1%) | 100 | W |
| Average power at 25°C | 2 | W (Free Air Cooled) |
| | | W (Conduction Cooled) |

MECHANICAL CHARACTERISTICS

| | | | |
|------------|----------------|--------------------|--------------------|
| Connectors | SMA 2.9 | Male Female | MIL-C 39012 |
| Weight | 6,65 | g | |

ENVIRONMENTAL CHARACTERISTICS

| | | |
|-----------------------------|-----------------|----|
| Operating temperature range | -55/+125 | °C |
| Storage temperature range | -55/+125 | °C |



SPECIFICATION

OTHER CHARACTERISTICS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[R413305000](#)