



Product: [89740](#)

Electronic, 2 C #18 Str TC, FEP Ins, FEP Jkt, CMP

Request Sample

Product Description

High Temperature Electronic, 2 Conductor 18AWG (19x30) Tinned Copper, FEP Insulation, FEP Outer Jacket, CMP

Technical Specifications

Product Overview

Suitable Applications:	extreme high/low temperature environments; chemical resistant; outdoor and burial applications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; voice communications; panel wiring
------------------------	---

Construction Details

Conductor				
Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	18 AWG	19x30	TC - Tinned Copper

Insulation				
Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	FEP - Fluorinated Ethylene Propylene	0.007 in (0.18 mm)	0.057 in (1.4 mm)	Black & Red

Outer Jacket			
Material	Nom. Thickness	Nom. Diameter	
FEP - Fluorinated Ethylene Propylene	0.015 in (0.38 mm)	0.144 in (3.66 mm)	

Overall Cable Diameter (Nominal):	0.144 in (3.66 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals				
Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Characteristic Impedence	Max. Current
Pair(s)	5.5 Ohm/1000ft	20 pF/ft (66 pF/m)	72 Ohm	5.4 Amps per Conductor at 25°C

Voltage
UL Voltage Rating
300 V (CMP), 150 V (CL3P)

Mechanical Characteristics

Temperature	
UL Temperature	Operating
150°C	-70°C to +200°C

Bend Radius	
Stationary Min.	Installation Min.
1.3 in (33 mm)	1.3 in (33 mm)

Max. Pull Tension:	49 lbs (22 kg)
Bulk Cable Weight:	15 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	NFPA 262 (UL 910), FT6, IEC 60332-1-2
NEC / UL Compliance:	Article 725, Article 800
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	9740

Product Notes

Notes:	For use in indoor plenum environments but also suitable for outdoor and underground applications. Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.
--------	---

History

Update and Revision:	Revision Number: 0.510 Revision Date: 02-15-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
89740 002100	Red	Reel	100 ft	612825221227	C
89740 002500	Red	Reel	500 ft	612825221258	C
89740 0021000	Red	Reel	1,000 ft	612825221234	C
89740 0023000	Red	Reel	3,000 ft	612825221241	C Z
89740 0025000	Red	Reel	5,000 ft	612825221265	C Z

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[89740 002100](#) [89740 0025000](#) [89740 0023000](#)