



Product: [9192](#)

Video Triax, RG11, #15 Stranded, CL2X



Product Description

15 AWG stranded (19x27) .064" bare copper conductor, foam HDPE insulation, bare copper braid shields (90% and 80% coverage), PVC jacket (polyethylene insulation between braids).

Technical Specifications

Physical Characteristics (Overall)

Conductor				
AWG	Stranding	Material	Nominal Diameter	No. of Coax
15	19x27	BC - Bare Copper	0.064 in	1
Conductor Count:			1	

Insulation	
Material	Nominal Diameter
PE - Polyethylene (Foam)	0.312 in
Table Notes: Gas Injected	

Inner Shield		
Type	Material	Coverage [%]
Braid	Bare Copper (BC)	90%

Inner Jacket	
Material	Nominal Diameter
PE - Polyethylene	0.391 in

Outer Shield		
Type	Material	Coverage [%]
Braid	Bare Copper (BC)	90%

Outer Jacket	
Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.52 in

Electrical Characteristics

Conductor DCR				
Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Inner Shield DCR	Nominal Outer Shield DCR
3.1 Ohm/1000ft	3.1 Ohm/1000ft		1.6 Ohm/1000ft	1.6 Ohm/1000ft

Capacitance	
Nom. Capacitance Conductor to Shield	
17.3 pF/ft	

Inductance	
Nominal Inductance	
0.097 µH/ft	

Impedance

Nominal Characteristic Impedance
75 Ohm

Return Loss (RL)

Frequency [MHz]	Minimum Return (RL)
5-850 MHz	21 dB

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.1 dB/100ft
3.6 MHz	0.3 dB/100ft
10 MHz	0.5 dB/100ft
71.5 MHz	1.2 dB/100ft
135 MHz	1.8 dB/100ft
270 MHz	2.6 dB/100ft
360 MHz	3.1 dB/100ft
540 MHz	3.9 dB/100ft
720 MHz	4.7 dB/100ft
750 MHz	4.8 dB/100ft
1000 MHz	5.7 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.3 ns/ft	78%

Voltage

Non-UL Voltage Rating	UL Voltage Rating	Voltage Rating [V]
300 V RMS	150 V RMS	30 V RMS
	30 V RMS	

Electrical Characteristics Notes:	Nominal Capacitance 1st Shield to 2nd Shield: 205 pf/ft.
Other Electrical Characteristic 2:	Nominal Voltage Breakdown: 20K V RMS

Temperature Range

Non-UL Temp Rating:	75°C
UL Temp Rating:	80°C
Operating Temperature Range:	-40°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	139 lbs/1000ft
Max. Pull Tension:	239 lbs
Min. Bend Radius/Minor Axis:	5.5 in

Standards

NEC/(UL) Compliance:	CL2X
UL AWM Style Compliance:	AWM 1641 (30 V 80°C)
CPR Euroclass:	Eca
RG Type:	11

Applicable Environmental and Other Programs

Environmental Space:	Indoor/Outdoor
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
MII Order #39 (China RoHS):	Yes

Suitability

--

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black for permanent outdoor installations; all colors suitable for outdoor field deployable use

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 UL Loading, VW-1
UL voltage rating:	150 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
9192 0041000	Yellow	Reel	1,000 ft	612825225201

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.369 Revision Date: 04-29-2024
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9192 0041000](#)