



Product: [9244](#)

Analog Video, RG59, #22 Solid BCCS, 85% BC Braid, PVC Jacket, CMX



Product Description

22 AWG solid bare copper-covered steel conductor, polyethylene insulation, bare copper braid shield (85% coverage), PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
22	Solid	BCCS - Bare Copper Covered Steel	0.025 in	1

Conductor Count:	1
------------------	---

Insulation

Material	Nominal Diameter
PE - Polyethylene	0.146 in

Outer Shield

Type	Material	Coverage [%]
Braid	Bare Copper (BC)	85%

Outer Jacket

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.242 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
50 Ohm/1000ft	50 Ohm/1000ft	4.5 Ohm/1000ft	4.5 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
19.4 pF/ft

Inductance

Nominal Inductance
0.112 µH/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

Return Loss (RL)

Frequency [MHz]	Minimum Return (RL)
5-450 MHz	23 dB

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.6 dB/100ft
10 MHz	1.1 dB/100ft
50 MHz	2.4 dB/100ft
100 MHz	3.4 dB/100ft
200 MHz	4.9 dB/100ft
400 MHz	7 dB/100ft
700 MHz	9.7 dB/100ft
900 MHz	11.1 dB/100ft
1000 MHz	12 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.54 ns/ft	66%

Power Rating

Frequency [MHz]	Max. Power Rating [W]	Nominal Power Rating [W]
50 MHz	470 W	470 W
100 MHz	310 W	310 W
300 MHz	160 W	160 W
500 MHz	115 W	115 W
1,000 MHz	76 W	76 W

Voltage

Non-UL Voltage Rating	UL Voltage Rating
1700 V RMS	150 V RMS

Temperature Range

Non-UL Temp Rating:	80°C
Operating Temperature Range:	-40°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	33 lbs/1000ft
Max. Pull Tension:	67 lbs
Min. Bend Radius/Minor Axis:	2.5 in

Standards

NEC/(UL) Compliance:	CMX
CEC/C(UL) Compliance:	CMX
UL AWM Style Compliance:	AWM 1354 (30 V 80°C)
CPR Euroclass:	Eca
RG Type:	59
Series Type:	59

Applicable Environmental and Other Programs

Environmental Space:	Indoor/Outdoor
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	VW-1
------------------	------

IEC Flammability:	IEC 60332-1-2
UL voltage rating:	150 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
9244 010U500	Black	UnReel	500 ft	612825358817
9244 0101000	Black	Reel	1,000 ft	612825357704
9244 010U1000	Black	UnReel	1,000 ft	612825357698

History

Update and Revision:	Revision Number: 0.377 Revision Date: 02-03-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9244 0101000](#) [9244 010U500](#) [9244 010U1000](#)