



Product: [9322](#)

High Perform Instr, 1 Pr #22 Str TC, PVC Ins E2, OS, PVC Jkt, PLTC-ER

[Request Sample](#)

Product Description

High Performance Instrumentation, 1 Pair 22AWG (7x30) Tinned Copper, PVC Insulation E2 Color Code, Overall Beldfoil® Shield, PVC Outer Jacket, PLTC-ER

Technical Specifications

Product Overview

| | |
|------------------------|--|
| Suitable Applications: | Instrumentation, Sensors, Valves, Positioners, 4-20mA, 0-10V |
|------------------------|--|

Construction Details

Conductor

| Element | Number of Element | AWG | Stranding | Material |
|---------|-------------------|-----|-----------|--------------------|
| Pair(s) | 1 | 22 | 7x30 | TC - Tinned Copper |

Insulation

| Element | Material | Thickness [in.] | Color Code |
|---------|--------------------------|-----------------|------------|
| Pair(s) | PVC - Polyvinyl Chloride | 0.017 | Black, Red |

Outer Shield Material

| Shield Type | Material | Coverage | Drainwire Type |
|-------------|-------------------------|----------|------------------|
| Tape | Bi-Laminate (Alum+Poly) | 100% | 22 AWG (7x30) TC |

Outer Jacket Material

| Material | Thickness | Nom. Diameter | Ripcord |
|--------------------------|-----------|---------------|---------|
| PVC - Polyvinyl Chloride | 0.037 in | 0.201 in | Yes |

| | |
|---------------------------|----------|
| Cable Diameter (Nominal): | 0.201 in |
|---------------------------|----------|

Electrical Characteristics

Electricals

| Element | Nom. Conductor DCR | Nom. Capacitance Cond-to-Cond |
|---------|--------------------|-------------------------------|
| Pair(s) | 15.0 Ohm/1000ft | 46 pF/ft |

| | |
|-----------------------|---------------|
| Nom Outer Shield DCR: | 15 Ohm/1000ft |
|-----------------------|---------------|

Voltage

| UL Voltage Rating |
|--------------------------------|
| 300 V (PLTC, CMG), 150 V (ITC) |

Mechanical Characteristics

Temperature

| UL Rating | Operating |
|-----------|-----------------|
| 105°C | -30°C to +105°C |

| | |
|--------------|----------|
| Table Notes: | AWM 80°C |
|--------------|----------|

Bend Radius

| Stationary Min. | Installation Min. |
|-----------------|-------------------|
| | |

| | |
|------|------|
| 2 in | 2 in |
|------|------|

| | |
|--------------------|---------------|
| Max. Pull Tension: | 24 lbs |
| Bulk Cable Weight: | 19 lbs/1000ft |

Standards and Compliance

| | |
|---------------------------------|---|
| Environmental Suitability: | Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance |
| Flammability / Fire Resistance: | UL1685 UL Loading, T-29-520, 1202 |
| NEC / UL Compliance: | Article 725, Article 727, Article 800, CMG, ITC-ER, PLTC-ER |
| AWM Compliance: | 2464 |
| CEC / C(UL) Compliance: | CMG |
| European Directive Compliance: | EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE) |
| APAC Compliance: | China RoHS II (GB/T 26572-2011) |

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.384 Revision Date: 09-30-2020 |
|----------------------|--|

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9322 060U500](#) [9322 0605000](#) [9322 060U1000](#)