



Part Number: 9365

300V PLTC, (1 triad) 18 AWG (19x30) TC, PVC/PVC, Foil Shld, TC

[Request Sample](#)

Product Description

One 18 AWG triad stranded (19x30) tinned copper conductors, PVC insulation, overall Beldfoil® shield (100% coverage), PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	No. of Triads
Triad	18	19x30	TC - Tinned Copper	1

Conductor Count:	3
Total Number of Pairs:	N/A
Total Number of Triads:	1
Conductor Size:	18 AWG

Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.017 in

Color Chart

Number	Color
1	Black & White & Red

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	20	19x32 mm

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.260 in	0.037 in	Yes

Construction and Dimensions

Cabling

Filler
Polypropylene Filler

Print Legend: LEGEND: BELDEN 9365 E34972 1TRD18 (UL) CMG 105C OR PLTC OR ITC SUN RES DIR BUR OR AWM 2464 80C 300V OR C(UL) CMG----FT4 IEEE 1202 (2 FT, 7 DIGIT SEQUENTIAL NUMBER) FEET

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
5.86 Ohm/1000ft	9.5 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
---	---

54 pF/ft	101 pF/ft
----------	-----------

Inductance

Nominal Inductance
0.17 µH/ft

Impedance

Nominal Characteristic Impedance
45 Ohm

Voltage

UL Description	UL Voltage Rating
PLTC, CMG	300 V RMS
ITC	150 V RMS

Temperature Range

UL Temp Rating:	80°C
Operating Temp Range:	-30°C To +105°C

Mechanical Characteristics

Bulk Cable Weight:	39 lbs/1000ft
Max Recommended Pulling Tension:	39 lbs
Min Bend Radius/Minor Axis:	2.5 in

Standards

NEC/(UL) Specification:	CMG, ITC-ER, PLTC-ER
CEC/C(UL) Specification:	CMG
UL AWM Style:	UL Style 2464 (300 V 80°C)

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 UL Loading
CSA Flammability:	FT4
IEEE Flammability:	1202
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Footnote
9365 0601000	Chrome	C
9365 0602500	Chrome	Z

9365 0605000	Chrome	C
9365 060U1000	Chrome	
9365 060U500	Chrome	

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.