



Product: [9463](#)

Blue Hose®, 1 Pr #20 Str TC, PE Ins Blu, Clr, Foil+TC Brd, PVC Jkt, CM

[Request Sample](#)

Product Description

Blue Hose® for Data Highway Plus, 1 Pair 20AWG (7x28) Tinned Copper, PE Insulation Blue & Clear, Overall Beldfoil®+Tinned Copper Braid(55%) Shield, Blue PVC Outer Jacket, CM

Technical Specifications

Product Overview

Suitable Applications:	harsh environment, Allen Bradley Data Highway communication interface between PLC processors, I/O devices, operator interfaces, computers and other intelligent devices, PLC processor interlocking, peer-to-peer messaging, remote programming, troubleshooting, I/O updates, etc.
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	20 AWG	7x28	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code	Notes
Pair(s)	PE - Polyethylene	0.019 in (0.48 mm)	0.0755 in (1.92 mm)	Clear & Blue	Twinax with rod fillers

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	20 AWG (7x28) TC
Braid	Tinned Copper (TC)	60%	

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.037 in (0.94 mm)	0.238 in (6.05 mm)

Table Notes:	Jacket OD +/- 0.003
Overall Cable Diameter (Nominal):	0.238 in (6.05 mm)

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Shield	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Velocity of Prop.
Pair(s)	9.5 Ohm/1000ft	19.7 pF/ft (64.6 pF/m)	37 pF/ft	36 pF/ft	78 Ohm	66%
Nom. Outer Shield DCR:	4.1 Ohm/1000ft (13 Ohm/km)					

High Frequency (Nominal/Typical)

Element	Frequency [MHz]	Nom. Insertion Loss (Attenuation)
Pair(s)	1	0.6 dB/100ft
	10	2.1 dB/100ft
	50	5.0 dB/100ft
	100	7.5 dB/100ft
	200	11.0 dB/100ft
	400	16.0 dB/100ft

Voltage

UL Voltage Rating
300 V (CM, CL2), 300 V (UL AWM 2464)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation	Storage
80°C	-40°C to +80°C	-40°C To +80°C	-40°C to +80°C

Bend Radius

Stationary Min.	Installation Min.
2.4 in (61 mm)	2.4 in (61 mm)

Max. Pull Tension:	48 lbs (22 kg)
Bulk Cable Weight:	36 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance
Flammability / Reaction to Fire:	UL 1685 UL Loading, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 725, Article 800, CM, CL2
AWM Compliance:	AWM 2464
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
Other Standard Compliance(s):	P-7K-SC-182141-MSHA, Allen Bradley Part No. 1770-CD
Plenum Number:	89463

History

Update and Revision:	Revision Number: 0.614 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC/EAN	Footnote
9463.0030	Blue	Reel	30 m	8719605020550	
9463.00U152	Blue	UnReel	152 m	8719605020574	
9463.01152	Blue	Reel	152 m	8719605020598	
9463.00305	Blue	Reel	305 m	8719605020567	
9463.00U305	Blue	UnReel	305 m	8719605020581	
9463.001000	Blue	Reel	1,000 m	8719605020536	
9463.001829	Blue	Reel	1,829 m	8719605020543	
9463 J22100	Blue, Strong	Reel	100 ft	612825253549	
9463 J22500	Blue, Strong	Reel	500 ft	612825253570	
9463 J22U500	Blue, Strong	UnReel	500 ft	612825253532	
9463 J221000	Blue, Strong	Reel	1,000 ft	612825253556	C
9463 J22U1000	Blue, Strong	UnReel	1,000 ft	612825253525	
9463 J2212000	Blue, Strong	Reel	2,000 ft	612825253563	C Y
9463 J226000	Blue, Strong	Reel	6,000 ft	612825253587	C Z
9463.02305	Brown	Reel	305 m	8719605020604	
9463 0011000	Brown	Reel	1,000 ft	612825253594	
9463 00112000	Brown	Reel	2,000 ft	612825253617	C Y
9463.023050	Brown	Reel	3,050 m	8719605020611	
9463 0016000	Brown	Reel	6,000 ft	612825253624	C Z
9463 00110000	Brown	Reel	10,000 ft	612825253600	C Z
9463 0031000	Orange	Reel	1,000 ft	612825253631	C
9463 00312000	Orange	Reel	2,000 ft	612825253655	C Y
9463 0036000	Orange	Reel	6,000 ft	612825253662	C Z

9463 00310000	Orange	Reel	10,000 ft	612825253648	C Z
9463 0071000	Violet	Reel	1,000 ft	612825253679	C
9463 0076000	Violet	Reel	6,000 ft	612825253686	C Z

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9463 J221000](#) [9463 J22500](#) [9463 J22U1000](#) [9463 J22U500](#) [9463 J22100](#) [9463 00110000](#) [9463 0011000](#) [9463](#)
[00310000](#) [9463 0031000](#) [9463 0036000](#) [9463 J226000](#) [9463 0016000](#) [9463 0076000](#) [9463 0071000](#) [9463](#)
[00112000](#) [9463 J2212000](#) [9463 00312000](#)