



Product: [9550](#)

RS232, #24-50pr, SR-PVC, O/A Foil, PVC Jkt, CMG, 75Ω

Product Description

Computer EIA RS-232 Cable, 24 AWG stranded (7x32) tinned copper conductors, semi-rigid PVC insulation, 50 twisted pairs, overall Beldfoil® shield (100% coverage), 24 AWG stranded tinned copper drain wire (continued), PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	RS-232 Applications; Computer Communications; Low Voltage Analog Signals (4-20ma, 0-10v, ...); Low Voltage Digital Control (24v, ...); Line Level Audio; Panel Wiring
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	50	24 AWG	7x32	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	SR-PVC - Polyvinyl Chloride (Semi-Rigid)	0.011 in (0.28 mm)	0.044 in (1.1 mm)	Blue & White, Orange & White, Green & White, Brown & White, Gray & White, Blue/ White & White, Blue/Orange & White, Blue/Green & White, Blue/Brown & White, Blue/Gray & White, Orange/White & White, Orange/Green & White, Orange/Brown & White, Orange/Gray & White, Green/White & White, Green/Brown & White, Green/Gray & White, Brown/White & White, Brown/Gray & White, Gray/White & White, Blue & Red, Orange & Red, Green & Red, Brown & Red, Gray & Red, Blue/White & Red, Blue/Orange & Red, Blue/Green & Red, Blue/Brown & Red, Blue/Gray & Red, Orange/White & Red, Orange/Green & Red, Orange/Brown & Red, Orange/Gray & Red, Green/White & Red, Green/Brown, Red, Green/Gray & Red, Brown/White & Red, Brown/Gray & Red, Gray/White & Red, Blue & Black, Orange & Black, Green & Black, Brown & Black, Gray & Black, Blue/White & Black, Blue/Orange & Black, Blue/Green & Black, Blue/Brown & Black, Blue/Gray & Black

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.054 in (1.4 mm)	0.708 in (18.0 mm)

Overall Cable Diameter (Nominal):	0.708 in (18.0 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Velocity of Prop.	Max. Current
Pair(s)	28.8 Ohm/1000ft	30 pF/ft (98 pF/m)	50 pF/ft (160 pF/m)	60%	2.2 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V (CMG), 300 V (UL AWM 2464)

Mechanical Characteristics

Temperature

UL Temperature	Operating
----------------	-----------

80°C	-30°C to +80°C
------	----------------

Bend Radius

Stationary Min.	Installation Min.
7.1 in (180 mm)	7.1 in (180 mm)

Max. Pull Tension:	556 lbs (252 kg)
Bulk Cable Weight:	286 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 2464, AWM I/II A
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.460 Revision Date: 01-20-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
9550 060100	Chrome	Reel	100 ft	612825255741	C
9550 060500	Chrome	Reel	500 ft	612825255765	C D
9550 0601000	Chrome	Reel	1,000 ft	612825255758	C D

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9550 060100](#) [9550 060500](#) [9550 0601000](#)