



Product: [9621](#)

Electronic, 9 C #16 Str TC, PVC Ins, PVC Jkt

[Request Sample](#)

Product Description

Electronic, 9 Conductor 16AWG (19x29) Tinned Copper, PVC Insulation, PVC Outer Jacket

Technical Specifications

Product Overview

Suitable Applications:	Analog Signals & Control (up to 600V); Line Level Audio; Voice Communications; Panel Wiring
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	9	16 AWG	19x29	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.031 in (0.79 mm)	0.121 in (3.07 mm)	Black, White, Red, Green, Orange, Blue, White/Black Stripe, Red/Black Stripe, Green/Black Stripe

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.045 in (1.1 mm)	0.533 in (13.5 mm)

Overall Cable Diameter (Nominal):	0.533 in (13.5 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals			
Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	4.4 Ohm/1000ft	19.5 pF/ft (64.0 pF/m)	5 Amps per Conductor at 25°C
Voltage			
Voltage Rating			
600 V			

Mechanical Characteristics

Temperature	
Operating	
-20°C to +80°C	

Bend Radius	
Stationary Min.	Installation Min.
5.3 in (130 mm)	5.3 in (130 mm)

Max. Pull Tension:	273 lbs (124 kg)
Bulk Cable Weight:	170 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1581 (VW-1), IEC 60332-1-2, VW-1
CPR Compliance:	CPR Euroclass: Eca
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.516 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	UPC	Footnote
9621 060100	Chrome	612825256700	C
9621 0601000	Chrome	612825256717	C
9621 060500	Chrome	612825256724	C
9621 0605000	Chrome	612825256731	

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9621 060100](#) [9621 060500](#) [9621 0601000](#) [9621 0605000](#)