



VHF ANTENNA, FLEXIBLE WHIP**136 MHz – 174 MHz****MD10-003****Series : Antenna**

UNITS: INCH



All dimensions are inches

Issue : 1041

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

RADIAL

VHF ANTENNA, FLEXIBLE WHIP**136 MHz – 174 MHz****MD10-003****Series : Antenna****ELECTRICAL CHARACTERISTICS**Frequency : **136 - 174 MHz**Nominal Impedance: **50 Ω** VSWR*: **3.0:1 Max**Peak Gain:: **>-2 dBi****Radiation Pattern**Horizontal Plane ($\Theta=90^\circ$): **Omni-directional**Vertical Plane ($\Phi=0^\circ/90^\circ$): **Dipolar**Polarization : **Linear Vertical**Power withstanding : **8 W (CW)**Connector type : **TNC Male****MECHANICAL CHARACTERISTICS**Antenna Color : **Black matte**Antenna Material : **Texin 245**Antenna Texture : **Flat**Flexibility: **180° - 500 cycles**Matching Unit Length: **2.70 Inches**Weight (antenna): **3 Oz**Overall length : **13.23 Inches**

*: Measured when antenna is mounted on a handheld radio chassis held by hand

Issue : 1041

In the effort to improve our products, we reserve the right to make changes judged to be necessary.



VHF ANTENNA, FLEXIBLE WHIP**136 MHz – 174 MHz****MD10-003****Series : Antenna****ENVIRONMENTAL CHARACTERISTICS**



Product Compliant with the RoHS (Restriction of Hazardous Substances) and WEEE (Waste Electrical and Electronics Equipment) requirements

Operating Temperature :	-33 / +60 °C MIL-STD-810F, Methods 501.4 & 502.4, Procedure II
Storage Temperature :	-51 / +71 °C MIL-STD-810F, Methods 501.4 & 502.4, Procedure I
Sand & Dust:	Ambient +70 °C Concentration 2.2 & 10.6 g/m³ Velocity 3450-5700 & 300-1750 ft/min MIL-STD-810F, Methods 510.4, Procedure I & Procedure II
Salt Fog:	5% Salt Concentration 96 Hours MIL-STD-810F, Methods 509.4
Humidity:	95% Relative Humidity +30/+60 °C MIL-STD-810F, Methods 507.4
Fungus:	US Standard Set Of Test Fungi Duration 28 Days MIL-STD-810F, Method 508.5
Shock (Transit Drop):	Drop Height 19.7 Inches MIL-STD-810F, Method 516.5, Procedure IV, 26 Drops
Vibration : (Loose Cargo Transportation)	MIL STD 810F Method 514.5 Procedure II Category 5 MIL-STD-810F Method 512.4 Stand alone & attached to the radio at ambient temperature
Immersion :	2 Meters, Salt Water Complete Immersion 2 Hours Conditioning Temperature: 27 ° Celsius above water temperature
Flexibility :	180 degree bend, 500x, .5 Hz Max

OTHER CHARACTERISTICS**Issue : 1041**



In the effort to improve our products, we reserve the right to make changes judged to be necessary.



VHF ANTENNA, FLEXIBLE WHIP**136 MHz – 174 MHz****MD10-003****Series : Antenna****CURVES****Figure 1: VSWR measured holding the radio chassis.****Figure 2: Elevation Gain Patterns @ 136 MHz****Issue : 1041**

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

RADIAL 

VHF ANTENNA, FLEXIBLE WHIP**136 MHz – 174 MHz****MD10-003****Series : Antenna****Figure 3: Elevation Gain Patterns @ 155 MHz****Figure 4: Azimuth & Elevation Gain Patterns @ 174 MHz****Issue : 1041**

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

RADIAL 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

[MD10-003](#)