

9738 Multi-Conductor - Multi-Pair Snake Cable

For more Information
please call

1-800-Belden1

**General Description:**

24 AWG stranded (7x32) TC conductors, Datalene® insulation, twisted pairs, individually shielded w/Beldfoil® (100% coverage), 24 AWG stranded TC drain wire, overall PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material	Dia. (in.)
27	24	7x32	TC - Tinned Copper	.024

Total Number of Conductors: 54

Insulation**Insulation Material:**

Insulation Trade Name	Insulation Material	Wall Thickness (in.)
Datalene®	FPE - Foam Polyethylene	0.019

Inner Shield**Inner Shield Material:**

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
24

Inner Shield Drain Wire Stranding: 7x32

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Shield**Outer Shield Material:**

Outer Shield Material
Unshielded

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.065

Overall Cable

Overall Nominal Diameter: 0.797 in.

Pair**Pair Color Code Chart:**

Number	Color
1	Black & Red
2	Black & White
3	Black & Green
4	Black & Blue
5	Black & Yellow
6	Black & Brown
7	Black & Orange
8	Red & White

9	Red & Green
10	Red & Blue
11	Red & Yellow
12	Red & Brown
13	Red & Orange
14	Green & White
15	Green & Blue
16	Green & Yellow
17	Green & Brown
18	Green & Orange
19	White & Blue
20	White & Yellow
21	White & Brown
22	White & Orange
23	Blue & Yellow
24	Blue & Brown
25	Blue & Orange
26	Brown & Yellow
27	Brown & Orange

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +80°C
UL Temperature Rating:	60°C (UL AWM Style 2493)
Bulk Cable Weight:	269 lbs/1000 ft.
Max. Recommended Pulling Tension:	432 lbs.
Min. Bend Radius/Minor Axis:	8 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
AWM Specification:	UL Style 2493 (300 V 60°C)
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
100

Nom. Inductance:

9738 Multi-Conductor - Multi-Pair Snake Cable

Inductance (μH/ft)

0.23

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

12.5

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

23.2

Nominal Velocity of Propagation:

VP (%)

76

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

24

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 15 Ohm/1000 ft

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
.384	0.74
.7056	0.87
.768	0.88
1.024	0.94
1.4112	1.01
1.536	1.03
2.048	1.13
2.8224	1.29
3.072	1.35
4.096	1.57
5.6448	1.78
6.144	1.84
8.192	2.13
11.2896	2.45
12.288	2.57
24.576	3.57

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

1.9 Amps per conductor @ 25°C

Notes (Overall)

Notes: Datalene® insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9738 0601000	1,000 FT	334.000 LB	CHROME	C	27 FS PR #24 FHDPE PVC

Notes:

C = CRATE REEL PUT-UP.

9738 Multi-Conductor - Multi-Pair Snake Cable

Revision Number: 2 Revision Date: 09-28-2012

© 2019 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9738 0601000](#)