



**Product:** [9839](#)

RS232/422 Low Cap, #24-6pr, PE, O/A Foil+Braid, PVC Jkt, CM, 100Ω

**Product Description**

Computer EIA RS-232/422 Cable, 6-Pair, 24 AWG stranded (7x32) tinned copper conductors, polyethylene insulation, overall Beldfoil® (100% coverage) + tinned copper braid shield (65% coverage), 24 AWG stranded tinned copper drain wire, PVC jacket.

**Technical Specifications**

**Product Overview**

Suitable Applications:	RS-232 extended distance applications; RS-422 applications; computer communications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; panel wiring
------------------------	--

**Construction Details**

**Conductor**

Element	No. of Elements	Size	Stranding	Material
Pair(s)	6	24 AWG	7x32	TC - Tinned Copper

**Insulation**

Element	Material	Nom. Thickness	Color Code
Pair(s)	PE - Polyethylene	0.0155 in (0.394 mm)	White/Blue Stripe & Blue/White Stripe, White/Orange Stripe & Orange/White Stripe, White/Green Stripe & Green/White Stripe, White/Brown Stripe & Brown/White Stripe, White/Gray Stripe & Gray/White Stripe, Red/Blue Stripe & Blue/Red Stripe

**Outer Shield**

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC
Braid	Tinned Copper (TC)	65%	

**Outer Jacket**

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.035 in (0.89 mm)	0.364 in (9.25 mm)

Overall Cable Diameter (Nominal):	0.364 in (9.25 mm)
-----------------------------------	--------------------

**Electrical Characteristics**

**Electricals**

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
Pair(s)	24 Ohm/1000ft (79 Ohm/km)	15.5 pF/ft (50.9 pF/m)	27.5 pF/ft (90.2 pF/m)	100 Ohm	66%	1.47 Amps per Conductor at 25°C

**Voltage**

UL Voltage Rating
300 V (CM), 30 V (UL AWM 2919)

**Mechanical Characteristics**

**Temperature**

UL Temperature	Operating
80°C (UL AWM 2919)	-30°C to +80°C

Bulk Cable Weight:	63 lbs/1000ft (94 kg/km)
--------------------	--------------------------

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL1685 UL Loading
NEC / UL Compliance:	Article 800, CM
AWM Compliance:	AWM 2919
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.330 Revision Date: 12-22-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
9839 060500	Chrome	Reel	500 ft	612825259435	C
9839 0601000	Chrome	Reel	1,000 ft	612825259428	C

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9839 0601000](#) [9839 060500](#)