



**Product:** [9862](#)

93Ω Coax RG-62/U, #22 BCCS, Semi-solid PO, BC Braid, PVC (Non-contam.) Jkt, CMX

Product Description

93 Ohm Coax MIL-DTL-17 QPL, M17/30-RG062, 22 AWG solid .025" bare copper-covered steel conductor, semi-solid polyethylene insulation, bare copper braid shield (95% coverage), non-contaminating PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	RF, Antenna, Mil Spec
------------------------	-----------------------

Physical Characteristics (Overall)

Conductor				
AWG	Stranding	Material	Nominal Diameter	No. of Coax
22	Solid	BCCS - Bare Copper Covered Steel	0.025 in	1
Conductor Count:		1		

Insulation		
Material	Nominal Diameter	Nominal Wall Thickness
PE - Polyethylene (Semi-Solid)	0.146 in	0.026 in

Outer Shield		
Type	Material	Coverage [%]
Braid	Bare Copper (BC)	95%

Outer Jacket		
Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride (Non-Contaminating)	0.242 in	0.033 in

Electrical Characteristics

Conductor DCR	
Nominal Conductor DCR	Nominal Outer Shield DCR
40.5 Ohm/1000ft	2.4 Ohm/1000ft

Capacitance	
Nom. Capacitance Conductor to Shield	
13.0 pF/ft	

Inductance	
Nominal Inductance	
0.116 μH/ft	

Impedance	
Nominal Characteristic Impedance	
93 Ohm	

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.3 dB/100ft
10 MHz	0.9 dB/100ft
50 MHz	1.9 dB/100ft
100 MHz	2.7 dB/100ft
200 MHz	3.8 dB/100ft
400 MHz	5.3 dB/100ft
700 MHz	7.3 dB/100ft
900 MHz	8.2 dB/100ft
1000 MHz	8.7 dB/100ft

Delay

Nominal Velocity of Propagation (VP) [%]
85%

Voltage

UL Voltage Rating	Voltage Rating [V]
300 V RMS	750 V RMS

Temperature Range

UL Temp Rating:	60°C
Operating Temperature Range:	-40°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	34 lbs/1000ft
Max. Pull Tension:	66 lbs
Min. Bend Radius/Minor Axis:	2.5 in

Standards

NEC/(UL) Compliance:	CMX
CEC/C(UL) Compliance:	CMX
UL AWM Style Compliance:	AWM 1354 (30 V 60°C)
RG Type:	62
Military Compliance:	MIL-DTL-17, M17/30-RG62, QPL
Qualified Products List (QPL):	Yes

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	Yes - Black only, when supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black only

Flammability, LSOH, Toxicity Testing

UL Flammability:	VW-1
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

--

**Variants**

Item #	Color	Put-Up Type	Length	UPC
9862 0101000	Black	Reel	1,000 ft	612825259732

**History**

Update and Revision:	Revision Number: 0.336 Revision Date: 04-29-2024
----------------------	--

© 2024 Belden, Inc  
 All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9862 0101000](#)