



Product: [9944](#)

RS-232, #22-8c, SR-PVC, O/A Foil+Braid, PVC Jkt, CMG

Product Description

Computer EIA RS-232 Cable, 22 AWG stranded (7x30) tinned copper conductors, semi-rigid PVC insulation, overall Beldfoil® (100% coverage) + tinned copper braid shield (65% coverage), PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	RS-232 Applications; Computer Communications; Low Voltage Analog Signals (4-20mA, 0-10V, ...); Low Voltage Digital Control (24V, ...); Line Level Audio; Panel Wiring
------------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Conductor(s)	8	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Color Code
Conductor(s)	SR-PVC - Polyvinyl Chloride (Semi-Rigid)	0.011 in (0.28 mm)	Black, White, Red, Green, Brown, Blue, Orange, Yellow

Outer Shield

Shield Type	Material	Coverage
Tape	Bi-Laminate (Alum+Poly)	100%
Braid	Tinned Copper (TC)	65%

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.035 in (0.89 mm)	0.264 in (6.71 mm)

Overall Cable Diameter (Nominal): 0.264 in (6.71 mm)

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	14.7 Ohm/1000ft (48.2 Ohm/km)	35 pF/ft (110 pF/m)	63 pF/ft (210 pF/m)	1.5 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V (CMG), 300 V (UL AWM 2464)

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C (UL CMG);80°C (UL AWM 2464)	-30°C to +80°C

Bend Radius

Stationary Min.	Installation Min.

3.2 in (81 mm)	3.2 in (81 mm)
----------------	----------------

Bulk Cable Weight:	48 lbs/1000ft (71 kg/km)
--------------------	--------------------------

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL1685 FT4 Loading, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	2464
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark

History

Update and Revision:	Revision Number: 0.346 Revision Date: 12-15-2021
----------------------	--------------------------------------------------

Variants

Item #	Color	UPC
9944 060100	Chrome	612825264835
9944 0601000	Chrome	612825264842
9944 060500	Chrome	612825264859
9944 0605000	Chrome	612825264866

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9944 0601000](#) [9944 060500](#) [9944 060100](#) [9944 0605000](#) [9541 0605000](#)