





- A** NOTES:
1. CONNECTOR HEIGHT NOT AVAILABLE AS STANDARD.
 2.  REPRESENTS A CRITICAL DIMENSION.
 3. CONTACT TO BE FLUSH $\pm .002[0.05]$ TO BE MEASURED AT ALL 4 CORNERS. DO NOT MEASURE ON THE BREAK-OFF SURFACE.
 4. PARTS TO BE PACKAGED IN TAPE & REEL.
FOR QUANTITIES LESS THAN 125 PCS, NO TRAILER OR LEADER WILL BE SUPPLIED.
 5. NOTE DELETED.
 6. MINIMUM PUSHOUT FORCE: .5 LB
 7. ONE REEL MINIMUM PLATING REQUIREMENT (85,000 CONTACTS PER REEL).
 8. ALL DIMS TO BE SYMMETRICAL ABOUT THE CENTERLINE WITHIN $\pm .001[0.03]$.
 9. MAXIMUM VARIATION BETWEEN SOLDERBALLS: .0025[0.064]
 10. REFER TO VISUAL INSPECTION BOARD FOR SOLDERBALL APPEARANCE CHECKS.
 11. THE DISTANCE FROM THE CENTER OF ANY SOLDERBALL TO THE CENTER OF ANY ADJACENT INNER PEG SHALL BE $.025 \pm .005[0.64 \pm 0.13]$.
 12. SOLDER JOINTS TO BE INSPECTED PER IPC SPECIFICATION 12.2.12 (IPC-A-610C).

DO NOT
SCALE FROM
THIS PRINT

ANY REV. MADE TO THIS PRINT MUST HAVE AN UPDATED MKT PRINT



ITEM NO.	PART NUMBER	QUANTITY	MATERIAL
1	ASP-167045-01-B	1.0000	LCP, COLOR: BLACK
2	ASP-190171-02-P-H-SUB	114.00	PHOS BRONZE
3	SDB-030-9653	114.00	96.5% Sn /3% Ag/.5% Cu
4	K-DOT-.354-.469-.005	1.0000	POLYIMIDE FILM
5	CT-ASP1949MS	.00222	CONDUCTIVE POLYMER

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS

ANGLES

.XX: $\pm .01[0.3]$

2°

.XXX: $\pm .005[0.13]$

.XXXX: $\pm .0020[0.051]$

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 3:1

PLATING:

CONTACT AREA: .000030 GOLD OVER .000050 NICKEL

REMAINDER: .000003 GOLD OVER .000050 NICKEL

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:

LEAD FREE VITA ASSEMBLY



DWG. NO.

ASP-189983-02


BY: J. BROWNING 11/04/2015

SHEET 1 OF 2


c:\enterprise\dwg\mktg\mktg\ASP-189983-02-MKT.SLDDRW




RECOMMENDED MAIN BOARD LAYOUT



RECOMMENDED STENCIL LAYOUT
STENCIL TO BE .006 [0.152] THICK



USER DIRECTION OF UN-REELING
POCKET NOT DETAILED



PACKAGING VIEW

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

SHEET SCALE: 3:1

DESCRIPTION: LEAD FREE VITA ASSEMBLY

DWG. NO. ASP-189983-02

BY: J. BROWNING 11/04/2015 SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[ASP-189983-02](#)