



(2.54 mm) .100"

BBS, BBL, BHS, BBD, BDL SERIES

MACHINED BOARD STACKING STRIPS

Mates with:

SS, SD, HSS, SL, SDL,
ESS, ESD

FEATURES

- Low profile design achieves (3.89 mm) .153" board spacings when mated with SL Series.
- Approach the reliability of a permanent connection with the flexibility of a separable connection.

SPECIFICATIONS

For complete specifications see www.samtec.com?BBS, www.samtec.com?BBL, www.samtec.com?BHS, www.samtec.com?BBD or www.samtec.com?BDL

Insulator Material:
Black Liquid Crystal Polymer (BBL, BHS)
Black Glass Filled Polyester (BBS, BBD, BDL)

Temperature Range:
-55 °C to +125 °C

Terminal Material:
Phosphor Bronze or Brass

Plating:

Au or Sn over
50 μ" (1.27 μm) Ni

Lead-Free Solderable:
Yes (BBL, BDL, BHS-S)


No, Lead Wave only
(BBS, BBD, BHS-N)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Note:
Some lengths, styles and options are non-standard, non-returnable.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[BHS-104-G-G](#) [BHS-107-T-A](#) [BHS-110-G-A](#) [BHS-102-G-B](#) [BHS-102-G-D](#) [BHS-102-G-G](#) [BHS-109-G-A](#) [BHS-109-T-A](#) [BHS-116-G-B](#) [BHS-120-G-A](#) [BHS-120-G-B](#) [BHS-130-G-A](#) [BHS-130-G-B](#) [BHS-131-G-A](#) [BHS-136-G-C](#) [BHS-136-G-D](#) [BHS-136-G-G](#) [BHS-136-T-B](#) [BHS-102-T-B](#) [BHS-105-T-A](#) [BHS-106-G-A](#) [BHS-106-G-G](#) [BHS-109-G-G](#) [BHS-112-G-C](#) [BHS-115-G-D](#) [BHS-115-T-A](#) [BHS-119-T-A](#) [BHS-119-T-B](#) [BHS-120-G-G](#) [BHS-115-G-A](#) [BHS-116-T-A](#) [BHS-117-G-B](#) [BHS-118-G-G](#) [BHS-133-T-B](#) [BHS-134-G-B](#) [BHS-136-T-A](#) [BHS-101-G-B](#) [BHS-104-G-B](#) [BHS-108-G-B](#) [BHS-108-G-C](#) [BHS-111-G-A](#) [BHS-117-G-G](#) [BHS-118-G-B](#) [BHS-124-T-B](#) [BHS-125-G-C](#) [BHS-132-T-A](#) [BHS-132-T-B](#) [BHS-133-G-A](#) [BHS-104-G-C](#) [BHS-105-G-B](#) [BHS-106-T-A](#) [BHS-110-G-B](#) [BHS-111-G-B](#) [BHS-113-G-B](#) [BHS-113-G-G](#) [BHS-118-T-A](#) [BHS-122-G-D](#) [BHS-132-G-D](#) [BHS-106-G-B](#) [BHS-109-G-B](#) [BHS-112-G-B](#) [BHS-112-G-D](#) [BHS-112-T-A](#) [BHS-116-G-A](#) [BHS-128-T-A](#) [BHS-136-G-A](#) [BHS-136-G-B](#) [BHS-101-G-C](#) [BHS-103-G-B](#) [BHS-104-T-A](#) [BHS-107-G-B](#) [BHS-117-T-A](#) [BHS-118-G-A](#) [BHS-125-G-A](#) [BHS-108-T-A](#) [BHS-108-T-C](#) [BHS-114-T-B](#) [BHS-116-G-G](#) [BHS-116-T-B](#) [BHS-119-G-B](#) [BHS-120-T-B](#) [BHS-125-G-G](#) [BHS-134-T-A](#) [BHS-114-G-G](#) [BHS-119-G-A](#) [BHS-120-T-A](#) [BHS-120-T-C](#) [BHS-127-T-A](#) [BHS-132-G-C](#) [BHS-132-G-G](#) [BHS-136-T-C](#) [BHS-103-G-A](#) [BHS-107-G-A](#) [BHS-108-G-G](#) [BHS-108-T-B](#) [BHS-113-G-A](#) [BHS-101-T-B](#) [BHS-103-G-D](#) [BHS-109-T-C](#) [BHS-110-G-D](#)