


LOW PROFILE DUAL WIPE SOCKET

(1.27 mm) .050" PITCH • CLP SERIES



CLP

Mates:

FTSH, FTS, FW

CLP	1	NO. PINS PER ROW	02	PLATING OPTION	ROW OPTION	OTHER OPTIONS
-----	---	------------------	----	----------------	------------	---------------

02 thru 50

SPECIFICATIONS

Insulator Material:

Black Liquid Crystal Polymer

Contact Material:

Phosphor Bronze

Plating:

Sn or Au over

50 μ" (1.27 μm) Ni

Current Rating (CLP/FTSH):

3.4 A per pin

(2 pins powered)

Voltage Rating:

280 VAC/395 VDC

Operating Temp Range:

-55 °C to +125 °C

Insertion Depth:

Top Entry =

(1.40 mm) .055" minimum

Bottom Entry =

(2.41 mm) .095" minimum

plus board thickness

DH Entry =

(2.31 mm) .091" to (2.67 mm) .105"

Max Cycles:

100 with 10 μ" (0.25 μm) Au

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:


(0.10 mm) .004" max (02-35)

(0.15 mm) .006" max (36-50)*

*(.004" stencil solution

may be available; contact

ipg@samtec.com)



ALSO AVAILABLE

MOQ Required

Single row

Other platings




Notes:


Severe Environment
Testing qualified; aligns
with MIL-DTL-55302.
Visit samtec.com/set

Some lengths, styles and
options are non-standard,
non-returnable.

PIN/ROW	A
04-15	(3.56) .140
16-50	(7.11) .280



If odd pins/row, alignment pins are on
middle position on centerline of the part.
If even pins/row, then alignment pins are
between middle two positions.



-PA OPTION



-P OPTION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[CLP-104-02-L-D](#) [CLP-102-02-G-D](#) [CLP-103-02-L-D](#) [CLP-104-02-F-D](#) [CLP-102-02-L-D](#) [CLP-104-02-G-D](#) [CLP-103-02-G-D-BE](#) [CLP-102-02-L-D-BE](#) [CLP-103-02-G-D](#) [CLP-102-02-F-D](#) [CLP-103-02-F-D-BE](#) [CLP-102-02-F-D-BE](#) [CLP-103-02-G-D-A](#) [CLP-104-02-G-D-BE](#) [CLP-104-02-F-D-BE](#) [CLP-102-02-G-D-BE](#) [CLP-103-02-F-D](#) [CLP-103-02-L-D-BE](#) [CLP-104-02-L-D-A](#) [CLP-104-02-G-D-A](#) [CLP-104-02-F-D-BE-A](#) [CLP-103-02-L-D-A](#) [CLP-104-02-L-D-BE-A](#) [CLP-103-02-F-D-A](#) [CLP-110-02-STL-D-TR](#) [CLP-120-02-H-D-A-P](#) [CLP-104-02-STL-D-A-K-TR](#) [CLP-117-02-H-D-BE-TR](#) [CLP-133-02-L-D-K-FR](#) [CLP-113-02-L-D-A-FR](#) [CLP-105-02-H-D-P](#) [CLP-102-02-STL-D-K-TR](#) [CLP-105-02-STL-D](#) [CLP-117-02-H-D-BE-FR](#) [CLP-102-02-STL-D-K-FR](#) [CLP-120-02-STL-D-A-P-FR](#) [CLP-105-02-F-S-FR](#) [CLP-114-02-L-D-BE-K-FR](#) [CLP-132-02-F-D-BE-A-K-FR](#) [CLP-108-02-L-D-BE-A-FR](#) [CLP-130-02-L-D-BE-A-K-FR](#) [CLP-150-02-S-D-A-K-FR](#) [CLP-105-02-STL-D-K](#) [CLP-113-02-S-D-BE-FR](#) [CLP-121-02-F-D-BE-A-P-TR](#) [CLP-121-02-F-D-BE-A-P-FR](#) [CLP-117-02-STL-D-A-K-FR](#) [CLP-107-02-L-D-BE-A-P-FR](#) [CLP-108-02-S-D-PA-FR](#) [CLP-120-02-STL-D-A-P-TR](#) [CLP-108-02-G-D-BE-A-FR](#) [CLP-118-02-F-D-BE-A-K-FR](#) [CLP-104-02-STL-D-A-K-FR](#) [CLP-135-02-H-D-A](#) [CLP-108-02-G-D-BE-A-TR](#) [CLP-112-02-S-D-FR](#) [CLP-108-02-S-D-PA-TR](#) [CLP-117-02-STL-D-A-K-TR](#) [CLP-118-02-G-D-BE-P-FR](#) [CLP-112-02-S-D-A-P-FR](#) [CLP-140-02-H-D](#) [CLP-113-02-S-D-BE-TR](#) [CLP-114-02-STL-D-A](#) [CLP-130-02-L-D-BE-FR](#) [CLP-140-02-L-D-A-TR](#) [CLP-106-02-STL-D](#) [CLP-123-02-F-DH-A](#) [CLP-111-02-S-D-A-P](#) [CLP-121-02-F-D-A-P-FR](#) [CLP-121-02-S-D-BE-A-P-TR](#) [CLP-126-02-L-D-BE-A-K](#) [CLP-104-02-L-D-BE-A-K](#)