


MICRO BOARD STACKER

(1.27 mm) .050" PITCH • DWM/HDWM SERIES



DWM/HDWM

Mates:
SMS, SLM, RSM

SPECIFICATIONS

Insulator Material:
Liquid Crystal Polymer
Terminal Material:
Phosphor Bronze
Plating:
Au or Sn over 50 μ " (1.27 μ m) Ni
Operating Temp Range:
-55 °C to +105 °C with Tin
-55 °C to +125 °C with Gold

PROCESSING

Lead-Free Solderable:
Yes
SMT Lead Coplanarity:
(0.15 mm) .006" max*
*(.004" stencil solution may be available; contact ipg@samtec.com)

ALSO AVAILABLE

Other Platings
(MOQ Required)

DWM	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	STACKER HEIGHT	OTHER OPTION
	01 thru 50	Specify LEAD STYLE from chart	-L = 10 μ " (0.25 μ m) Gold on contact, Matte Tin on tail -G = 10 μ " (0.25 μ m) Gold on contact, Gold flash on tail	-S = Single Row -D = Double Row	- "XXX" = Stacker Height Example: -200 = (5.08 mm) .200"	- "XXX" = Polarized Position (Specify position of omitted pin)

(1.27) .050 x No. of Positions

(2.48) .098

(4.98) .196

(0.00) .000 MIN

(2.54) .100

(3.05) .120

STACKER HEIGHT (5.08) .200 MIN

OAL

OAL	
LEAD STYLE	THROUGH-HOLE
-01	(11.43) .450
-51	(10.41) .410
-52	(10.80) .425
-53	(12.83) .505
-54	(14.10) .555
-55	(15.49) .610
-56	(15.88) .625
-57	(16.51) .650
-58	(17.91) .705
-59	(19.18) .755
-60	(20.96) .825
-61	(26.67) 1.050

HDWM	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	STACKER HEIGHT	OTHER OPTION
	01 thru 50	Specify LEAD STYLE from chart	-L = 10 μ " (0.25 μ m) Gold on contact, Matte Tin on tail -G = 10 μ " (0.25 μ m) Gold on contact, Gold flash on tail	-S = Single Row -D = Double Row	- "XXX" = Stacker Height Example: -250 = (6.35 mm) .250"	- "XXX" = Polarized Position (Specify position of omitted pin) - SM = Surface Mount (02 thru 40 positions only) - A = Alignment Pin (6 positions minimum -D only) Metal or plastic at Samtec discretion (Not available with -LC) - LC = Locking Clip (5 positions minimum -D only) (Not available with -A) (Manual placement required) - P = Pick & Place Pad

(1.27) .050 x No. of Positions

(2.48) .098

(4.98) .196

(0.00) .000 MIN

(2.54) .100

(3.05) .120

STACKER HEIGHT (5.08) .200 MIN

OAL

STACKER HEIGHT (6.35) .250 MIN

OAL

OAL		
LEAD STYLE	THROUGH-HOLE	SURFACE MOUNT
-01	(11.43) .450	(8.38) .330
-51	(10.41) .410	—
-52	(10.80) .425	—
-53	(12.83) .505	(9.78) .385
-54	(14.10) .555	(11.05) .435
-55	(15.49) .610	(12.45) .490
-56	(15.88) .625	(12.83) .505
-57	(16.51) .650	(13.46) .530
-58	(17.91) .705	(14.86) .585
-59	(19.18) .755	(15.62) .615
-60	(20.96) .825	—
-61	(26.67) 1.050	—

Notes:
For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

This Series is non-standard, non-returnable.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[DWM-07-01-S-S-205](#) [DWM-10-61-L-D-820](#) [DWM-04-01-T-S-240](#) [DWM-20-01-L-S-236](#) [DWM-24-61-G-S-400](#) [DWM-20-60-L-D-590](#) [DWM-25-61-L-D-618](#) [DWM-02-01-T-S-240](#) [DWM-04-59-L-D-452](#) [DWM-15-57-L-D-410](#) [DWM-08-60-G-D-525](#) [DWM-08-55-L-D-380](#) [DWM-06-53-L-D-280](#) [DWM-01-53-L-S-236](#) [DWM-24-52-L-S-210](#) [DWM-02-53-L-S-236](#) [DWM-12-53-L-S-253](#) [DWM-11-58-G-D-405](#) [DWM-10-58-G-D-405](#) [DWM-03-54-G-S-216](#) [DWM-05-57-L-S-409](#) [DWM-01-51-L-S-230](#)