

RUGGED HIGH-SPEED STRIPS




NRZ	PAM 4
28 Gbps	56 Gbps

FEATURES & BENEFITS

Edge Rate® rugged high-speed connector strips are designed for high speed, high cycle applications, and enabled by Samtec's signal integrity-optimized Edge Rate® contact system.


- Choice of 0.50 mm, 0.635 mm or 0.80 mm pitch
- 0.50 mm pitch system offers up to 40% PCB space savings vs. 0.80 mm pitch
- 0.635 mm pitch system with extremely slim 2.5 mm body width
- Rugged latching, locking and 360° shielding
- Up to 1.5 mm contact wipe; robust when "zippered" during unmating
- Compatible with UMPT/UMPS for power/signal flexibility

EDGE
RATE
CONTACT




Signal integrity-optimized Edge Rate® contact system reduces broadside coupling

EDGE RATE® STACK HEIGHT FLEXIBILITY (actual size in mm)





Sockets shown actual size with 40 total positions




KEY SPECIFICATIONS


SERIES	PITCH	STACK HEIGHTS	TOTAL PINS / PAIRS	INSULATOR MATERIAL	TERMINAL MATERIAL	PLATING	OPERATING TEMP RANGE	LEAD-FREE SOLDERABLE
ERM5 / ERF5	0.50 mm	7-12 mm	20-150	Black LCP	Phosphor Bronze or BeCu (ERM5), BeCu (ERF5)	Au or Sn over 50 μ" (1.27 μm) Ni	-55 °C to +125 °C	Yes
ERM6 / ERF6	0.635 mm	5 mm	20-120		Copper Alloy			
ERM8 / ERF8	0.80 mm	7-18 mm	10-200		Phosphor Bronze or BeCu (ERM8), BeCu (ERF8)			

(0.80 mm) .0315" PITCH • RUGGED HIGH-SPEED HEADERS & SOCKETS

TYPE	POSITIONS PER ROW	LEAD STYLE	PLATING OPTION	DV	OPTIONS	"X"R
ERM8 = Header	-005, -010, -011, -013, -020, -025, -030, -035, -040, -049, -050, -060, -070, -075, -100	SPECIFY LEAD STYLE FROM CHART	-L = 10 μ" (0.25 μm) Gold on contact, Matte Tin on tail -S = 30 μ" (0.76 μm) Gold on contact, Matte Tin on tail		-DS = Differential Pair (ERM8 -05.0 Lead Style with -010, -013, -025, -049 Positions only) -L = Latching (ERM8-05.0 & -09.0 Lead Styles only & -EGP Option N/A) (ERF8-05.0 Lead Style only and -L to -EGP Option N/A) -EGP = Extended Guide Post (ERM8-05.0 & ERF8-07.0 Lead Style Only & -L Option N/A) -DSP = Differential Pair with Extended Guide Post (ERM8 -05.0 Lead Style with -013 and -025 Positions only) -K = Polyimide Film Pick & Place Pad (-02.0 Lead Style N/A) -P = Pick & Place Pad (ERM8 and -02.0 & -05.0 Lead Styles only)	-TR = Tape & Reel -FR = Full Reel Tape & Reel (must order maximum quantity per reel; contact Samtec for quantity breaks)
ERF8 = Socket	(100 Position Only Available with ERM8-09.0 & ERF8-05.0 Lead Styles; -L or -EGP N/A)					
ERM8 Board Mates: ERF8 ERM8 Cable Mates: ERCD, ERDP						

View complete specifications at: samtec.com?ERM8

ERF8 Board Mates: ERM8	
ERF8 Cable Mates: ERCD, ERDP	


View complete specifications at: samtec.com?ERF8

Note:
Some lengths, styles and options are non-standard, non-returnable.

See pg 52-53 for Right-Angle &
Edge Mount options, pg 54 for
Shielded options.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[ERF8-025-09.0-L-DV-K-TR](#)