



**Product:** RSP20-11003Z6TT-SK9V9HSE2S

**Configurator:** RSP20-11003Z6TT-SK9V9HSE2S

**Configurator Description**

The RSP series features hardened, compact managed industrial DIN rail switches with Fast and Gigabit speed options. These switches support comprehensive redundancy protocols like PRP (Parallel Redundancy Protocol), HSR (High-availability Seamless Redundancy), DLR (Device Level Ring) and FuseNet™ and provide an optimum degree of flexibility with several thousand variants.

**Technical Specifications**

**Product description**

Description	Managed Industrial Switch for DIN Rail, fanless design Fast Ethernet Type
Part Number	942053002
Port type and quantity	11 Ports in total: 8 x 10/100BASE TX / RJ45; 3 x SFP slot FE (100 Mbit/s)

**More Interfaces**

Power supply/signaling contact	1 x plug-in terminal block, 3-pin; 1 x plug-in terminal block, 2-pin
V.24 interface	1 x RJ11 socket
SD-card slot	1 x SD card slot to connect the auto configuration adapter ACA31

**Network size - length of cable**

Twisted pair (TP)	0-100
Single mode fiber (SM) 9/125 µm	see SFP fiber module M-SFP-xx / M-Fast SFP-xx
Single mode fiber (LH) 9/125 µm (long haul transceiver)	see SFP fiber module M-SFP-xx / M-Fast SFP-xx
Multimode fiber (MM) 50/125 µm	see SFP fiber module M-SFP-xx / M-Fast SFP-xx
Multimode fiber (MM) 62.5/125 µm	see SFP fiber module M-SFP-xx / M-Fast SFP-xx

**Network size - cascadiability**

Line - / star topology	any
------------------------	-----

**Power requirements**

Operating Voltage	1 x 60 - 250 VDC (48V - 320 VDC) and 110 - 230 VAC (88 - 265 VAC)
Power consumption	15 W
Power output in BTU (IT)/h	51

**Software**

Switching	Independent VLAN Learning, Fast Aging, Static Unicast/Multicast Address Entries, QoS / Port Prioritization (802.1D/p), TOS/DSCP Prioritization, Interface Trust Mode, CoS Queue Management, Queue-Shaping / Max. Queue Bandwidth, Flow Control (802.3X), Egress Interface Shaping, Ingress Storm Protection, Jumbo Frames, VLAN (802.1Q), VLAN Unaware Mode, Voice VLAN, IGMP Snooping/Querier per VLAN (v1/v2/v3), Unknown Multicast Filtering, Multiple VLAN Registration Protocol (MVRP), Multiple MAC Registration Protocol (MMRP), Multiple Registration Protocol (MRP) , Layer 2 Loop Protection
Redundancy	Link Aggregation with LACP, Link Backup, Media Redundancy Protocol (MRP) (IEC62439-2), RSTP 802.1D-2004 (IEC62439-1), RSTP Guards
Management	Dual Software Image Support, TFTP, SFTP. SCP. LLDP (802.1AB), LLDP-MED, SSHv2, V.24, HTTP, HTTPS, Traps, SNMP v1/v2/v3, Telnet OPC-UA Server
Diagnostics	Management Address Conflict Detection, MAC Notification, Signal Contact, Device Status Indication, TCPDump, LEDs, Syslog, Persistent Logging on ACA, Port Monitoring with Auto-Disable, Link Flap Detection, Overload Detection, Duplex Mismatch Detection, Link Speed and Duplex Monitoring, RMON (1,2,3,9), Port Mirroring 1:1, Port Mirroring 8:1, Port Mirroring N:1, System Information, Self-Tests on Cold Start, Copper Cable Test, SFP Management, Configuration Check Dialog, Switch Dump, Snapshot Configuration Feature

Configuration	Automatic Configuration Undo (roll-back), Configuration Fingerprint, Text-based Configuration File (XML), BOOTP/DHCP Client with Auto-Configuration, DHCP Server: per Port, DHCP Server: Pools per VLAN, AutoConfiguration Adapter ACA31 (SD card), HiDiscovery, DHCP Relay with Option 82, Command Line Interface (CLI), CLI Scripting, Full-featured MIB Support, Web-based Management, Context-sensitive Help
Security	MAC-based Port Security, Port-based Access Control with 802.1X, Guest/unauthenticated VLAN, Integrated Authentication Server (IAS), RADIUS VLAN Assignment, Denial-of-Service Prevention, VLAN-based ACL, Ingress VLAN-based ACL, Basic ACL, Access to Management restricted by VLAN, Device Security Indication, Audit Trail, CLI Logging, HTTPS Certificate Management, Restricted Management Access, Appropriate Use Banner, Configurable Password Policy, Configurable Number of Login Attempts, SNMP Logging, Multiple Privilege Levels, Local User Management, Remote Authentication via RADIUS, User Account Locking
Time synchronisation	PTPv2 Transparent Clock two-step, PTPv2 Boundary Clock, Buffered Real Time Clock, SNTP Client, SNTP Server
Industrial Profiles	EtherNet/IP Protocol, IEC61850 Protocol (MMS Server, Switch Model), ModbusTCP, PROFINET IO Protocol
Miscellaneous	Manual Cable Crossing, Port Power Down

Ambient conditions

Operating temperature	0-+60 °C
Storage/transport temperature	-40-+70 °C
Relative humidity (non-condensing)	10-95 %

Mechanical construction

Dimensions (WxHxD)	90 mm x 164 mm x 120 mm
Weight	1200 g
Mounting	DIN rail
Protection class	IP20

Mechanical stability

IEC 60068-2-6 vibration	1 mm, 2 Hz-13.2 Hz, 90 min.; 0.7 g, 13.2 Hz-100 Hz, 90 min.; 3.5 mm, 3 Hz-9 Hz, 10 cycles, 1 octave/min.; 1 g, 9 Hz-150 Hz, 10 cycles, 1 octave/min
IEC 60068-2-27 shock	15 g, 11 ms duration, 18 shocks

EMC interference immunity

EN 61000-4-2 electrostatic discharge (ESD)	8 kV contact discharge, 15 kV air discharge
EN 61000-4-3 electromagnetic field	35 V/m (80-2700 MHz); 1 kHz, 80% AM
EN 61000-4-4 fast transients (burst)	4 kV power line, 4 kV data line
EN 61000-4-5 surge voltage	power line: 2 kV (line/earth), 1 kV (line/line), 1 kV data line IEEE1613: power line 5 kV (line/earth)
EN 61000-4-6 Conducted Immunity	3 V (10 kHz-150 kHz), 10 V (150 kHz-80 MHz)
EN 61000-4-16 mains frequency voltage	30 V, 50 Hz continous; 300 V, 50 Hz 1 s

EMC emitted immunity

EN 55032	EN 55032 Class A
----------	------------------

Approvals

Basis Standard	CE, FCC, EN61131
Substation	IEC 61850-3, IEEE 1613

Reliability

Guarantee	60 months (please refer to the terms of guarantee for detailed information)
-----------	---

Scope of delivery and accessories

Accessories	Rail power supply RPS 30, RPS 80 EEC, RPS 120 EEC, terminal cable, network management Industrial HiVision, auto-configuration adpater ACA31, 19" installation frame
Scope of delivery	Device, terminal blocks , General safety instructions

Further Instructions

Product Documentation	<a href="https://www.doc.hirschmann.com/index.html">https://www.doc.hirschmann.com/index.html</a>
Certificates	<a href="https://www.doc.hirschmann.com/certificates.html">https://www.doc.hirschmann.com/certificates.html</a>

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirschmann:](#)

[RSP20-11003Z6TT-SK9V9HSE2AXX.X](#)