



0906 UAC 301 | 0906 UAC 302 | 0906 UAC 303




DeviceNet Receptacles, Panel Feed Through, 7/8"

5-Pole, Male

DeviceNet, 3-, 4-, and 5-pole, male to female 7/8" panel feed through receptacle.


0906 UAC 303




Pin Assignments

Face Views, 7/8"


3 pole



4 pole



5 pole





Be Certain with Belden

DeviceNet Receptacles, 7/8"

0906 UAC 301 | 0906 UAC 302 | 0906 UAC 303

Technical Data

Environmental

Degree of protection IP 67 / NEMA 6P
Operating temperature range -25°C (-13°F) / +90°C (+194°F)

Materials

Contacts Brass, gold over nickel plated
Insert PUR, yellow
O-ring Viton
Shell Brass, nickel plated
Panel nut Zinc diecast, zinc plated

Electrical

Current rating 8 A
Voltage rating 600 V

Part Number	Pins	Characteristics
0906 UAC 301	3	  
0906 UAC 302	4	  
0906 UAC 303	5	  

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lumberg Automation:](#)

[0906 UAC 303](#) [0906 UAC 302](#) [0906 UAC 301](#)