

## HC2759 Multi-Conductor - New Generation®

For more Information  
please call

1-800-Belden1

**General Description:**

14 AWG stranded (105x34) bare copper conductors, PVC insulation, conductors cabled, PVC jacket.

**Usage (Overall)**

Suitable Applications: Intercom/PA Systems, Sound/Audio Systems

**Physical Characteristics (Overall)****Conductor**

AWG:

# Conductors	AWG	Stranding	Dia. (in.)
2	14	105x34	.074

Total Number of Conductors: 2

**Insulation**

Insulation Material:

Insulation Material	Dia. (in.)
PO - Polyolefin	.105

**Outer Shield**

Outer Shield Material:

Outer Shield Material
Unshielded

**Outer Jacket**

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

**Overall Cable**

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Red

Overall Nominal Diameter: 0.264 in.

**Mechanical Characteristics (Overall)**

Operating Temperature Range: -20°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 40.300 lbs/1000 ft.

Max. Recommended Pulling Tension: 104 lbs.

Min. Bend Radius/Minor Axis: 2.700 in.

**Applicable Specifications and Agency Compliance (Overall)****Applicable Standards & Environmental Programs**

NEC/(UL) Specification: CL3, CM

CEC/C(UL) Specification: CM

## HC2759 Multi-Conductor - New Generation®

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 07/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire &amp; Cable): Yes

MII Order #39 (China RoHS): Yes

## Flame Test

UL Flame Test: UL1581 Vertical Flame and FT-1 Flame Test

CSA Flame Test: FT1

## Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: Yes

## Plenum/Non-Plenum

Plenum (Y/N): No

Plenum Number: 6200FE

## Electrical Characteristics (Overall)

## Nom. Inductance:

Inductance (μH/ft)

.16

## Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

20.5

## Nominal Velocity of Propagation:

VP (%)

66

## Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

2.5

## Max. Operating Voltage - UL:

Voltage

300 V RMS

## Max. Recommended Current:

Current

13 Amps per conductor @ 25°C

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 1    Revision Date: 09-02-2009

© 2019 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

## HC2759 Multi-Conductor - New Generation®

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[HC2759 1SLU500](#) [HC2759 004U500](#)