

HCMD-10-S-03.00-01

(2.54 mm) .100"

IDC SOCKET & TERMINAL CABLE

Mates with:

TSW, MTSW, TST, HTST, EW, ZST, MTLW, TSM, EJH-02 (HCSD only)

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?HCSD or www.samtec.com?HCSS

HCSD, HCSS

Insulator Material: Black Liquid Crystal Polymer
Flammability Rating: UL 94V-0

Temperature Range: -20 °C to +105 °C (Rainbow Cable)
 -40 °C to +105 °C (Gray Cable)

Voltage Rating: 425 VAC/600 VDC

Contact: Phosphor Bronze
Plating: 10 μm (0.25 μm) Au on contact area, 150 μm (3.81 μm) Sn on balance over 50 μm (1.27 μm) Ni.

Lead Size Range: .024" (0.61 mm) SQ to .026" (0.66 mm) SQ

Lead Insertion Depth: .185" (4.70 mm) to .250" (6.35 mm)

Wire: 28 AWG 7/36 stranded Tinned Copper
RoHS Compliant: Yes

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?HCMD or www.samtec.com?HCMS

HCMD, HCMS

Insulator Material: Black Liquid Crystal Polymer
Flammability Rating: UL 94V-0

Temperature Range: -20 °C to +105 °C (Rainbow Cable)
 -40 °C to +105 °C (Gray Cable)

Voltage Rating: 425 VAC/600 VDC

Terminal: Phosphor Bronze
Plating: Sn over 50 μm (1.27 μm) Ni

Wire: 28 AWG 7/36 stranded Tinned Copper
RoHS Compliant: Yes

Note: IDC assemblies are non-standard, non-returnable.

TYPE STRIP	ROW OPTION	NO. PINS PER ROW	END ASSEMBLY	ASSEMBLED LENGTH
	<p>S = Single</p> <p>D = Double (Color coded cable N/A for 36 pins/row. See -G option.)</p>	<p>-05, -08, -10, -12, -13, -15, -17, -20</p>		<p>-"XX.XX" = Assembled Length</p> <p>Assembled Length in INCHES (±1/8") 2 inches minimum</p>

HCM = Male Strip

LEAD STYLE	A
-01	(3.05) .120
-02	(5.84) .230

HCS = Socket Strip

-S = Single End

Socket or Male Plug on one end

-D = Double End

Socket or Male Plug on each end

-T = Transfer End

Male Plug on one end with socket on other.
Begin part number with HCM.

HCSS-15-S-03.00-01-G

HCSD-10-S-03.00-01-T-G

HCMD, HCMS, HCSD, HCSS SERIES

LEAD STYLE

PLATING OPTION

NOTCH POLARIZATION

OTHER OPTIONS

-01

= HCSS/HCSD or (3.05 mm) .120" tail for HCMS/HCMD

-02

= (5.84 mm) .230" tail HCMS/HCMD only


-S

= 10 μm (0.25 μm) Gold on contact area or tail, Tin on balance (Standard on HCSS & HCSD. Leave blank)

-T

= Tin (Standard on HCMS & HCMD. Leave blank)


-N = Notch Polarization



Required for HCSS and HCSD. (Not available on HCMS or HCMD, unless Transfer, then only the socket is polarized.)

-P "XX"

= Position Polarization



Specify "XX" as position. For Double the same position will be polarized on both ends. (Not available on HCM, unless Transfer, then only the socket is polarized)

-G


= Gray Cable

Standard cable is color coded. Specify -G for Gray cable with one red edge.

-ST "X"

= Stripped & Tinned

Specify Suffix from table. All dimensions are ± 1/16" (1.59 mm). Not available in 28 positions and higher.




-ST8	1/8" (3.18)
-ST4	1/4" (6.35)
-ST2	1/2" (12.70)
-ST3	3/8" (9.53)

-B "XX"

= Breakout

Specify "XX" as number of conductors to be broken out.



Breakout starts with Number 1 lead indicated by brown wire or red stripe. Shown on top side.


-RW

= Reversed Wiring

#1 wire opposite position #1

-S "XX"


= Daisy Chain Single



When mating double row connector with two single row connectors, the outer most single will be connected to Conductor #1 and the inside single to Conductor #2.

-D "XX"

= Daisy Chain, Double




-W "XX"

= Wiring Reversed Daisy Chain, Single

Same as -S "XX" except outer strip connected to conductor #2 and inside strip connected to conductor #1.


-R

= Reversed



-M


= Middle Reversed



Requires -SXX, -WXX or -DXX

-O

= Outside Reversed



Requires -SXX, -WXX or -DXX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[HCMD-05-01](#) [HCMD-13-01](#) [HCMD-20-01](#) [HCMD-20-S-10.00-02](#) [HCMD-32-02-S](#) [HCMD-20-02-S](#) [HCMD-04-S-18.00-01](#) [HCMD-04-T-04.00-01-G](#) [HCMD-05-D-05.00-01-S](#) [HCMD-05-S-36.00-01-ST2](#) [HCMD-05-T-02.00-01-T-N-G-R](#) [HCMD-05-T-06.00-01-R](#) [HCMD-05-T-06.00-01-S-G](#) [HCMD-06-S-15.00-01](#) [HCMD-07-T-03.00-01-S](#) [HCMD-07-T-07.00-01-R](#) [HCMD-08-S-36.00-01-ST2](#) [HCMD-08-T-24.00-02](#) [HCMD-10-D-09.00-01-S](#) [HCMD-10-T-02.00-01-G](#) [HCMD-10-T-02.00-01-R](#) [HCMD-10-T-02.00-01-T-R](#) [HCMD-10-T-04.30-01-S](#) [HCMD-10-T-04.30-01-S-G](#) [HCMD-12-02](#) [HCMD-12-D-03.50-02-S-R](#) [HCMD-12-D-06.00-02-S](#) [HCMD-12-T-10.00-01-T-P24](#) [HCMD-13-T-04.00-01-T](#) [HCMD-13-T-04.00-02-G](#) [HCMD-13-T-16.00-02-R](#) [HCMD-14-02-S](#) [HCMD-14-T-02.00-02-T-N](#) [HCMD-15-D-12.00-01-S](#) [HCMD-15-S-06.00-02](#) [HCMD-15-T-03.30-02-N-R-RW](#) [HCMD-15-T-03.60-01-S-G-R](#) [HCMD-15-T-03.65-02-S-N-R-RW](#) [HCMD-15-T-18.00-01](#) [HCMD-17-T-02.50-02-T-R](#) [HCMD-17-T-03.00-01](#) [HCMD-17-T-03.00-01-R](#) [HCMD-17-T-06.00-01-N](#) [HCMD-17-T-06.00-01-R](#) [HCMD-17-T-13.00-02-N-G-R-RW](#) [HCMD-20-D-05.00-01-S-G](#) [HCMD-20-D-05.00-02](#) [HCMD-20-S-03.00-02-S-G-RW](#) [HCMD-20-T-03.00-01-S](#) [HCMD-20-T-06.00-01](#) [HCMD-20-T-06.00-01-S-G](#) [HCMD-20-T-12.00-02](#) [HCMD-20-T-36.00-02-N](#) [HCMD-21-02-S](#) [HCMD-02-S-05.00-02](#) [HCMD-05-01-S](#) [HCMD-05-S-03.00-01](#) [HCMD-05-T-04.00-01-N](#) [HCMD-05-T-04.50-01-R](#) [HCMD-05-T-08.50-01-S-G](#) [HCMD-06-D-02.00-01-G](#) [HCMD-06-T-24.00-01-T](#) [HCMD-06-T-24.00-02](#) [HCMD-07-T-04.00-02-N-G](#) [HCMD-08-T-14.00-01-S](#) [HCMD-09-S-05.00-02](#) [HCMD-09-S-18.00-01](#) [HCMD-10-S-05.00-01](#) [HCMD-10-T-03.00-01-R](#) [HCMD-10-T-06.00-01-G](#) [HCMD-10-T-06.00-01-N](#) [HCMD-10-T-10.00-01-N-G](#) [HCMD-10-T-12.00-01](#) [HCMD-11-01](#) [HCMD-11-02](#) [HCMD-11-S-06.50-01-ST4](#) [HCMD-13-T-10.00-01](#) [HCMD-13-T-10.00-01-S](#) [HCMD-13-T-10.00-02-T-R](#) [HCMD-15-02](#) [HCMD-15-02-S](#) [HCMD-15-T-06.00-01-G](#) [HCMD-16-02-S](#) [HCMD-16-T-03.00-02](#) [HCMD-17-T-04.44-01-G-P14-R](#) [HCMD-17-T-05.00-01](#) [HCMD-17-T-05.00-01-R](#) [HCMD-17-T-24.00-01](#) [HCMD-20-D-07.50-01](#) [HCMD-20-D-10.00-02-R](#) [HCMD-20-S-12.00-01-ST4](#) [HCMD-20-S-12.00-02](#) [HCMD-20-T-04.00-01-S-G](#) [HCMD-20-T-04.00-01-T](#) [HCMD-20-T-10.00-01-N-G-RW](#) [HCMD-20-T-18.00-02-S](#) [HCMD-20-T-22.00-01-S-N](#) [HCMD-12-T-06.00-02-S](#) [HCMD-12-T-13.00-02](#) [HCMD-12-T-24.00-01](#)