



RKU 6-204/...M

Power supply cable for Remote Bus modules, single ended with 6-pole female M23 connector, 5 conductor cable.

RSU 6-RKU 6-204/0.6 M

Power supply cable for Remote Bus modules, double ended with 6-pole male and female M23 connectors, 5 conductor cable.

M23 Male/Female connector, 5 poles	Signal	Leads
Pin 1	earth	green/yellow
Pin 2	+24 V ¹	1
Pin 3	GND (0 V) ¹	2
Pin 4	+24 V ²	3
Pin 5	GND (0 V) ²	4
Pin 6	n.c.	

¹ = Installation remote bus

² = Sensors local / Module supply



Technical Data	
Conductor	5 x 1.00 mm ² bare, very finely stranded wires acc. to VDE 0295 KL6
Insulation of lead	Polypropylen
Colors of the leads	green/yellow other wires black with numbers
Outer jacket	PUR, black Ø 7.8 mm
Electrical data	
Nominal voltage	≤ 300 V
Test voltage	2 kV eff.
Resistance of conductor	≤ 19.5 Ω/km
Insulation resistance	≤ 10 MΩ/km
Mechanical data	
Bending radius	min. 80 mm
Temperature range static	- 40°C(-40°F) /+90°C(+194°F)
Temperature range moved	+ 5°C(+41°F) /+90°C(+194°F)

Further details
 Inflammability acc. to DIN VDE 0472-804 test type B and suitable for C-tracks. Resistant to oil acc to DIN VDE 0472-803 and provides good resistance to chemicals, hydrolysis and microbes.

Part Number		
0955 204 000/...M		 
RKU A 6-204/...M	RSU 6-RKU A 6-204/0.6 M	 

Standard Cable Lengths: 5 M / 10 M / 15 M
 Other cable lengths or cable specifications are available upon request.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lumberg Automation:](#)

[RKU 6-204/15 M](#) [RKU 6-204/10 M](#) [RKU 6-204/20 M](#) [RKU 6-204/5 M](#)