

**FLEX
STACK**
(1.27 mm) .050"

MTMS-130-02-G-D-100

MTMS-110-02-G-D-100

MTMS-125-51-G-S-200

MTMS, HMTMS SERIES

MODIFIED MICRO TERMINAL

SPECIFICATIONS

For complete specifications see www.samtec.com?MTMS or www.samtec.com?HMTMS

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over 50 μ " (1.27 μ m) Ni

Operating Temp Range:

-55 °C to +105 °C with Tin
-55 °C to +125 °C with Gold

RoHS Compliant:

Yes

Mates with:

SMS, SLM, RSM

PROCESSING

Lead-Free Solderable:

Yes

RECOGNITIONS




For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594

ALSO AVAILABLE (MOQ Required)

- Other platings



Tail DIA is .020" (0.51 mm) for min .120" (3.05 mm).
Balance of tail is .018" (0.46 mm) SQ.

LEAD STYLE	OAL	B (Maximum when C = (3.05 mm) .120")
-01	(11.43) .450	(5.84) .230
-02	(8.13) .320	(2.54) .100
-25*	(8.38) .330	(3.18) .125
-51	(10.41) .410	(4.83) .190
-52	(10.80) .425	(5.21) .205
-53	(12.83) .505	(7.24) .285
-54	(14.10) .555	(8.51) .335
-55	(15.49) .610	(9.91) .390
-56	(15.88) .625	(10.29) .405
-57	(16.51) .650	(10.92) .430
-58	(17.91) .705	(12.32) .485
-59	(19.18) .755	(13.59) .535
-60	(20.96) .825	(15.37) .605

*Style -25 tail C = (1.02 mm) .040" min is available.

Note:
This Series is non-standard, non-returnable.

WWW.SAMTEC.COM

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[HMTMS-110-54-G-D-335](#) [HMTMS-106-52-SM-S-205](#) [HMTMS-132-53-SM-S-285](#) [HMTMS-106-01-S-S-230](#) [HMTMS-105-25-S-D-125-007](#) [HMTMS-107-25-S-S-125](#) [HMTMS-108-25-S-S-125](#) [HMTMS-108-53-S-D-285](#) [HMTMS-110-02-G-D-100](#) [HMTMS-135-53-G-S-285](#) [HMTMS-110-52-G-D-205](#) [HMTMS-111-01-G-S-230](#) [HMTMS-105-02-G-D-100](#) [HMTMS-112-01-G-S-215](#) [HMTMS-112-52-T-S-205](#) [HMTMS-108-02-S-S-100](#) [HMTMS-116-02-G-S-030](#) [HMTMS-115-25-S-D-125](#) [HMTMS-120-02-G-S-100](#) [HMTMS-150-54-S-S-100](#) [HMTMS-106-52-S-S-195](#) [HMTMS-116-02-TM-S-100](#) [HMTMS-110-25-S-S-125](#) [HMTMS-101-25-G-S-110](#) [HMTMS-136-57-S-D-430](#) [HMTMS-110-56-S-D-405](#) [HMTMS-108-51-S-S-180](#) [HMTMS-105-55-S-D-370](#) [HMTMS-107-53-G-S-270](#) [HMTMS-108-51-S-S-190](#) [HMTMS-115-56-S-D-405](#) [HMTMS-104-25-G-S-110](#) [HMTMS-115-02-TM-S-100](#) [HMTMS-102-25-G-S-110](#) [HMTMS-123-25-G-S-110](#) [HMTMS-102-52-G-S-205](#) [HMTMS-106-01-SM-S-230](#) [HMTMS-110-60-G-D-605](#) [HMTMS-118-02-SM-S-100](#) [HMTMS-117-52-G-D-205](#) [HMTMS-130-54-G-D-335](#) [HMTMS-130-55-G-D-390](#) [HMTMS-130-54-S-D-335](#) [HMTMS-102-53-G-S-285](#) [HMTMS-104-01-S-S-230](#) [HMTMS-105-25-S-D-125-009](#) [HMTMS-105-25-SM-D-125-009](#) [HMTMS-112-02-SM-S-100](#) [HMTMS-116-02-G-D-100](#) [HMTMS-136-57-G-D-430](#) [HMTMS-150-01-S-S-215](#) [HMTMS-108-58-S-S-485](#) [HMTMS-115-25-T-S-115](#) [HMTMS-120-25-T-D-115](#) [HMTMS-102-25-T-D-115](#) [HMTMS-109-53-G-D-285](#) [HMTMS-116-02-G-D-015](#) [HMTMS-140-53-G-S-285](#) [HMTMS-110-02-G-S-100](#) [HMTMS-108-25-G-S-125](#) [HMTMS-101-54-L-S-230](#) [HMTMS-109-25-G-S-125](#) [HMTMS-150-54-L-S-230](#) [HMTMS-106-02-L-D-100](#) [HMTMS-123-56-G-S-400](#) [HMTMS-125-56-G-S-400](#) [HMTMS-150-25-G-S-125](#) [HMTMS-108-58-G-S-485](#) [HMTMS-108-57-S-S-205](#) [HMTMS-110-51-T-D-120-006](#) [HMTMS-103-01-G-D-230](#) [HMTMS-108-57-S-S-255](#) [HMTMS-112-52-L-D-205](#) [HMTMS-130-25-L-D-115](#) [HMTMS-145-52-G-D-205](#) [HMTMS-109-55-L-D-315](#) [HMTMS-124-53-S-D-285](#) [HMTMS-145-25-L-D-115](#) [HMTMS-108-53-S-D-100](#) [HMTMS-140-52-G-D-205](#) [HMTMS-101-54-L-D-335](#) [HMTMS-105-25-S-D-125](#) [HMTMS-130-55-S-D-390](#) [HMTMS-120-25-T-S-125](#) [HMTMS-115-25-L-D-125](#) [HMTMS-115-53-L-D-285](#) [HMTMS-120-25-S-S-125](#) [HMTMS-117-51-G-D-155](#)