




Q STRIP® COAX CABLE ASSEMBLIES

14
Gbps



(0.50 mm) .0197" & (0.80 mm) .0315" PITCH • HQCD/EQCD SERIES

HQCD


Mates:
QTH, QSH

EQCD

Mates:
QTE, QSE

SPECIFICATIONS

Cable:
38 AWG micro coax ribbon
Signal Routing:
50 Ω Single-Ended
Overall Length:
(95.3 mm) 03.75" to
(1 m) 40" standard
Cable Flexing Life:
>10,000 cycles
Cable Bending Radius:
<2.5mm
Plating:
Au over 50 μ" (1.27 μm) Ni
Current Rating:
EQCD = 500 mA per pin
HQCD = 300 mA per pin
(6 adjacent pins powered)
Cable Propagation Delay:
4.79 nsec/meter
Operating Temp Range:
-25 °C to +105 °C
Unmating Force (-RT1 option):
-RT1 option increases
unmating force up to 50%



**EYE
SPEED
CABLE**



Notes:

Cable lengths longer than
40.00" (1 meter) are not
supported with S.I. test data.

Design your full cable
assembly with Samtec's
High-Speed Cable Builder at
www.samtec.com/cablebuilder

This Series is non-standard,
non-returnable.

END 1 or END 2	SURFACE MOUNT
TTR	Terminal, Top Mount, Notch Right
TTL	Terminal, Top Mount, Notch Left
TBR	Terminal, Bottom Mount, Notch Right
TBL	Terminal, Bottom Mount, Notch Left
STR	Socket, Top Mount, Notch Right
STL	Socket, Top Mount, Notch Left
SBR	Socket, Bottom Mount, Notch Right
SBL	Socket, Bottom Mount, Notch Left

END 1 or END 2	EDGE MOUNT
TEU	Terminal, Edge Mount, Notch Up
TED	Terminal, Edge Mount, Notch Down
SEU	Socket, Edge Mount, Notch Up
SED	Socket, Edge Mount, Notch Down

END1 ONLY	PANEL MOUNT
TPU	Terminal, Panel Mount, Notch Up
TPD	Terminal, Panel Mount, Notch Down
SPU	Socket, Panel Mount, Notch Up
SPD	Socket, Panel Mount, Notch Down

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[HQCD-030-06.00-TED-SED-1-B](#) [HQCD-030-06.00-TTR-STR-1](#) [HQCD-090-40.00-TED-SED-1](#) [HQCD-090-40.00-TED-SED-1-B](#) [HQCD-090-40.00-TTR-STR-1](#) [HQCD-090-40.00-TTR-STR-1-B](#) [HQCD-090-12.00-TED-SED-1](#) [HQCD-090-12.00-TED-SED-1-B](#) [HQCD-090-12.00-TTR-STR-1](#) [HQCD-090-12.00-TTR-STR-1-B](#) [HQCD-090-06.00-TED-SED-1-B](#) [HQCD-090-06.00-TTR-STR-1](#) [HQCD-090-06.00-TTR-STR-1-B](#) [HQCD-060-40.00-TED-SED-1](#) [HQCD-060-40.00-TED-SED-1-B](#) [HQCD-060-40.00-TTR-STR-1](#) [HQCD-060-40.00-TTR-STR-1-B](#) [HQCD-060-12.00-TTR-STR-1](#) [HQCD-060-12.00-TTR-STR-1-B](#) [HQCD-060-06.00-TTR-STR-1](#) [HQCD-060-06.00-TTR-STR-1-B](#) [HQCD-030-40.00-TED-SED-1](#) [HQCD-030-40.00-TED-SED-1-B](#) [HQCD-030-40.00-TTR-STR-1](#) [HQCD-030-40.00-TTR-STR-1-B](#) [HQCD-030-06.00-TTR-STR-1-B](#) [HQCD-030-12.00-TTR-STR-1](#) [HQCD-030-12.00-TTR-STR-1-B](#) [HQCD-030-12.00-TTR-STR-3](#) [HQCD-030-12.00-TTR-STR-3-B](#) [HQCD-030-40.00-TTR-STR-3](#) [HQCD-030-40.00-TTR-STR-3-B](#) [HQCD-060-06.00-TTR-STR-3](#) [HQCD-060-06.00-TTR-STR-3-B](#) [HQCD-060-12.00-TTR-STR-3](#) [HQCD-060-12.00-TTR-STR-3-B](#) [HQCD-060-40.00-TTR-STR-3](#) [HQCD-060-40.00-TTR-STR-3-B](#) [HQCD-090-06.00-TTR-STR-3](#) [HQCD-090-06.00-TTR-STR-3-B](#) [HQCD-090-12.00-TTR-STR-3](#) [HQCD-090-12.00-TTR-STR-3-B](#) [HQCD-090-40.00-TTR-STR-3](#) [HQCD-090-40.00-TTR-STR-3-B](#)