


GENERATE[®]

HIGH-SPEED EDGE CARD SYSTEMS

0.60 mm, 0.80 mm and 1.00 mm PITCH





**EDGE
RATE[®]**
CONTACT


FEATURES & BENEFITS

- Maximum Design Flexibility
- Up to 64 Gbps PAM4 performance
- PCI Express[®] 3.0, 4.0, 5.0 and 6.0
- Edge Rate[®] contacts optimized for signal integrity performance and high-cycle life
- Up to 200 positions available
- Vertical, right-angle, edge mount, pass-through orientations
- Power/signal combo, press-fit tails, rugged weld tabs, locks and latches
- Mating cable assemblies available


The PCI Express[®] design marks are registered trademarks and/or service marks of PCI-SIG.



Rugged tucked beam technology (HTEC8)



Differential pair for increased speed (HSEC8-DP)



Custom designs allow for misalignment in the X-Y axes (HSEC1)

KEY SPECIFICATIONS

SERIES	PITCH	TOTAL POSITIONS	INSULATOR MATERIAL	CONTACT MATERIAL	OPERATING TEMP RANGE	CURRENT RATING	VOLTAGE RATING	LEAD-FREE SOLDERABLE
HSEC6	0.60 mm	56-168	Black LCP	Copper Alloy	-55 °C to +125 °C	1.9 A (2 pins)	240 VAC/339 VDC	Yes
HTEC8	0.80 mm	20-200	Black LCP	Copper Alloy	-55 °C to +125 °C	3.0 A (2 pins)	215 VAC/304 VDC	Yes
HSEC8-DV	0.80 mm	18-200	Black LCP	BeCu	-55 °C to +125 °C	2.8 A (2 pins)	240 VAC/339 VDC	Yes
HSEC8-RA	0.80 mm	18-120	Black LCP	BeCu	-55 °C to +125 °C	2.6 A (2 pins)	175 VAC/247 VDC	Yes
HSEC8-EM	0.80 mm	20-120	Black LCP	BeCu	-55 °C to +125 °C	2.8 A (2 pins)	240 VAC/339 VDC	Yes
HSEC8-PE	0.80 mm	20-40	Black LCP	BeCu	-55 °C to +125 °C	2.8 A (2 pins)	240 VAC/339 VDC	Yes
HSEC8-PV	0.80 mm	40-80	Black LCP	BeCu	-55 °C to +125 °C	3.2 A (2 pins)	215 VAC/304 VDC	Yes
HSEC8-DP	0.80 mm	16-112	Black LCP	BeCu	-55 °C to +125 °C	2.7 A (2 pins)	235 VAC/332 VDC	Yes
HSEC1	1.00 mm	20-140	Black LCP	Phosphor Bronze	-55 °C to +125 °C	2.2 A (2 pins)	215 VAC/304 VDC	Yes

(0.80 mm) .0315" PITCH • RIGHT-ANGLE & EDGE MOUNT SOCKET

HSEC8	1	POSITIONS PER ROW	CARD THICKNESS	PLATING OPTION	RA	OTHER OPTIONS	"X"R
-------	---	-------------------	----------------	----------------	----	---------------	------

09, 10, 13,
20, 25, 30,
40, 49, 50, 60

-01
= (1.60 mm) .062"
thick card

-L
= 10 μ" (0.25 μm)
Gold on contact area,
Matte Tin on tail

-S
= 30 μ" (0.76 μm)
Gold on contact area,
Matte Tin on tail

-BL
= Board Locks
(09, 13, 25, 40,
49, 50, 60 only)

-L2
= ECDP Latching
(09, 13, 25, 49 only)


Leave blank for
Tray Packaging

-TR
= Tape & Reel





-FR
= Full Reel
Tape & Reel Packaging
(must order max.
quantity per reel;
contact Samtec for
quantity breaks)

HSEC8-RA

Card Mates:
(1.60 mm) .062"
thick card,
HSC8
Cable Mates:
ECDP



POSITIONS PER ROW	A	B	C
40	(43.80) 1.724	(18.90) .744	(36.60) 1.441
50	(51.80) 2.039	(22.90) .902	(44.60) 1.756
60	(59.80) 2.354	(26.90) 1.059	(52.60) 2.071
40-BL	(51.30) 2.020	(18.90) .744	(36.60) 1.441
50-BL	(59.30) 2.335	(22.90) .902	(44.60) 1.756
60-BL	(67.30) 2.650	(26.90) 1.059	(52.60) 2.071



10, 20 & 30 POSITIONS

View complete specifications at: samtec.com?HSEC8-RA

HSEC8	1	POSITIONS PER ROW	01	PLATING OPTION	D	EM2
-------	---	-------------------	----	----------------	---	-----

10, 20, 30, 40, 50, 60



-L
= 10 μ" (0.25 μm)
Gold on contact area,
Matte Tin on tail

-S
= 30 μ" (0.76 μm)
Gold on contact area,
Matte Tin on tail

-EM2
=(1.60 mm) .062"
thick PCB

HSEC8-EM

Card Mates:
(1.60 mm) .062"
thick card,
HSC8
Cable Mates:
ECDP



POSITIONS PER ROW	A	B
40	(18.90) .744	(36.60) 1.441
50	(22.90) .902	(44.60) 1.756
60	(26.90) 1.059	(52.60) 2.071

View complete specifications at: samtec.com?HSEC8-EM

Note:
Some sizes, styles and
options are non-standard,
non-returnable.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[HSEC8-160-01-S-RA-TR](#) [HSEC8-130-01-S-RA](#) [HSEC8-160-01-S-RA](#) [HSEC8-120-01-S-RA](#) [HSEC8-130-01-L-RA](#)
[HSEC8-140-01-L-RA-TR](#) [HSEC8-125-01-L-RA-L2](#) [HSEC8-160-01-L-RA-TR](#) [HSEC8-150-01-L-RA-TR](#) [HSEC8-160-01-](#)
[L-RA-BL](#) [HSEC8-140-01-L-RA](#) [HSEC8-140-01-S-RA](#) [HSEC8-160-01-L-RA](#) [HSEC8-140-01-L-RA-BL](#) [HSEC8-125-01-](#)
[S-RA-BL](#) [HSEC8-125-01-S-RA-L2](#) [HSEC8-150-01-S-RA](#) [HSEC8-160-01-S-RA-BL](#) [HSEC8-150-01-L-RA-BL](#) [HSEC8-](#)
[130-01-L-RA-TR](#) [HSEC8-149-01-L-RA-L2](#) [HSEC8-140-01-S-RA-TR](#) [HSEC8-120-01-S-RA-TR](#) [HSEC8-125-01-S-RA](#)
[HSEC8-130-01-S-RA-TR](#) [HSEC8-125-01-L-RA-L2-TR](#) [HSEC8-150-01-L-RA](#) [HSEC8-140-01-S-RA-BL](#)