




SS-132-G-2



ESD-115-TT-05

(2.54 mm) .100"

SS, SD, ESD, ESS, HSS SERIES

PRECISION MACHINED SOCKET STRIPS

Mates with:

TS, TD, HTS, BBS,
BBD, BBL, BDL, BHS

SPECIFICATIONS

For complete specifications see www.samtec.com?SS,
www.samtec.com?ESS,
www.samtec.com?SD,
www.samtec.com?ESD or
www.samtec.com?HSS

Insulator Material:

SS, SD, ESS, ESD= Black G.F. Polyester
HSS= Black Liquid Crystal Polymer

Contact:

BeCu

Shell:

Brass except Style 5A
Phosphor Bronze

Plating:

Au over 50 μ " (1.27 μ m) Ni or
Sn over 50 μ " (1.27 μ m) Ni

Operating Temp Range:

-55 °C to +125 °C

Lead Size Range:

(0.38 mm to 0.56 mm)

.015" to .022" DIA

and most IC leads

RoHS Compliant:

Yes

Lead-Free Solderable:

SS, SD, ESS, ESD:

No, Lead Wave only

HSS: Yes

RECOGNITIONS

For complete scope of recognitions see
www.samtec.com/quality



FILE NO. E111594

TYPE STRIP	1	NO. PINS PER ROW	PLATING OPTION	LEAD STYLE	OPTION	OTHER OPTION
------------	---	------------------	----------------	------------	--------	--------------

01 thru 32

=SS, ESS Series

01 thru 36

=HSS, SD & ESD Series

SS

= Standard
Single Row Socket


HSS

= High Temp
Single Row Socket

ESS

= Elevated Single Row Socket

Styles -5A & -05 socket
heads not countersunk.




SD

= Standard Double
Row Socket

ESD

= Elevated Double
Row Socket

Style -5A not available.
Styles -5A & -05 socket
heads not countersunk.



Note:
Some lengths, styles and
options are non-standard,
non-returnable.

**PLATING
OPTION**

-S

= 10 μ " (0.25 μ m) Gold
contact, Tin shell
(Styles 2 & 22 only)

-T

= 30 μ " (0.76 μ m) Gold
contact, Tin shell

-G

= 30 μ " (0.76 μ m)
Gold contact,
10 μ " (0.25 μ m) Gold shell

-TT


= Tin contact and shell
(Styles 1, 2, 4, and 05
except LIF N/A)

LIF= Low Insertion Force

OPTION

**- L = Locking
Socket**


Add -L suffix for locking
lead socket in end positions.
Requires Style -2 or -22 and
.035" $\pm$.003 DIA board hole.



Requires -T Plating Option

**OTHER
OPTION**

**- N
= Non
Flush**




N/A Style -5A

**ALSO AVAILABLE
(MOQ Required)**

- Locking lead option on ESS
and ESD series


-1A, -1B OR -1C

For LIF specify -21A, -21B or -21C
(SS, HSS, SD)



**-2, -22*, -5A,
or -38***


*For LIF specify -22 or -38 (SS, HSS, SD)



Locking lead available. See OPTION.

-03, -04, -05

For LIF specify -23
(ESS, ESD)



LEAD STYLE	A	B	C
-05	(17.86) .703	(13.46) .530	(4.39) .173
-03 or -23	(11.51) .453	(8.38) .330	(3.12) .123
-04	(14.05) .553	(10.92) .430	(3.12) .123

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[HSS-102-G-2](#) [HSS-101-TT-2](#) [HSS-132-G-2](#) [HSS-103-T-2](#) [HSS-109-S-2](#) [HSS-102-TT-2](#) [HSS-105-S-2](#) [HSS-108-G-2](#) [HSS-106-G-2](#) [HSS-136-G-1C](#) [HSS-136-T-1B](#) [HSS-136-T-1B-N](#) [HSS-136-G-1A](#) [HSS-116-T-2](#) [HSS-116-TT-2](#) [HSS-118-G-3](#) [HSS-118-T-2-L](#) [HSS-120-G-2-N](#) [HSS-120-G-38](#) [HSS-120-S-2](#) [HSS-120-TT-2](#) [HSS-123-T-38](#) [HSS-125-G-2-N](#) [HSS-128-T-18](#) [HSS-132-G-1A](#) [HSS-132-G-1B](#) [HSS-132-T-18-N](#) [HSS-136-G-38](#) [HSS-112-T-18](#) [HSS-114-G-1A](#) [HSS-114-G-1B-N](#) [HSS-115-G-2](#) [HSS-115-G-3](#) [HSS-115-T-21B](#) [HSS-116-T-38](#) [HSS-118-T-22](#) [HSS-118-T-22-L](#) [HSS-120-G-7](#) [HSS-123-T-18](#) [HSS-123-T-1A](#) [HSS-125-S-22](#) [HSS-128-T-2](#) [HSS-129-G-2](#) [HSS-132-G-1C](#) [HSS-132-T-2](#) [HSS-132-T-21A](#) [HSS-134-S-22](#) [HSS-134-T-1B](#) [HSS-134-TT-2](#) [HSS-136-G-2-N](#) [HSS-136-G-3](#) [HSS-136-T-38](#) [HSS-120-T-18](#) [HSS-121-G-38](#) [HSS-121-T-22](#) [HSS-122-T-2](#) [HSS-122-TT-1C](#) [HSS-123-G-2-N](#) [HSS-125-G-1B](#) [HSS-125-G-22](#) [HSS-125-T-1B](#) [HSS-127-TT-2](#) [HSS-130-G-1B](#) [HSS-132-G-18](#) [HSS-132-G-21C](#) [HSS-132-S-2](#) [HSS-132-T-38](#) [HSS-136-G-22-N](#) [HSS-136-S-2-N](#) [HSS-136-T-22-N](#) [HSS-113-S-2](#) [HSS-114-T-22](#) [HSS-116-G-1B](#) [HSS-118-G-22-N](#) [HSS-119-T-22](#) [HSS-120-G-2](#) [HSS-124-G-2](#) [HSS-125-G-2](#) [HSS-125-T-2-L](#) [HSS-130-G-1A](#) [HSS-130-T-2-L](#) [HSS-132-T-2-N](#) [HSS-134-G-7](#) [HSS-134-TT-2-N](#) [HSS-136-G-21A](#) [HSS-136-T-18](#) [HSS-136-T-2](#) [HSS-136-TT-18](#) [HSS-114-S-2](#) [HSS-114-T-1A](#) [HSS-114-T-2](#) [HSS-116-G-21A](#) [HSS-116-G-38](#) [HSS-120-T-2](#) [HSS-120-T-21B](#) [HSS-120-T-22](#) [HSS-122-G-2](#) [HSS-122-G-2-N](#) [HSS-124-T-2](#) [HSS-124-T-21A](#)