


THROUGH-HOLE .025" SQ POST HEADER

(2.54 mm) .100" PITCH • TSW/HTSW SERIES



TSW/HTSW

Board Mates:

SSW, SSQ, SSM, ESW, ESQ,
BCS, BSW, CES, SLW

Cable Mates:

IDSD, IDSS

SPECIFICATIONS

Insulator Material:

TSW: PBT

HTSW: Natural LCP

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over 50 μ" (1.27 μm) Ni

Operating Temp Range:

-55 °C to +125 °C with Gold

-55 °C to +105 °C with Tin

Voltage Rating:

550 VAC mated with SSW;

500 VAC mated with BCS;

515 VAC mated with ESQ;

450 VAC -RA/-RE mated

with BCS or SSM;

400 VAC mated with CES

Lead-Free Solderable:

HTSW: Yes

TSW: No, Lead Wave Only

CURRENT RATING (PER PIN)

TSW mated with

ESW	SSW	SLW	SSQ	SSM	BCS	SNT
5.2 A	5.7 A	5.2 A	6.3 A	5.2 A	4.6 A	4.3 A

2 POSITIONS POWERED

ALSO AVAILABLE MOQ Required

Other Platings

OTHER SOLUTIONS

Elevated Right-angle option
Shunts

Note:

Some lengths, styles and
options are non-standard,
non-returnable.

SERIES

TSW

= Standard Strip

HTSW

= Hi-Temp Strip

PIN CENTERS

-1

= .100" (2.54 mm) Centers,
(All positions filled)

-2

= .200" (5.08 mm) Centers,
(Every other position filled)

NO. PINS PER ROW

01 thru 50



= .100" (2.54 mm)
Center Version

02 thru 25

= .200" (5.08 mm)
Center Version

LEAD STYLE

Specify
LEAD STYLE
from chart



Straight Pin Versions

STRAIGHT PIN VERSIONS

LEAD STYLE	A	B	C
*-05	(8.51) .335	(3.30) .130	(2.67) .105
*-06	(7.62) .300	(2.41) .095	(2.67) .105
*-07	(10.92) .430	(2.54) .100	
*-08	(13.46) .530	(5.08) .200	
-09	(18.54) .730	(10.16) .400	
-10	(21.08) .830	(12.70) .500	(5.84) .230
-11	(23.62) .930	(15.24) .600	
-12	(26.16) 1.030	(17.78) .700	
-13	(31.24) 1.230	(22.86) .900	
-14	(13.46) .530	(2.79) .110	(8.13) .320
*-15	(18.54) .730	(13.21) .520	
*-16		(7.87) .310	(8.13) .320
*-17	(21.08) .830	(2.79) .110	(15.74) .620
*-18	(23.62) .930		(18.29) .720

* Available with -LL (Locking Lead) Option


Specify -07 for best mate with IDXX Series IDC Cable

STRAIGHT PIN VERSIONS

LEAD STYLE	A	B	C
*-19	(26.16) 1.030		(20.83) .820
*-20	(31.24) 1.230	(2.79) .110	(25.91) 1.020
*-21	(36.32) 1.430	(2.79) .110	(30.99) 1.220
*-22	(16.00) .630	(7.62) .300	
*-23	(11.30) .445		(5.84) .230
*-24	(12.15) .480	(2.92) .115	(6.73) .265
*-25	(16.00) .630	(5.33) .210	(8.13) .320
▲-26	(11.58) .456	(3.20) .126	
-27	(33.78) 1.330	(25.40) 1.000	(5.84) .230
-28	(28.70) 1.130	(20.32) .800	
-29	(33.78) 1.330	(23.11) .910	(8.13) .320
-30	(28.70) 1.130	(18.03) .710	
+41	(9.27) .365	(0.89) .035	(5.84) .230
+42	(11.94) .470	(1.27) .050	(8.13) .320

† Style -41 & -42 available with HTSW only.

▲ Except: Style -26 (0.46) .018 DIA Tail







PLATING OPTION

-F
= Gold flash on post, Matte Tin on tail

-GF
= 3 μ " (0.07 μ m) Gold on post and tail

-L
= 10 μ " (0.25 μ m) Gold on post, Matte Tin on tail

-T
= Matte Tin



Right-Angle Versions

LEAD STYLE	D
-RA	(1.52) .060
-RE	(4.06) .160

RIGHT-ANGLE VERSIONS		
-RE LEAD STYLE	C	SINGLE E
-09	(5.84) .230	(4.83) .190
-10		(7.37) .290
-11		(9.91) .390
-12		(12.45) .490
-13		(17.53) .690
-16	(8.13) .320	(2.54) .100
-21	(5.84) .230	(22.61) .890
-22		(2.29) .090
-27		(20.07) .790
-28		(14.99) .590
-28		(14.99) .590





ROW OPTION

-S
= Single Row

-D
= Double Row

-T
= Triple Row

-Q
= Double Row
(5.08 mm).200" row space



OTHER OPTION

-RA or -RE
= Right-angle

-NA
= Right-angle
(Using straight body for coplanar mating with SSW-RA series)

-LL
= Locking Lead
See charts for available styles.
Not available with single row
1 or 2 positions.
Recommended hole size
(1.02 mm $\pm$ 0.03 mm) .040" $\pm$.001

-LC
= Locking Clip
(Styles -08 thru -13 & -22 only)
(Requires 4 pin minimum)
(Not available with T, -Q, -RA or -RE)

-LA
= -RA Option with -LL Option

-"XXX"
= Polarized Position

-RA LEAD STYLE	RIGHT-ANGLE VERSIONS			
	SINGLE (-S)		DOUBLE (-D)	TRIPLE (-T & -Q)
	C	E	E	E
-08	(5.84) .230	(2.29) .090	(2.29) .090	(2.29) .090
-09		(7.37) .290	(7.37) .290	(7.37) .290
-10		(9.91) .390	(9.91) .390	(9.91) .390
-11		(12.45) .490	(12.45) .490	(12.45) .490
-12		(14.99) .590	(14.99) .590	(14.99) .590
-13		(20.07) .790	(20.07) .790	N/A
*-16	(8.13) .320	(5.08) .200	(5.08) .200	(5.08) .200
-21	(5.84) .230	(25.15) .990	N/A	N/A
*-22		(4.83) .190	(4.83) .190	(4.83) .190
*-25	(8.13) .320	(2.54) .100	(2.54) .100	(2.54) .100
-27	(5.84) .230	(22.61) .890	N/A	N/A
-28		(17.53) .690	(17.53) .690	
-29	(8.13) .320	(20.32) .800	N/A	
-30		(15.24) .600	(15.24) .600	

* Available with -LA (Locking Lead) Option

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[TSW-104-08-T-D-008](#) [TSW-104-25-TM-D-LA](#) [TSW-124-05-F-D](#) [TSW-113-08-F-S](#) [TSW-216-08-L-D](#) [TSW-204-15-G-D](#) [TSW-208-06-G-S](#) [TSW-121-06-S-S](#) [TSW-210-16-G-S-RE](#) [HTSW-107-23-F-S](#) [HTSW-138-08-S-D](#) [HTSW-140-05-G-T](#) [HTSW-112-17-T-D](#) [HTSW-112-19-T-D](#) [HTSW-124-07-F-T](#) [HTSW-110-05-L-T](#) [TSW-126-13-L-S](#) [TSW-112-29-L-D](#) [TSW-140-30-G-D-RA](#) [TSW-214-29-T-S-RA](#) [TSW-130-06-L-D](#) [TSW-107-21-G-S-RA](#) [TSW-128-22-G-D](#) [TSW-133-08-G-T](#) [TSW-124-09-T-S-RE](#) [TSW-108-13-G-S-RE](#) [TSW-206-07-G-T](#) [TSW-122-05-G-T](#) [TSW-110-22-L-T-RA](#) [TSW-112-17-G-T](#) [TSW-148-19-F-D](#) [TSW-137-26-T-D](#) [TSW-122-08-F-T](#) [HTSW-103-18-STL-D-LL](#) [HTSW-104-18-STL-D-LL](#) [HTSW-104-26-T-S-002](#) [TSW-110-16-L-D-NA](#) [TSW-140-08-G-S-LA](#) [TSW-116-07-G-S-007](#) [TSW-123-05-F-D-002](#) [TSW-119-08-TL-S-RA](#) [TSW-110-22-L-D-NA](#) [TSW-108-22-L-T](#) [TSW-105-08-STL-D](#) [TSW-105-15-G-S-LL](#) [TSW-117-15-L-Q](#) [TSW-110-25-T-S-RA-004](#) [TSW-117-08-STL-D](#) [TSW-110-16-H-S-001](#) [TSW-105-07-STL-S-002](#) [TSW-146-25-T-S-RA](#) [TSW-116-17-T-D-LL](#) [TSW-103-08-STL-S-RA](#) [TSW-105-20-T-D-LL](#) [TSW-110-05-H-S](#) [TSW-103-08-STL-S](#) [TSW-114-08-F-Q-NA](#) [TSW-148-24-S-S](#) [TSW-119-08-F-D-LA](#) [TSW-136-08-STL-S](#) [TSW-110-08-STL-D](#) [TSW-108-07-TL-D](#) [TSW-126-05-G-D-LL](#) [TSW-124-24-STL-S](#) [TSW-142-15-T-D](#) [TSW-126-07-STL-D](#) [TSW-107-08-STL-D](#) [TSW-117-15-G-Q-LL](#) [TSW-126-07-STL-D-LL](#) [TSW-106-08-STL-D](#) [TSW-111-22-T-Q-RA](#) [TSW-107-20-H-D-LL](#) [TSW-106-07-STL-S-005](#) [TSW-104-24-STL-D](#) [TSW-108-08-STL-T](#) [TSW-123-12-T-D](#) [TSW-119-21-F-S](#) [TSW-126-14-F-T](#) [TSW-112-25-G-S-003](#) [TSW-111-15-G-S-LL](#) [TSW-103-08-STL-D](#) [TSW-111-07-TL-D](#) [TSW-132-28-L-S](#) [TSW-106-07-F-D-011](#) [TSW-146-24-F-D](#) [TSW-105-06-L-T](#) [TSW-120-07-F-D-036](#) [TSW-110-08-TL-S](#) [TSW-135-08-T-D-NA](#) [TSW-108-08-STL-D](#) [TSW-112-08-TL-D-RA](#) [TSW-117-08-STL-T](#) [TSW-126-08-STL-D](#) [TSW-115-10-G-D-006](#) [TSW-124-08-G-Q-RA-001](#) [TSW-125-07-STL-T](#) [TSW-107-06-L-T](#) [TSW-108-12-G-D-NA](#) [TSW-115-08-STL-D](#) [TSW-107-08-STL-D-006](#)