

# FLEX STACK



HW-14-08-G-S-300-100



DW-11-20-T-D-825

## DW, EW, ZW, HW-TH SERIES

(2.54 mm) .100"

# FLEXIBLE .025" SQ BOARD STACKERS

**Mates with:**  
SSW, SSQ, ESW, ESQ, CES, SLW, BSW, BCS, SSM, HLE, PHF

**Cable Mates:**  
IDSS, IDSD

### SPECIFICATIONS

For complete specifications see [www.samtec.com?DW](http://www.samtec.com?DW), [www.samtec.com?EW](http://www.samtec.com?EW), [www.samtec.com?ZW](http://www.samtec.com?ZW) or [www.samtec.com?HW-TH](http://www.samtec.com?HW-TH)

**Insulator Material:**  
DW, EW, ZW: Black Glass Filled Polyester  
HW: Natural Liquid Crystal Polymer

**Terminal Material:**  
Phosphor Bronze

**Plating:**  
Au or Sn over 50 μ" (1.27 μm) Ni  
**Operating Temp Range:**  
-55 °C to +125 °C with Gold  
-55 °C to +105 °C with Tin  
**RoHS Compliant:**  
Yes

**Lead-Free Solderable:**  
DW, EW, ZW:  
No, Lead Wave Only  
HW: Yes

### RECOGNITIONS

For complete scope of recognitions see [www.samtec.com/quality](http://www.samtec.com/quality)



FILE NO. E111594

### ALSO AVAILABLE (MOQ Required)

- Other platings

**Notes:**  
For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact [ipg@samtec.com](mailto:ipg@samtec.com) for more information.

This Series is non-standard, non-returnable.

TYPE STRIP	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	STACKER HEIGHT	OTHER OPTIONS																											
<p><b>DW</b> = (2.79 mm) .110" Tail</p>	<p><b>Specify LEAD STYLE from chart</b></p> <table border="1"> <thead> <tr> <th>LEAD STYLE</th> <th>OAL</th> </tr> </thead> <tbody> <tr><td>-07</td><td>(10.92) .430</td></tr> <tr><td>-08</td><td>(13.46) .530</td></tr> <tr><td>-09</td><td>(18.54) .730</td></tr> <tr><td>-10</td><td>(21.08) .830</td></tr> <tr><td>-11</td><td>(23.62) .930</td></tr> <tr><td>-12</td><td>(26.16) 1.030</td></tr> <tr><td>-13</td><td>(31.24) 1.230</td></tr> <tr><td>-14</td><td>(36.32) 1.430</td></tr> <tr><td>-15</td><td>(16.00) .630</td></tr> <tr><td>-16</td><td>(11.30) .445</td></tr> <tr><td>-17</td><td>(12.19) .480</td></tr> <tr><td>-19</td><td>(33.78) 1.330</td></tr> <tr><td>-20</td><td>(28.70) 1.130</td></tr> </tbody> </table>	LEAD STYLE	OAL	-07	(10.92) .430	-08	(13.46) .530	-09	(18.54) .730	-10	(21.08) .830	-11	(23.62) .930	-12	(26.16) 1.030	-13	(31.24) 1.230	-14	(36.32) 1.430	-15	(16.00) .630	-16	(11.30) .445	-17	(12.19) .480	-19	(33.78) 1.330	-20	(28.70) 1.130	<p><b>01 thru 50</b></p>	<p><b>-S</b> = Single Row</p> <p><b>-D</b> = Double Row</p> <p><b>-T</b> = Triple Row</p> <p><b>-Q</b> = Double Row .200" (5.08 mm) row space</p>	<p><b>“XXX”</b> = Stacker Height (in inches) (5.08 mm) .200" minimum Example: -250 = (6.35 mm) .250"</p>	<p><b>“XXX”</b> = ZW or HW Tail Length (in inches) (1.40 mm) .055" minimum Example: -250 = (6.35 mm) .250"</p>
LEAD STYLE		OAL																															
-07	(10.92) .430																																
-08	(13.46) .530																																
-09	(18.54) .730																																
-10	(21.08) .830																																
-11	(23.62) .930																																
-12	(26.16) 1.030																																
-13	(31.24) 1.230																																
-14	(36.32) 1.430																																
-15	(16.00) .630																																
-16	(11.30) .445																																
-17	(12.19) .480																																
-19	(33.78) 1.330																																
-20	(28.70) 1.130																																
<p><b>EW</b> = (8.38 mm) .330" Tail</p>	<p><b>-F</b> = Gold flash on contact, Matte Tin on tail</p>	<p><b>-L</b> = 10 μ" (0.25 μm) Gold on contact area of longer tail, Matte Tin on tail</p>	<p><b>-G</b> = 10 μ" (0.25 μm) Gold on contact area of longer tail, Gold flash on balance</p>	<p><b>-T</b> = Matte Tin</p>	<p><b>-LL</b> = Locking Lead (Shortest dimension between the tail and the post is the end that will be crimped. Available on tails from (2.29 mm) .090" to (7.87 mm) .310" only.) Single row, 01 &amp; 02 positions &amp; -Q row not available</p>																												
<p><b>ZW</b> = Custom Tail</p>	<p><b>HW</b> = High Temp Custom Tail</p>	<p><b>-T or -Q*</b> <b>-Q*</b> = Same as -T except middle row of pins missing.</p>	<p><b>“XXX”</b> = Polarized Specify omitted pin position</p>																														

Due to technical progress, all designs, specifications and components are subject to change without notice.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Samtec:

[HW-16-14-S-D-1085-130](#) [HW-13-13-G-D-865-120](#) [HW-20-09-S-D-455-SM-LC](#) [HW-20-20-L-D-600-SM-A](#) [HW-30-09-G-D-450-SM](#) [HW-04-08-L-D-250-SM](#) [HW-02-20-T-S-850-140](#) [HW-03-07-T-S-252-089-002](#) [HW-05-10-G-D-370-190](#) [HW-02-11-L-D-395-SM](#) [HW-02-12-L-D-710-SM](#) [HW-04-09-L-D-354-SM](#) [HW-05-15-T-D-465-SM](#) [HW-03-10-T-D-590-SM](#) [HW-03-12-T-D-750-SM](#) [HW-04-16-G-S-250-SM](#) [HW-03-15-T-S-367-132](#) [HW-04-10-L-D-465-SM-A](#) [HW-06-13-G-D-725-230](#) [HW-07-10-T-D-565-SM](#) [HW-08-14-G-D-1300-055](#) [HW-08-09-G-D-400-SM-A](#) [HW-05-15-G-S-500-065](#) [HW-17-09-S-D-560-085](#) [HW-20-15-G-D-310-SM](#) [HW-08-09-G-S-410-SM](#) [HW-20-12-S-D-330-560](#) [HW-05-11-T-D-750-SM](#) [HW-40-17-L-D-235-090](#) [HW-10-08-L-D-280-SM](#) [HW-10-12-G-D-800-SM](#) [HW-10-10-S-D-500-SM-A](#) [HW-07-09-L-D-250-SM-A](#) [HW-13-09-LM-D-440-SM-A](#) [HW-20-10-L-D-500-SM-A](#) [HW-16-08-T-S-264-133](#) [HW-16-12-G-S-525-295](#) [HW-24-13-L-S-590-170](#) [HW-24-20-L-D-930-100](#) [HW-26-10-L-D-450-SM-A](#) [HW-02-15-G-D-300-055](#) [HW-02-09-G-D-355-SM](#) [HW-03-10-T-D-640-SM](#) [HW-04-09-G-S-590-SM](#) [HW-04-10-T-D-354-236](#) [HW-02-11-T-D-724-103](#) [HW-04-15-L-S-261-118](#) [HW-02-10-T-D-640-SM](#) [HW-05-09-T-S-394-SM](#) [HW-05-15-L-D-315-SM](#) [HW-07-10-G-D-330-SM-A](#) [HW-03-09-G-D-395-SM](#) [HW-03-13-G-S-1024-103](#) [HW-05-10-T-S-484-SM](#) [HW-05-09-L-D-355-120](#) [HW-08-11-S-D-590-SM-A](#) [HW-06-15-G-D-285-100](#) [HW-17-10-TM-D-540-110](#) [HW-06-19-L-D-900-110](#) [HW-07-13-T-S-520-110](#) [HW-10-20-G-D-750-SM-A](#) [HW-12-10-L-D-465-SM-A](#) [HW-06-20-L-D-740-SM-002](#) [HW-08-17-G-D-270-104](#) [HW-20-12-L-D-705-SM-LC](#) [HW-04-09-L-D-250-SM-A](#) [HW-10-09-T-D-390-SM](#) [HW-15-20-L-D-740-SM-A](#) [HW-16-20-S-D-390-370](#) [HW-17-11-G-D-610-SM](#) [HW-14-08-G-D-255-SM-A](#) [HW-24-08-G-S-465-SM](#) [HW-10-09-L-D-450-SM-A](#) [HW-15-11-S-D-715-SM-A](#) [HW-28-09-T-S-425-SM](#) [HW-13-10-L-D-418-180](#) [HW-02-16-T-S-250-SM](#) [HW-02-12-T-S-228-086](#) [HW-04-09-T-S-507-SM](#) [HW-03-13-T-S-520-110](#) [HW-02-12-L-D-395-SM](#) [HW-03-19-T-D-354-119](#) [HW-05-09-T-D-460-SM](#) [HW-06-10-T-S-640-SM](#) [HW-03-09-G-D-355-SM](#) [HW-06-20-L-D-834-100](#) [HW-09-10-TM-D-450-190](#) [HW-07-10-L-D-374-SM](#) [HW-12-11-L-D-618-122](#) [HW-04-11-G-D-500-SM-A](#) [HW-08-09-LM-D-440-SM-A](#) [HW-10-11-T-S-725-SM](#) [HW-10-15-G-S-200-250](#) [HW-12-17-L-D-250-SM-A](#) [HW-17-20-G-D-740-SM-A](#) [HW-06-08-T-S-410-055](#) [HW-06-10-T-D-490-SM](#) [HW-06-12-L-S-650-140](#) [HW-10-16-G-D-275-SM-A](#) [HW-20-09-L-D-252-SM-A](#)