

Product: <u>RP12M-MSSV4D-0508</u>




M12 pigtail, Push Pull, Rolling Stock, EN45545, PUR black cable, shielded, male, straight, D-coded, 4-Pin, 4x0.34mm², PoE

Product Description

M12 pigtail, Push Pull, sensor cable, PVC orange cable, shielded, male, straight, A-coded, 4-Pin, 4x0.34mm², 50 V AC / 60 V DC, 4 A, - 25 °C - + 70 °C (operating temp.), IP65, IP67, DIN EN 60332-1-2, VDE 0482-332-1-2, IEC 60332-1-2, UL VW-1, CSA FT-1, DIN EN 50267-2-1, IEC 60754-1, VDE 0482-267-2-1, Free of lacquer wetting disturbing substances, Exclusion of silicone, Coldness flexibility

Technical Drawing



Technical Specifications

Technical Data

Product Family:	Data Connectors
Product Sub Family:	M12 Railway push pull
Brand:	Lumberg Automation
Connector Type:	Cordset, single ended
Type of Contact / Gender:	Male
Connector Design:	Straight
Number of Pins:	4
Coding:	D
Shielding:	Shielded
Attachment Type:	Snap Ring
Rated Voltage:	60 V
Rated Impulse Voltage:	1.5 kV
Operating Voltage:	50 V AC / 60 V DC
Rated Current*:	4 A
Data Transmission:	Fast Ethernet Cat5e
Data Transmission Rate:	100 Mbit/s
Contact Resistance:	≤ 10 mOhm
Insulation Resistance:	> 10^9 Ohm

Mating Cycles:	≤ 100
Ambient Temperature (Operation)*:	- 40 °C - + 85 °C
Protection Degree / IP Rating**:	IP65, IP67
Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Overvoltage Category:	III acc. to DIN EN 60664-1 (VDE 0110-1)

Materials

Contact Base Material:	CuSn
Contact Plating:	Cu/Au
Contact Bearer Material:	PA
Contact Bearer Color:	Black
Flammability Class (Contact Bearer):	UL 94 V-0
Molded Body Material:	PA
Molded Body Color:	Black
Flammability Class (Molded Body):	UL 94 V-0
Attachment Material:	PA
Shielding Material:	GD-Zn, nickel-plated

Additional Technical Data

			-
Fastening Torque (Attachment):	PushPull		

Cable Data

Cable Number:	508
Conductor Size:	0.34 mm ²
Number of Wires:	4
Minimal Bending Radius (Fixed Inst):	>5xD
Minimal Bending Radius (Flexible Inst):	> 10 x D
Conductor material:	Cu
Cable Jacket Material:	X-FRNC
Cable Jacket Color:	black
Cable Diameter D:	ø 6.70 ± 0.30 mm
Wire Insulation Material:	Polyolefin
Insulated Wire Diameter:	ø 1.63 ± 0.05 mm
Overall Shield (Cable):	Cu-ETP1 tinned
Foil shield:	AI-PT Foil
Ambient Temperature (Fixed Installation):	- 40 °C - + 90 °C
Ambient Temperature (Flex Installation):	- 40 °C - + 90 °C
Flammability Class (Cable Jacket):	Flame resistance acc. IEC 45545: IEC 60332-1-2, EN50305 and IEC60332-3-25 cat D
Cable Characteristics:	cable meets the requirements of the relevant parts of international railway standards like DIN 5510-2, EN50153 EN50155, EN50305 and CEN/TS 45545
Core Colors:	white & blue, yellow & orange

Safety & Environmental Compliance

RoHS Compliant:	yes
Resistances	
Halogenfree:	IEC 60754-1, EN 50267-1-2, HCL < 0.4%
Oil Resistance:	IEC 60811-2-1, EN 50306 par 4.8, EN 50306 par 4.9, EN 50306 par 4.10
Notos	

U	
_	

Note Derating:	* Notice derating
Protection Degree / IP Rating Note:	** only if mounted and locked in combination with Hirschmann / Lumberg Automation connector.

Variants

Item #	Item Description
935301028	RP12M-MSSV4D-0508-0500
935301027	RP12M-MSSV4D-0508-0300
935301026	RP12M-MSSV4D-0508-0200
935301025	RP12M-MSSV4D-0508-0100

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulators based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumberg Automation:

RP12M-MSSV4D-0508-0200
RP12M-MSSV4D-0508-0500
RP12M-MSSV4D-0508-0300
RP12M-MSSV4D-0508-0300

0100

</td