

(2.00 mm) .0787" PITCH • CABLE ASSEMBLY/COMPONENTS

SERIES	PINS PER ROW	WIRE GAUGE	PLATING OPTION	ASSEMBLED LENGTH	END OPTIONS	END 2 OPTIONS
S2SD = Double Row PVC Cable	-05, -07, -10, -15, -20, -25, -30 (Standard sizes)	-24 -24C = Color Coded Cable (S2SD only)	-L = 10 μ" (0.25 μm) Gold on contact	-"XX.XX" = Wire Length in Inches (69.85 mm) 02.75" min.	-S = Single End -D = Double End Specify "S" for single ended and "D" for double ended. -(X)R = Retention Latch (-SR mates with T2M-WT) -(X)S = Screw Down (10 positions minimum) (mates with T2M-DS)	(Only available with -D, -DR & -DS) -NUS = Notch up, straight (Pin 1 to Pin N-1) -NDS = Notch down, straight (Pin 1 to Pin 2) -NUX = Notch up, crossed (Pin 1 to Pin N) -NDX = Notch down, crossed (Pin 1 to Pin 1)
S2SDT = Double Row Blue *Teflon™ Fluoropolymer Cable (24, 28, 30 AWG only)		-26 -28 -30				




S2SD(T)

Board Mates:
T2M

SPECIFICATIONS

Insulator Material:
Black LCP
Contact Material:
BeCu
Plating:
Au over 50 μ" (1.27 μm) Ni
Wire:
24, 26, 28 or 30 AWG
Operating Temp Range:
-10 °C to +105 °C (PVC)
-40 °C to +125 °C
(*Teflon™ Fluoropolymer)
**Current Rating
(S2SD-24/T2M):**
3.8 A per pin
(2 pins powered)
Voltage Rating:
250 VAC

-24C CABLE COLOR CODING	
PIN	COLOR
1	BROWN
2	RED
3	ORANGE
4	YELLOW
5	GREEN
6	VIOLET
7	GRAY
8	WHITE
9	BLACK
10	BLUE
ETC	REPEAT



*Teflon™ is a trademark of The Chemours Company FC, LLC used under license by Samtec.

Notes:
Teflon™ Fluoropolymer cable is intended for crimp only. Contact Samtec for solderable cable applications.

For wiring option information refer to drawings on web.

View complete specifications at: samtec.com?S2SD & samtec.com?S2SDT

ISD2	POSITIONS PER ROW	ROW OPTION	LATCH OPTION	SERIES	WIRE GAUGE	01	PLATING OPTION
	-05, -07, -10, -15, -20, -25, -30 (Standard sizes)	-D = Double Row	-M = Metal Retention Latch -S = Screw Down	CC81L = Contact, Loose CC81R = Contact, Full Reel (17,000 Parts per Reel)	-2426 = 24 to 26 AWG -2830 = 28 to 30 AWG		-L = 10 μ" (0.25 μm) Gold on contact

TOOLING

Hand Tool: CAT-HT-281-2430-13

Mini Applicator: CAT-MC-281-2426-XX-01 (24-26 AWG)

Extraction Tool: CAT-EX-169-01

Mini Applicator: CAT-MC-281-2830-XX-01 (28-30 AWG)

Note:
Some lengths, styles and options are non-standard, non-returnable.

View complete specifications at: samtec.com?ISD2, samtec.com?CC81R & samtec.com?CC81L

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[ISD2-10-D-M](#) [ISD2-25-D-M](#) [ISD2-05-D-M](#) [ISD2-08-D-DS](#) [ISD2-09-D-R](#) [ISD2-12-D-R](#) [ISD2-14-D-R](#) [ISD2-16-D-DS](#)
[ISD2-18-D-R](#) [ISD2-50-D-M](#) [ISD2-18-D-M](#) [ISD2-40-D-DS](#) [ISD2-03-D-R](#) [ISD2-05-D-DS](#) [ISD2-07-D-DS](#) [ISD2-15-D-DS](#)
[ISD2-25-D-DS](#) [ISD2-14-D-M](#) [ISD2-15-D-M](#) [ISD2-20-D-DS](#) [ISD2-20-D-M](#) [ISD2-30-D-DS](#) [ISD2-30-D-M](#) [ISD2-10-D-](#)
[DS](#) [ISD2-11-D-M](#) [ISD2-11-D-R](#) [ISD2-12-D-M](#) [ISD2-13-D-M](#) [ISD2-13-D-R](#) [ISD2-04-D-R](#) [ISD2-06-D-M](#) [ISD2-06-D-R](#)
[ISD2-08-D-M](#) [ISD2-08-D-R](#) [ISD2-09-D-M](#) [ISD2-50-D](#) [ISD2-50-D-R](#) [ISD2-02-D-M](#) [ISD2-02-D-R](#) [ISD2-03-D-M](#)
[ISD2-04-D-M](#) [ISD2-30-D-R](#) [ISD2-36-D](#) [ISD2-38-D](#) [ISD2-40-D](#) [ISD2-44-D](#) [ISD2-48-D](#) [ISD2-24-D](#) [ISD2-25-D](#) [ISD2-](#)
[25-D-R](#) [ISD2-26-D](#) [ISD2-29-D](#) [ISD2-30-D](#) [ISD2-16-D](#) [ISD2-18-D](#) [ISD2-19-D](#) [ISD2-20-D](#) [ISD2-20-D-R](#) [ISD2-22-D](#)
[ISD2-10-D-R](#) [ISD2-11-D](#) [ISD2-12-D](#) [ISD2-14-D](#) [ISD2-15-D](#) [ISD2-15-D-R](#) [ISD2-07-D](#) [ISD2-07-D-M](#) [ISD2-07-D-R](#)
[ISD2-08-D](#) [ISD2-09-D](#) [ISD2-10-D](#) [ISD2-02-D](#) [ISD2-03-D](#) [ISD2-04-D](#) [ISD2-05-D](#) [ISD2-05-D-R](#) [ISD2-06-D](#) [ISD2-40-](#)
[D-M](#) [ISD2-28-D-M](#) [ISD2-32-D-M](#) [ISD2-33-D](#) [ISD2-17-D-M](#) [ISD2-22-D-M](#) [ISD2-16-D-M](#) [ISD2-28-D](#)