

# JACK SCREW STANDOFF

## JSO SERIES



### SPECIFICATIONS

**Material:**  
Stainless Steel  
**Locking Compound:**  
Nylon

### JSO

### BOARD STACKER

### LEAD STYLE

### PLATING OPTION

Specify  
BOARD STACKER  
from chart

### -01

= Press-In  
(-0415, -0515, -0715, -0815 only)

### -03

= Male Thread  
(-0815, -1015, -1115, -1615 only)

### -L

= Locking compound  
(Not available with -01 lead style,  
Required for -03 lead style)


BOARD STACKER	A	B	BOARD STACK HEIGHT
-0415	(4.15) .163	(2.50) .098	4 mm
-0515	(5.15) .203	(3.50) .138	5 mm
-0715	(7.15) .281	(5.50) .217	7 mm
-0815	(8.15) .321	(6.50) .256	8 mm
-1015	(10.15) .400	(8.50) .335	10 mm
-1115	(11.15) .439	(9.50) .374	11 mm
-1615	(16.15) .636	(14.50) .571	16 mm

### ALSO AVAILABLE MOQ Required

Other heights  
Locking compound removed

**Notes:**  
Standoffs are designed,  
0.15 mm longer than  
connector stack heights to  
allow for processing variables.

Some sizes, styles and  
options are non-standard,  
non-returnable.




-01 LEAD STYLE

-03 LEAD STYLE

Components are to be packaged in separate bags unassembled.

## APPLICATION



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[JSO-1615-03-L](#) [JSO-1015-03-L](#) [JSO-0815-03-L](#) [JSO-0715-01](#) [JSO-1765-01](#) [JSO-1115-03-L](#) [JSO-0415-01](#) [JSO-0515-01](#) [JSO-0815-01](#)