

XCGB4 Multi-Conductor - GigaBIX Cross-Connect Wire



For more Information
please call

1-800-Belden1

**General Description:**

CAT6 (250MHz), 4-Pair, U/UTP-Unshielded, Premise Cross-Connect Cable, 23 AWG solid bare copper conductors, Dual FRPO/FEP insulation

Usage (Overall)

Suitable Applications: Cross-Connect, Interconnect

Physical Characteristics (Overall)**Conductor**

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	23	Solid	BC - Bare Copper

Total Number of Conductors: 8

Insulation

Insulation Material:

Insulation Material
PO - Polyolefin

Overall Cable

Overall Cabling Color Code Chart:

Number	Color	AWG
1	Blue + White / Blue	23
1	Orange + White / Orange	23
1	Green + White / Green	23
1	Brown + White / Brown	23

Overall Nominal Diameter: 4.699 mm

Mechanical Characteristics (Overall)

UL Temperature Rating: 60°C

Bulk Cable Weight: 40.181 Kg/Km

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification: UL444

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 08/19/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: UL1685 UL Loading

XCGB4 Multi-Conductor - GigaBIX Cross-Connect Wire

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics-Premise (Overall)

Premise Cable Electricals:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. SRL (dB)	Fitted Imp. (Ohms)
0.772	1.800		102 ± 15
1.0	2.000	20.0	100 ± 15
4.0	3.700	23.0	100 ± 15
8.0	5.200	24.5	100 ± 15
10.0	5.800	25.0	100 ± 15
16.0	7.400	25.0	100 ± 15
20.0	8.300	25.0	100 ± 15
25.0	9.300	24.3	100 ± 15
31.25	10.400	23.6	100 ± 15
62.5	15.000	21.5	100 ± 15
100.0	19.300	20.8	100 ± 15
155.0	24.500	19.5	100 ± 15
200.0	28.300	18.7	100 ± 15
250.0	32.100	18.0	100 ± 15
300.0	35.600	17.5	100 ± 15

Notes (Overall)

Notes: Third party verified to ANSI/TIA-568-C.2, Category 6.

Reference (Overall)

Previous Part Number: 24577B15, 24570521

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
XCGB4 000A1000	1,000 FT	21.000 LB	NONE		GIGABIX 4PR X-CONN RIB
XCGB4 0001000	1,000 FT	20.000 LB	NONE		GIGABIX 4PR X-CONN REEL

Revision Number: 1 Revision Date: 08-14-2013

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[XCGB4 000A1000](#) [XCGB4 0001000](#)