



**POWER
STRIP[™] 30**
(5.00 mm) .1969"

MPPT SERIES

HERMAPHRODITIC 30A POWER SYSTEM

SPECIFICATIONS

For complete specifications see www.samtec.com?MPPT

Insulator Material:

Black LCP

Terminal Material:

Copper Alloy

Plating:

Sn or Au over 50 μ "
(1.27 μ m) Ni

Operating Temp Range:

-55 °C to +105 °C with Tin;
-55 °C to +125 °C with Gold

Voltage Rating:

510 VAC/721 VDC

Standard Creepage:

(2.95 mm) .116"

Standard Clearance:

(2.71 mm) .106"

RoHS Compliant:


Yes

Lead-Free Solderable:

Yes

Mates with:
MPPT

CREEPAGE AND CLEARANCE



Selectively loading contacts achieves customer specific creepage and clearance requirements.

Contact asp@samtec.com

Dual leaf contacts

Screw down option

Dual blade post

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality




MPPT/MPPT	
POWER PINS	CURRENT RATING (PER CONTACT)
1	35.5 A
2	29.6 A
3	27.6 A
4	24.4 A
10	20.2 A



ALSO AVAILABLE (MOQ Required)

- Locking Clip (Manual placement required)
- Solder Leads for (2.36 mm) .093" thick board

APPLICATION



Note:
Some sizes, styles and options are non-standard, non-returnable.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[MPPT-04-01-01-L-RA-SD](#) [MPPT-08-01-01-L-RA-SD](#) [MPPT-10-01-02-T-RA-SD](#) [MPPT-02-01-01-L-RA-SD-TR](#) [MPPT-04-01-01-L-RA-SD-TR](#) [MPPT-04-01-01-T-RA-SD](#) [MPPT-08-01-02-L-RA-SD](#) [MPPT-08-01-02-T-RA-SD](#) [MPPT-10-01-01-L-RA-SD](#) [MPPT-10-01-01-L-RA-SD-TR](#) [MPPT-06-01-01-T-RA-SD](#) [MPPT-08-01-01-T-RA-SD](#) [MPPT-06-01-01-L-RA-SD](#) [MPPT-02-01-01-L-RA-SD](#) [MPPT-08-01-01-L-RA-SD-TR](#) [MPPT-08-01-02-L-RA-SD-TR](#) [MPPT-10-01-02-L-RA-SD](#) [MPPT-04-01-02-T-RA-SD](#) [MPPT-02-01-02-L-RA-SD](#) [MPPT-06-01-02-L-RA-SD-TR](#) [MPPT-04-01-02-L-RA-SD](#)