



IMAGING TRMS MULTIMETER

FLIR DM166™

The FLIR DM166 is the most affordable multimeter with built-in thermal imaging – a must-have tool for commercial electricians, automation, electronics, and HVAC technicians. Featuring Infrared Guided Measurement (IGM™) powered by an 80 x 60 FLIR thermal imager, the DM166 visually guides you to the precise location of temperature anomalies and potential problems faster, more safely, and efficiently. The feature-packed multimeter is an ideal tool for troubleshooting and diagnosing complex issues in both high-voltage and low-voltage applications.

www.flir.com/professionalDMMs



TROUBLESHOOT FASTER

One tool gets the job done

- Quickly scan for overheating components with IGM
- Diagnose faults with broad DMM test functions
- Troubleshoot easier with the unique combination of onboard thermal imaging and traditional DMM test functions



WORK SAFER

Identify energized and potentially faulty equipment from a safe distance

- Safely check for live connections using non-contact temperature measurement
- Carefully measure voltage with integrated non-contact voltage detection
- Work with peace of mind knowing your meter has a CAT III-600V, CAT IV-300V safety rating



DIAGNOSE PROBLEMS MORE EFFICIENTLY

Rich feature set covers both high-voltage and low-voltage applications

- Reliably take 600 V AC/DC voltage measurements and 10 A AC/DC current measurements
- Remove high-frequency noise that affects readings with the Variable Frequency Drive (VFD) measurement function
- Precisely measure resistance up to 60 MΩ, frequency up to 50 KHz, and capacitance up to 10,000 μF

SPECIFICATIONS

Thermal Imaging DM166	
IR Resolution	80 x 60 pixels (4,800 pixels)
Thermal Imaging Detector	FLIR Lepton® microbolometer
Temperature Sensitivity	≤ 150 mK
Emissivity Settings	4 presets with custom adjustment
Temperature Accuracy	3°C or 3%
Temperature Range	14° F to 302°F (-10C to 150° C)
Field of View	50° x 38°
Laser Pointer	Yes
Focus	Fixed
Thermal Imaging Palette	Iron, Rainbow, Grayscale
Level & Span	Auto
Measurements	
True RMS	Yes
	Range Basic Accuracy
AC / DC Volts	600.0 V ±0.7% / 0.5%
AC / DC mVolt	600.0 mV ±1% / 0.3%
VFD AC Volts	600.0 V ±1.0%
AC / DC Amps	10.00 A ±1.0% / 0.7%
AC / DC mAmps	600.0 mA ±1.0% / 0.7%
AC / DC µAmps	6000 µA ±1.5% / 1.0%
Resistance	6.000 MΩ ±0.9% 60.00 MΩ ±1.5%
Capacitance	2.000 mF ±2.0% 10.00 mF ±5.0%
Diode Test	3.000 V ±0.9%
Frequency Counter	50.00 kHz ±0.3%
Temperature, Type-K Thermocouple	-40°F to 752.0°F ±1.0% + 3°F -40°C to 400°C ±1.0% + 1.5°C

Additional Measurements DM166	
Continuity Check	30 Ω and 480 Ω
Measuring rate	5 samples per second
General Information	
Auto Power Off	Yes
Display Size	2.4 in TFT screen
Battery	3 AA batteries; optional TA04 Li-Poly rechargeable battery
Drop Test	3 m
IP Rating	IP40
Safety Category Rating	CAT III-600V, CAT IV-300V
Size (L x W x H)	190 × 86.4 × 48.3 mm (7.5 × 3.4 × 1.9 in)
Weight	428.3 g (15.1 oz)
Warranty	10 year on product and detector

Box Contents	
	DM166, L91 lithium batteries, silicone test leads, soft carrying case

Ordering Information	Order #
FLIR DM166 Thermal Imaging TRMS Multimeter with IGM	793950391662

For a complete list of available accessories, go to:
flir.com/store/instruments/testaccessories

Specifications are subject to change without notice.
 For the most up-to-date specs, go to www.flir.com

CORPORATE HEADQUARTERS
 FLIR Systems, Inc.
 27700 SW Parkway Ave.
 Wilsonville, OR 97070
 PH: +1 877.773.3547

NASHUA
 FLIR Systems, Inc.
 9 Townsend West
 Nashua, NH 03063
 USA
 PH: +1 866.477.3687

LATIN AMERICA
 FLIR Systems Brasil
 Av. Antonio Bardella, 320
 Sorocaba, SP 18085-852
 Brasil
 PH: +55 15 3238 7080

CANADA
 FLIR Systems, Ltd.
 920 Sheldon Court
 Burlington, ON L7L 5K6
 Canada
 PH: +1 800.613.0507

www.flir.com
 NASDAQ: FLIR

Equipment described herein is subject to US export regulations and may require a license prior to export. Diversion contrary to US law is prohibited. Imagery for illustration purposes only. Specifications are subject to change without notice. ©2017 FLIR Systems, Inc. All rights reserved. 09/22/17

17-2458-INS-TAM



The World's Sixth Sense®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FLIR:

[DM166-NIST](#) [DM166](#)