


FLEX STACK

LOW-PROFILE .025" SQ POST HEADERS

(2.54 mm) .100" PITCH • TLW/MTLW SERIES



TLW/MTLW

Board Mates:

BSW, CES, SLW, HLE

FEATURES

These headers provide the ultimate low-profile (0.64 mm) .025" square post board stacking system. The high quality Phosphor Bronze terminals are available with a standard short post height (TLW Series) for mating with low-profile sockets, or the post height can be Modified (MTLW Series) to accommodate IDC assemblies and other applications.

SPECIFICATIONS

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over

50 μ " (1.27 μ m) Ni

Current Rating (TLW/SLW):

5.2 A per pin

(2 pins powered)

Operating Temp Range:

-55 °C to +105 °C with Tin

-55 °C to +125 °C with Gold

PROCESSING

Lead-Free Solderable:

Yes

ALSO AVAILABLE


MOQ Required


Other platings

Notch option

Note:

Some lengths, styles and options are non-standard, non-returnable. MTLW Series is non-standard, non-returnable.

TLW	- 1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OTHER OPTION
		01 thru 40 = Single Row	Specify LEAD STYLE from chart	-F = Gold flash on post, Matte Tin on tail	-S = Single Row	-RA = Right-angle (-01 Lead Style only)
		01 thru 36 = Double Row		-G = 10 μ" (0.25 μm) Gold on post, Gold flash on tail	-D = Double Row	-“XX” = Polarized Position Specify position for omitted pin.
				-T = Matte Tin		
						
-05 & -06						
LEAD STYLE	A	B				
-01	N/A	(5.84) .230				
-05	(4.32) .170	(2.67) .105				
-06	(3.43) .135					

MTLW	- 1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	POST HEIGHT																				
		01 thru 40 = Single Row	Specify LEAD STYLE from chart	-F = Gold flash on post, Matte Tin on tail	- S = Single Row	- "XXX" = Post Height Dimension (In inches)																				
		01 thru 36 = Double Row		-L = 10 μ" (0.25 μm) Gold on post, Matte Tin on tail	- D = Double Row																					
				-G = 10 μ" (0.25 μm) Gold on post, Gold flash on tail																						
				-T = Matte Tin																						
																										
				<table><thead><tr><th>LEAD STYLE</th><th>OAL</th></tr></thead><tbody><tr><td>-05</td><td>(8.51) .335</td></tr><tr><td>-06</td><td>(7.62) .300</td></tr><tr><td>-07</td><td>(10.92) .430</td></tr><tr><td>-08</td><td>(13.46) .530</td></tr><tr><td>-09</td><td>(18.54) .730</td></tr><tr><td>-10</td><td>(21.08) .830</td></tr><tr><td>-22</td><td>(16.00) .630</td></tr><tr><td>-23</td><td>(11.30) .445</td></tr><tr><td>-24</td><td>(12.19) .480</td></tr></tbody></table>			LEAD STYLE	OAL	-05	(8.51) .335	-06	(7.62) .300	-07	(10.92) .430	-08	(13.46) .530	-09	(18.54) .730	-10	(21.08) .830	-22	(16.00) .630	-23	(11.30) .445	-24	(12.19) .480
LEAD STYLE	OAL																									
-05	(8.51) .335																									
-06	(7.62) .300																									
-07	(10.92) .430																									
-08	(13.46) .530																									
-09	(18.54) .730																									
-10	(21.08) .830																									
-22	(16.00) .630																									
-23	(11.30) .445																									
-24	(12.19) .480																									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[MTLW-108-05-G-D-170](#) [MTLW-105-07-L-D-200](#) [MTLW-110-05-T-S-195](#) [MTLW-106-05-G-S-140](#) [MTLW-102-23-L-S-255](#) [MTLW-105-08-G-D-150](#) [MTLW-102-09-T-S-500](#) [MTLW-103-05-S-D-120](#) [MTLW-103-06-G-S-155](#) [MTLW-103-07-G-S-240](#) [MTLW-102-07-G-S-230](#) [MTLW-105-07-L-S-250](#) [MTLW-102-07-G-S-270](#) [MTLW-103-23-L-D-295](#) [MTLW-105-05-L-S-157](#) [MTLW-106-06-T-S-125](#) [MTLW-107-06-L-D-145](#) [MTLW-106-05-G-D-160](#) [MTLW-106-07-G-S-280](#) [MTLW-107-07-S-D-280](#) [MTLW-108-06-G-D-120](#) [MTLW-105-07-T-S-270](#) [MTLW-108-07-G-S-200](#) [MTLW-106-07-S-S-235](#) [MTLW-104-07-L-S-250](#) [MTLW-108-07-L-S-195](#) [MTLW-110-06-S-D-130](#) [MTLW-105-07-L-S-235](#) [MTLW-106-06-T-S-050](#) [MTLW-105-09-S-S-530](#) [MTLW-114-22-G-S-270](#) [MTLW-105-05-T-S-185](#) [MTLW-105-07-G-S-260](#) [MTLW-106-07-G-D-230](#) [MTLW-106-07-G-S-240](#) [MTLW-107-07-T-D-240](#) [MTLW-108-07-G-D-275](#) [MTLW-115-05-G-D-170](#) [MTLW-116-07-S-S-290](#) [MTLW-125-07-L-D-240](#) [MTLW-120-06-S-D-133](#) [MTLW-120-07-G-S-235](#) [MTLW-120-06-G-D-160](#) [MTLW-125-07-G-D-245](#) [MTLW-114-07-S-S-185](#) [MTLW-125-06-L-D-135](#) [MTLW-110-05-G-D-185](#) [MTLW-120-05-L-S-165](#) [MTLW-136-05-G-S-200](#) [MTLW-101-07-T-S-255](#) [MTLW-102-06-G-S-110](#) [MTLW-103-06-G-D-135](#) [MTLW-101-06-G-D-125](#) [MTLW-101-06-S-D-105](#) [MTLW-102-07-G-S-160](#) [MTLW-102-07-G-D-250](#) [MTLW-103-07-G-D-270](#) [MTLW-104-06-T-S-150](#) [MTLW-104-06-T-S-195](#) [MTLW-105-06-G-S-150](#) [MTLW-105-07-G-D-220](#) [MTLW-102-07-T-S-270](#) [MTLW-104-08-G-S-350](#) [MTLW-105-07-L-D-240](#) [MTLW-107-06-G-D-100](#) [MTLW-104-07-S-D-245](#) [MTLW-107-07-T-S-280](#) [MTLW-108-05-T-D-185](#) [MTLW-106-07-G-S-189](#) [MTLW-108-06-G-D-125](#) [MTLW-106-09-T-S-500](#) [MTLW-107-07-S-D-250](#) [MTLW-107-24-T-D-110](#) [MTLW-103-09-G-D-470](#) [MTLW-110-07-L-D-190](#) [MTLW-105-07-L-S-240](#) [MTLW-108-05-G-D-216](#) [MTLW-103-08-SM-S-280](#) [MTLW-105-24-T-D-305](#) [MTLW-109-10-T-S-380](#) [MTLW-110-09-G-D-580](#) [MTLW-132-06-S-D-130](#) [MTLW-130-08-L-D-470](#) [MTLW-112-05-G-S-175](#) [MTLW-112-08-G-S-345](#) [MTLW-125-07-G-D-280](#) [MTLW-116-05-T-S-185](#) [MTLW-136-24-T-D-330](#) [MTLW-140-10-T-S-680](#) [MTLW-102-07-T-S-319](#) [MTLW-103-05-G-S-225](#) [MTLW-104-07-G-D-255](#) [MTLW-101-05-G-S-160](#) [MTLW-102-06-G-D-170](#) [MTLW-102-07-G-D-240](#) [MTLW-103-06-L-S-130](#) [MTLW-103-07-G-S-150](#) [MTLW-102-07-L-S-250](#) [MTLW-104-07-S-D-184](#) [MTLW-101-05-G-S-185](#)