

1

2

3

4

A

B


C

D





E

Actuating Force

$F = 9N \pm 3N$



Terminal
6.3 - 0.8



Marking

168..

16(4)/250V ~ T100/55

05

16A 125-250V AC

R81

Code of manufacture: place/year/week

On Box: G

Operating Position	h
OFF	24.0
ON	21.3
Block	19.7

DPST

Suitable for appliances of class II

Actuator designed for use with external cap.
This cap must be used to ensure that
no additional force is applied to the switch base
during the entire stroke.

G = matching IEC 60335-1:2001 clause 30

-		-						-			1682.7704-XX			
Figure		Type						Customer No.			Art.No.-PI			
General tolerances									Sheet 01			Ident. K	Document number 16827704	Index a
All dimensions are in millimetres		Shape and location 	Angle ± 2 °	Edge tolerance 			Length	Radii						
						0-6	± 0.15	± 0.2						
						>6-15	± 0.2	± 0.3						
						>15-30	± 0.25	± 0.5						
						>30-70	± 0.4	± 10%						
						>70-120	± 0.6							
>120	± 1													
a	129820		2019-11-25				HHE		System NX V11.0			Appliance Switch		
	47738		2006-06-06				HHE		Replacement of					
Index	MEC-No.		Date (YYYY-MM-DD)				Edited by					 MARQUARDT		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[01682.7704-00](#)