

MUSB-05-F-B-SM-A

MUSB SERIES

MINI USB 2.0 INTERFACES

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?MUSB

Insulator Material:

High Temperature
Thermoplastic

Contact Material:

Phosphor Bronze

Shell Material:

Brass

Plating:

Gold on Mating Area,
Nickel on Shell, Tin on Tails

Operating Temp Range:

-50 °C to +85 °C

Voltage Rating:

30 VRMS

Minimum Cycles:

1500

Packaging:



Packaged and shipped in
Bulk Packaging Trays; Trays
suitable for automation are
available upon request.

RoHS Compliant:

Yes

Lead-Free Solderable:

Yes



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[MUSB-05-F-B-SM-A](#) [MUSB-05-S-AB-SM-A-TR](#) [MUSB-05-S-AB-SM-A](#) [MUSB-05-S-B-SM-A](#) [MUSB-05-F-AB-SM-A-K-TR](#) [MUSB-05-F-AB-SM-A](#) [MUSB-05-S-B-SM-A-R-TR](#) [MUSB-05-S-AB-SM-A-K-TR](#) [MUSB-05-S-B-SM-A-K](#) [MUSB-05-F-B-SM-A-TR](#) [MUSB-05-F-B-SM-A-K-TR](#) [MUSB-05-F-AB-SM-A-TR](#) [MUSB-05-S-B-SM-A-K-TR](#) [MUSB-05-S-B-SM-A-TR](#) [MUSBR-05-S-O-B-SM-A](#) [MUSBR-05-F-O-B-SM-A](#) [MUSB-05-S-A-SM-A-TR](#) [MUSB-05-F-A-SM-A-TR](#) [MUSB-05-F-A-SM-A](#) [MUSB-05-F-AB-SM-A-R-TR](#) [MUSB-05-F-B-SM-A-R-TR](#) [MUSB-05-S-A-SM-A](#) [MUSB-05-S-AB-SM-A-R-K-TR](#) [MUSB-05-S-AB-SM-A-K](#) [MUSB-05-S-AB-SM-A-R-K](#) [MUSB-05-F-B-SM-A-K](#) [MUSB-05-S-A-SM-A-R-TR](#) [MUSB-05-S-AB-SM-A-R-TR](#) [MUSB-05-F-A-SM-A-R-TR](#) [MUSB-05-F-AB-SM-A-K](#) [MUSB-05-F-B-SM-A-R-K-TR](#) [MUSB-05-F-A-SM-A-R](#) [MUSB-05-F-B-SM-A-R-K](#) [MUSB-05-F-AB-SM-A-R-K](#) [MUSB-05-F-AB-SM-A-R-K-TR](#) [MUSBR-05-F-O-A-SM-A](#) [MUSBR-05-S-O-A-SM-A](#) [MUSB-05-S-AB-SM-A-FR](#) [MUSB-05-F-B-SM-A-K-FR](#) [MUSB-05-F-AB-SM-A-K-FR](#) [MUSB-05-S-B-SM-A-K-FR](#) [MUSB-05-F-AB-SM-A-FR](#) [MUSBS-05-S-B-TH-FR](#) [MUSB-05-F-B-SM-A-FR](#) [MUSB-05-S-B-SM-A-FR](#) [MUSB-05-S-AB-SM-A-K-FR](#)