## **Features**

# Regulated Converters

- 3W power in SMD package
- 4:1 Input voltage range
- Efficiency up to 84%
- 1.6kVDC/1min isolation
- Regulated output
- -40°C to +71°C at full load
- Continuous short circuit protected

## Description

The R3M is an isolated 3W DC/DC converter in a compact SMD package available with 4:1 inputs covering 5, 12, 24, and 48V rails providing single or dual regulated, short-circuit protected outputs. There is no minimum load requirement. Isolation is 1.6kVDC/1min, and the operating temperature is from -40°C up to +71°C without derating. Class A and Class B EMC conformity requires only a few external components. Standard packaging is tube.

## R3M

3 Watt
SMD
Single & Dual
Output

RECC

DC/DC Converter







#### **Selection Guide**

Part Number	Input Voltage Range <sup>(1)</sup> [VDC]	nom. Output Voltage [VDC]	Output Current [mA]	Efficiency typ. <sup>(2)</sup> [%]	max. Capacitive Load <sup>(3)</sup> [μ <b>F</b> ]
R3M-xx3.3S/SMD	4.5-18, 9-36, 18-75	3.3	700	76-77	4700
R3Mxx05S/SMD	4.5-18, 9-36, 18-75	5	600	80	2530
R3Mxx09S/SMD	4.5-18, 9-36, 18-75	9	333	81	1470
R3M-xx12S/SMD	4.5-18, 9-36, 18-75	12	250	83	1220
R3M-xx15S/SMD	4.5-18, 9-36, 18-75	15	200	83-84	1000
R3M-xx24S/SMD	4.5-18, 9-36, 18-75	24	125	82	470
R3M-xx05D/SMD	4.5-18, 9-36, 18-75	±5	±300	80	±1470
R3M-xx12D/SMD	4.5-18, 9-36, 18-75	±12	±12 <mark>5</mark>	82	±680
R3M-xx15D/SMD	4.5-18, 9-36, 18-75	±15	±100	82	±470

#### Notes:

Note1: Refer to "Input Voltage Range"

Note2: Efficiency is tested at nominal input and full load at +25°C ambient Note3: Max Cap Load is tested at nominal input and full resistive load

#### **Model Numbering**



#### Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

BASIC CHARACTERISTICS							
Parameter	Cond	dition	Min.	Тур.	Max.		
	nom. V <sub>™</sub>	= 12VDC	4.5VDC	12VDC	18VDC		
Input Voltage Range	nom. V <sub>IN</sub> = 24VDC		9VDC	24VDC	36VDC		
	nom. V <sub>™</sub>	nom. $V_{IN}$ = 48VDC		48VDC	75VDC		
		nom. V <sub>IN</sub> = 12VDC			25VDC		
Input Surge Voltage	1 second max.	nom. V <sub>IN</sub> = 24VDC			50VDC		
		nom. V <sub>IN</sub> = 48VDC			100VDC		
continued on next page							



## **Series**

### Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

Parameter	Co	ndition	Min.	Тур.	Max.
	nom. \	/ <sub>IN</sub> = 12VDC		40mA	
Quiescent Current	nom. \	/ <sub>IN</sub> = 24VDC		20mA	
	nom. \	/ <sub>IN</sub> = 48VDC		15mA	
Start-up time	power up,	power up, CTRL ON/OFF		10ms	20ms
ON/OFF CTRL (4)	DC	DC-DC ON		open or	high im <mark>ped</mark> ance
	DC-DC OFF		2mA	3mA	4mA
Standby Current	DC-	-DC OFF		2.5mA	
Internal Operating Frequency					
Output Ripple and Noise	201	20MHz BW		50mVp-p	
Reflected Back Ripple Current		nom. V <sub>IN</sub> = 12VDC		20mAp-p	
	with external	nom. V <sub>IN</sub> = 24VDC		30mAp-p	
	components	nom. V <sub>IN</sub> = 48VDC		20mAp-p	


#### Notes:

#### Note4: Refer to "ON/OFF CTRL"











continued on next page



## **Series**

Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)







## **Series**


#### Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

REGULATIONS			
Parameter	Con	dition	Value
Output Accuracy			±1.0% max.
Line Regulation	low line to hig	h line, full load	±0.2% max.
	0% to 100% load	single	1% max.
Load Pagulation		dual	1% max.
Load Regulation		single	0.5% max.
		dual	0.8% max.
Cross Regulation	asymmetrical 25% / 100% load		±5% max.
Transient Response Recovery Time	25% load step change		±500μs typ.

PROTECTIONS							
Parameter	Ту	pe				P	Value
Short Circuit Protection (SCP)						continuou	s, auto recovery
Isolation Voltage (5)	I/P to O/P	1 minute					1.6kVDC min.
Isolation Resistance	I/P to O/P, V	so= 500VDC					1G $\Omega$ min.
Isolation Capacitance	I/P to O/P, 1	00kHz/0.1V					50pF typ.
Notes:  Note5: This power module is not internally fused. An input line fuse must always be used							
Recom suggests: 12Vin=T1.6A; 24Vin=T0.8A; 48Vin=T0.5A slow blow							

ENVIRONMENTAL			
Parameter		Condition	Value
Operating Temperature Dange		with derating	-40°C to +105°C
Operating Temperature Range		without derating	-40°C to +71°C
Maximum Case Temperature		measured at "tc point"	+105°C
Operating Humidity		non-condensing	5% - 95% RH max.
Thermal Shock			according to MIL-STD-810F
Vibration			according to MIL-STD-810F
MTBF	6	according to MIL-HDBK-217F, G.B. +25°C	5627 x 10 <sup>3</sup> hours

**Derating Graph** (@ Chamber and natural convection 0.1m/s)






## **Series**

#### Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

SAFETY AND CERTIFICATIONS						
Certificate Type (Safety)	File Number	Standard				
RoHS2		RoHS-2011/65/EU + AM-2015/863				
EMC Compliance	Condition	Standard / Criterion				
Electromagnetic compatibility of multimedia equipment – Emission Requirements	with external filter refer to "EMC Filtering"	EN55032, Class A and B				

#### **EMC Filtering Suggestions according to EN55032**




#### **Class A Component List**

Model	C1	C2	C3	L1
R3M-12xxS	22µF	N/A	220pF	6.8µH
R3M-24xxS	10μF	N/A	470pF	15µH
R3M-48xxS	2.2µF	N/A	680pF	68µH

#### Class B Component List

Model	C1, C2	C3	L1
R3M-12xxS	22µF	220pF	6.8µH
R3M-24xxS	10μF	470pF	15μΗ
R3M-48xxS	2.2µF	680pF	68µH






## **Series**

### Specifications (measured @ Ta= 25°C, nom. Vin, full load and after warm-up unless otherwise stated)

DIMENSION AND PHYSICAL CHARACTERISTICS				
Parameter	Туре	Value		
Matarial	baseplate/case	black plastic (UL94 V-0)		
Material	potting	silicone (UL94 V-0)		
Dimension (LxWxH)		14.2 x 9.1 x 10.2mm		
Weight		2.7g typ.		



PACKAGING INFORMATION		
Parameter	Туре	Value
Packaging Dimension (LxWxH)	tube	218.0 x 17.2 x 19.9mm
Packaging Quantity		20pcs
Storage Temperature Range	non-condensing	-55°C to +125°C
Storage Humidity		5% to 95% RH max.

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

### **RECOM:**

 R3M-1205D/SMD
 R3M-1205S/SMD
 R3M-1209S/SMD
 R3M-1212D/SMD
 R3M-1212S/SMD
 R3M-1215D/SMD

 R3M-4815S/SMD
 R3M-4824S/SMD
 R3M-483.3S/SMD
 R3M-4805D/SMD
 R3M-4805S/SMD
 R3M-4809S/SMD
 R3M-4809S/SMD
 R3M-4809S/SMD
 R3M-4809S/SMD
 R3M-2412D/SMD
 R3M-2412S/SMD
 R3M-2415D/SMD
 R3M-2415D/SMD
 R3M-2415D/SMD
 R3M-2415D/SMD
 R3M-1215S/SMD
 R3M-1215S/SMD
 R3M-1224S/SMD
 R3M-123.3S/SMD
 R3M-123.3S/SMD
 R3M-12405D/SMD
 R3M-12405S/SMD
 R3M-12409S/SMD
 R3M-12405S/SMD
 R3M-12405S/SMD
 R3M-12409S/SMD
 R3M-12405S/SMD
 R3M-12405S/