

R-78K-2.0(L) series

2Amp / SIP3 Single Output

FEATURES

- Efficiency up to 96%, no need for heatsinks
- 4.5 - 36VDC wide input voltage
- -40°C to +90°C ambient operation without derating
- Pin compatible with 78 series regulators
- Non isolated DC/DC converter
- Undervoltage and short circuit protection



Dimensions (LxWxH): 11.5 x 8.5 x 17.5mm (0.45 x 0.33 x 0.69 inch)
4.0g (0.09 lbs)

APPLICATIONS**SAFETY & EMC****DESCRIPTION**

The R-78K-2.0 series is a switching regulator module that has been designed to offer all the advantages of a switching regulator (high efficiency, wide input range, accurate output voltage regulation) but with a low cost for production quantities. Due to the R-78K-2.0's high efficiency of up to 96% no heat-sink is required, and operation from -40 to 90°C is possible without derating. The compact TO-220 compatible SIP3 package measures only 11.5 x 8.5 x 17.5, so it saves precious board space.

SELECTION GUIDE

Part Number	Input Voltage Range [VDC]	Output Voltage [VDC]	Output Current [mA]	Efficiency	
				@ min. Vin [%]	@ max. Vin [%]
R-78K1.2-2.0 ⁽¹⁾	4.5 - 36	1.2	2000	75	73
R-78K1.5-2.0 ⁽¹⁾	4.5 - 36	1.5	2000	82	71
R-78K1.8-2.0 ⁽¹⁾	4.5 - 36	1.8	2000	85	78
R-78K2.5-2.0 ⁽¹⁾	4.5 - 36	2.5	2000	88	85
R-78K3.3-2.0 ⁽¹⁾	4.5 - 36	3.3	2000	85	78
R-78K5.0-2.0 ⁽¹⁾	6.5 - 36	5	2000	85	78
R-78K9.0-2.0 ⁽¹⁾	11 - 36	9	2000	95	93
R-78K12-2.0 ⁽¹⁾	14 - 36	12	2000	96	94
R-78K15-2.0 ⁽¹⁾	18 - 36	15	2000	96	94


Note1: add suffix "L" for 90° bent pins, e.g. R-78K5.0-2.0L

R-78K-2.0(L) series**2Amp / SIP3 Single Output**BASIC CHARACTERISTICS (measured @ $T_{AMB}=25^{\circ}\text{C}$, nom. V_{IN} , full load and after warm-up unless otherwise stated)


Parameter	Condition		Min.	Typ.	Max.
Input Under Voltage Lockout (UVLO)	others	DC-DC ON	4VDC		4.4VDC
		DC-DC OFF	3.8VDC		4.2VDC
	R-78K3.3-0.5	DC-DC ON	5VDC		6.5VDC
		DC-DC OFF	4.8VDC		6.3VDC
	R-78K5.0-0.5	DC-DC ON	9.9VDC		10.7VDC
		DC-DC OFF	9.7VDC		10.5VDC
	R-78K12-0.5	DC-DC ON	13.1VDC		14.0VDC
		DC-DC OFF	12.7VDC		13.8VDC
	R-78K15-0.5	DC-DC ON	15.4VDC		16.7VDC
		DC-DC OFF	15.2VDC		16.5VDC
Maximum Input Voltage Slew Rate ⁽²⁾	+ V_{IN} to GND				10VDC/ μs
Quiescent Current					1mA
Internal Operating Frequency				400kHz	
Minimum Load			0%		
Output Ripple and Noise ⁽³⁾	20MHz BW and full load	others		100mVp-p	120mVp-p
		R-78K12-2.0		170mVp-p	200mVp-p
		R-78K15-2.0		200mVp-p	250mVp-p

Note2: At higher slew rates or hard plugging, add 27 μF E-Cap on + V_{IN} , especially when V_{IN} is greater than 18VDCNote3: Measurements are made with a 10 μF MLCC across output. (low ESR)**R-78K1.2-2.0**


Efficiency vs. Output Load




Power Dissipation vs. Output Load

**R-78K1.5-2.0**

Efficiency vs. Output Load



Power Dissipation vs. Output Load




R-78K-2.0(L) series

2Amp / SIP3 Single Output


BASIC CHARACTERISTICS (measured @ $T_{AMB} = 25^{\circ}\text{C}$, nom. V_{IN} , full load and after warm-up unless otherwise stated)

R-78K1.8-2.0

Efficiency vs. Output Load




Power Dissipation vs. Output Load




R-78K2.5-2.0

Efficiency vs. Output Load




Power Dissipation vs. Output Load




R-78K3.3-2.0

Efficiency vs. Output Load



Power Dissipation vs. Output Load




R-78K-2.0(L) series

2Amp / SIP3 Single Output


BASIC CHARACTERISTICS (measured @ $T_{AMB} = 25^{\circ}\text{C}$, nom. V_{IN} , full load and after warm-up unless otherwise stated)

R-78K5.0-2.0

Efficiency vs. Output Load




Power Dissipation vs. Output Load




R-78K9.0-2.0

Efficiency vs. Output Load




Power Dissipation vs. Output Load




R-78K12-2.0

Efficiency vs. Output Load




Power Dissipation vs. Output Load




R-78K15-2.0

Efficiency vs. Output Load



Power Dissipation vs. Output Load

**REGULATIONS**

Parameter	Condition	Value
Output Accuracy		$\pm 3.0\%$ typ.
Line Regulation	low line to high line, full load	$\pm 0.5\%$ max.
Load Regulation	0% to 100%	4.0% max.



PROTECTIONS

Parameter	Condition	Value
Short Circuit Protection (SCP)		continuous, automatic recovery

Optional Diode Protection Circuit

Add a blocking diode to V_{out} if current can flow backwards into the output, as this can damage the converter when it is powered down.

The diode can either be fitted across the device if the source is low impedance or fitted in series with the output (recommended).





Optional Protection 1:**Optional Protection 2:****ENVIRONMENTAL**

Parameter	Condition	Value
Operating Temperature Range	refer to „Derating Graph“	-40°C to $+100^{\circ}\text{C}$
Maximum Case Temperature		$+110^{\circ}\text{C}$
Operating Altitude		5000m
Operating Humidity	non-condensing	95% RH max.
Pollution Degree		PD2
Short Circuit Protection (SCP)		continuous, automatic recovery
MTBF	according to MIL-HDBK-217F, G.B., $+25^{\circ}\text{C}$	R-78K1.8-2.0
		R-78K2.5-2.0
		R-78K3.3-2.0
		R-78K5.0-2.0
		R-78K9.0-2.0
		R-78K12-2.0
		R-78K15-2.0
Vibration		10-55Hz, 2G, 30min along X,Y and Z axis

ENVIRONMENTAL

Derating Graph

(@ Chamber and natural convection 0.1m/s, over Vin)



SAFETY AND CERTIFICATIONS

Certificate Type (Safety)

Audio/Video, information and communication technology equipment - Part 1: Safety requirements (CB Scheme)

Audio/Video, information and communication technology equipment - Part 1: Safety requirements

RoHS2

Report Number

085-220299301-100

Standard

IEC62368-1:2018 3rd Edition

EN IEC 62368-1:2020+A11:2020

RoHS 2011/65/EU + AM2015/863

EMC Compliance


Electromagnetic compatibility of multimedia equipment - Emission requirements

Condition

with external filter

Standard /Criterion



EN55032, Class A and B



Component List	C1	C2	C3	L1	L2	C4
Class A	22µF	22µF	N/A	4.7µH	N/A	N/A
Class B	10µF	22µF	22µF	4.7µH	22µH	1nF

R-78K-2.0(L) series**2Amp / SIP3 Single Output****DIMENSION & PHYSICAL CHARACTERISTICS**

Parameter	Type	Value
Material	case	black plastic, (UL94 V-0)
	potting	PU, (UL94 V-0)
	PCB	FR4, (UL94 V-0)
Dimension (HxWxD)		11.5 x 8.5 x 17.5mm
		0.45 x 0.33 x 0.69 inch
Weight		4g typ. 0.009 lbs

Dimension Drawing (mm)**PACKAGING INFORMATION**

Parameter	Type	Value
Packaging Dimension (LxWxH)	tube	standard 520.0 x 25.5 x 10.5mm
		"L"-version 520.0 x 23.0 x 16.5mm
Packaging Quantity		43pcs
Storage Temperature Range		-40°C to +125°C
Storage Humidity	non-condensing	95% RH max.

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[RECOM:](#)

[R-78K3.3-2.0](#) [R-78K9.0-2.0](#) [R-78K2.5-2.0](#) [R-78K1.2-2.0](#) [R-78K12-2.0](#) [R-78K1.5-2.0](#) [R-78K5.0-2.0](#) [R-78K1.8-2.0](#)
[R-78K15-2.0](#) [R-78K1.2-2.0L](#) [R-78K1.5-2.0L](#) [R-78K1.8-2.0L](#) [R-78K12-2.0L](#) [R-78K15-2.0L](#) [R-78K2.5-2.0L](#) [R-78K3.3-](#)
[2.0L](#) [R-78K5.0-2.0L](#) [R-78K9.0-2.0L](#)