




SC-7P1-GG



STANDARD, LOW PROFILE &

Specifications: SC, SP, SK

Contact:

BeCu

Shell:

Brass

-GG Plating:

30μ" (0,76μm) Au over 50μ"
(1,27μm) Ni on contact;
10μ" (0,25μm) Au over 50μ"
(1,27μm) Ni on shell

-GT Plating:

30μ" (0,76μm) Au over 50μ"
(1,27μm) Ni on contact; Sn
over 50μ" (1,27μm) Ni on shell

-TT Plating:

Sn over 50μ" (1,27μm) Ni
on contact; Sn over 50μ"
(1,27μm) Ni on shell

-ST Plating:

10μ" (0,25μm) Au over 50μ"
(1,27μm) Ni on contact; Sn
over 50μ" (1,27μm) Ni on shell

Current Rating:

1 A

Contact Resistance:

10 mΩ max

Insertion Force (SC):

9 oz (2,50N) avg, 16 oz
(4,45N) max

Withdrawal Force (SC):

2.5 oz (0,70N) avg, 1.5 oz
(0,42N) min

Insertion Force (EZ):

2.5 oz (0,70N) avg, 5.5
(1,53N) oz max

Withdrawal Force (EZ):

2.0 oz (0,56N) avg, 0.35 oz
(0,10mm) min

Lead DIA Accepted:

.015" to .022" (0,38mm to
0,56mm) and most IC leads


RECOMMENDED PC HOLE SIZE:

LEAD SIZE	HOLE SIZE
(0,46) .018 DIA	(0,61) .024 DIA
(0,51) .020 DIA	(0,66) .026 DIA
(0,64) .025 DIA	(0,79) .031 DIA
(0,76) .030 DIA	(0,91) .036 DIA
(0,89) .035 DIA	(1,04) .041 DIA
(1,14) .045 DIA	(1,30) .051 DIA
(1,32) .052 DIA	(1,47) .058 DIA
(0,46) .018 SQ	(0,76) .030 DIA
(0,64) .025 SQ	(1,02) .040 DIA
(1,14) .045 SQ	(1,75) .069 DIA
(0,20) .008 x (0,71) .028	(0,89) .035 DIA
(0,25) .010 x (0,51) .020	(0,71) .028 DIA
(0,41) .016 x (0,51) .020	(0,79) .031 DIA
(0,41) .016 x (0,61) .024	(0,89) .035 DIA
(0,41) .016 x (0,79) .031	(1,04) .041 DIA

Note:

Some sizes, styles and
options are non-standard,
non-returnable.

SC-1P1-, SC-6P1-, SC-1P3-, SC-2P1- EZ-1P1-, EZ-6P1-, SC-7P1



Part No.	X DIA	Y ±.010	Z ±.015
SC-1P1- EZ-1P1-	(0,51) .020	(3,18) .125	(7,62) .300
SC-6P1- EZ-6P1-	(0,51) .020	(4,57) .180	(8,89) .350
SC-1P3-	(0,64) .025	(10,41) .410	(15,24) .600
SC-2P1-	(0,89) .035	(12,95) .510	(17,86) .703
SC-7P1-	(0,51) .020	(7,06) .278	(11,25) .443

Insertion Depth (SC-1P1, SC-1L1, SC-6P1, SC-7P1)
= .95" to .145" (2,41mm to 3,68mm)


Insertion Depth (SC-2P1) = .125" to .157" (3,18mm to 3,99mm)

Insertion Depth (SC-1P3) = .095" to .138" (2,41mm to 3,51mm)


Plating Available (SC-1P1, SC-1L1) = GG, GT, TT, ST

Plating Available (SC-6P1, SC-2P1, SC-7P1) = GG, GT

SC-1L1- EZ-1L1-



SC-2P3-, EZ-2P3-, EZ-2P2-



Plating Available = GG, GT

Part No.	X DIA	W ±.010	Y ±.015	Z ±.015
SC-2P3- EZ-2P3-	(0,51) .020	(4,32) .170	(8,86) .349	(13,77) .542
EZ-2P2-	(0,46) .018	(3,81) .150	(12,95) .510	(17,86) .703


Insertion Depth (SC-2P2) =

.125" to .145" (3,18mm to 2,41mm)

Insertion Depth (SC-2P3) =

.125" to .170" (3,18mm to 4,32mm)

SC-1W1- EZ-1W1-




Part No.	Y ±.010	Z ±.015
SC-1W1-XX-1 EZ-1W1-XX-1	(12,95) .510	(17,86) .703
SC-1W1-XX-2 EZ-1W1-XX-2	(9,14) .360	(14,05) .553
SC-1W1-XX-3 EZ-1W1-XX-3	(6,60) .260	(11,51) .453

Insertion Depth=

.125" to .157" (3,18mm to 3,99mm)

Plating Available = GG, GT, TT

SC-5P1- EZ-5P1-




Insertion Depth (SC-5P1) = .080" to .150"

(2,03mm to 3,81mm)

Lead DIA Accepted: .016" to .020" (0,41mm to 0,51mm)

Plating Available (SC-5P1, EZ-5P1) = GG, GT, TT

SC-3P1- EZ-3P1-



Insertion Depth = .105" to .170" (2,67mm to 4,32mm)

Lead DIA Accepted: .015" to .020" (0,38mm to 0,51mm)

Plating Available = GG, GT, TT

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 • Fax: 812-948-5047

SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0 • Fax: +49 (0) 89 / 89460-299

SAMTEC NORDIC/BALTIC • Tel: +46-84477280 • Fax: +46-87420413

SAMTEC JAPAN • Tel: 045-475-1385 • Fax: 045-475-1340

SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 • Fax: 65 6841-1502

SAMTEC HONG KONG • Tel: 852-26904858 • Fax: 852-26904842

SAMTEC SILICON VALLEY • Tel: 408-395-5900 • Fax: 408-395-1520

SAMTEC FRANCE • Tel: 01 60 95 06 60 • Fax: 01 60 95 06 61

SAMTEC ISRAEL • Tel: 972-3-7526600 • Fax: 972-3-7526690

SAMTEC CHINA • Tel: 86-21-61103766 • Fax: 86-21-5423 4575

SAMTEC SOUTH AFRICA • Tel: 27 11 454 4317 • Fax: 27 86 6714432

SAMTEC UK • Tel: 01236 739292 • Fax: 01236 727113

SAMTEC ITALY • Tel: 39 039 6890337 • Fax: 39 039 6890315

SAMTEC INDIA • Tel: +91-80-3272 1612 • Fax: +91-80-4152 8187

SAMTEC TAIWAN • Tel: 886-2-2735-6109 • Fax: 886-2-2735-5036

SAMTEC ANZ • Tel: 613 9512 7747 • Fax: 613 9512 7745



SC-1S1-GG



SURFACE MOUNT SOCKETS SC, EZ SERIES

Specifications:

SC-1P4, 2P4

Contact: BeCu

Shell: Brass

-GG Plating:

20μ" (0,51μm) Au over 50μ" (1,27μm) Ni on contact, except SC-2P4 30μ" (0,76μm) Au; 10μ" Au over 50μ" (1,27μm) Ni on shell

-GT Plating:

20μ" (0,51μm) Au over 50μ" (1,27μm) Ni on contact, except SC-2P4 30μ" (0,76μm) Au; Sn over 50μ" (1,27μm) Ni on shell

Current Rating:

5 A

Contact Resistance:

10 mΩ max

Insertion Force:

6.5 oz (1,81N) avg, 13 oz (3,62N) max (.032" (0,81mm) DIA probe)

Withdrawal Force: 3 oz (0,83N) avg, 2 oz (0,56N) min (.032" (0,81mm) DIA probe)

Specifications:

SC-2P8, 2P9

Contact: BeCu

Shell: Brass

-GG Plating:

20μ" (0,51μm) Au over 50μ" (1,27μm) Ni on contact; 10μ" (0,25μm) Au over 50μ" (1,27μm) Ni on shell

-GT Plating:

20μ" (0,51μm) Au over 50μ" (1,27μm) Ni on contact; 200μ" (5,08μm) Sn over 50μ" (1,27μm) Ni on shell

Current Rating:

10 A

Contact Resistance:

10 mΩ max

Insertion Force: SC-2P9 = 32 oz (8,90N) max (.050" (1,27mm) DIA probe); SC-2P8 = 16 oz (4,45N) max (.040" (1,02mm) DIA probe)

Withdrawal Force: SC-2P9 2 oz (0,56N) min (.050" (1,27mm) DIA probe) SC-2P8 = 4 oz (1,11N) min (.040" (1,02mm) DIA probe)

Specifications:

T, S

-G Plating:

Au over 50μ" (1,27μm) Ni

-T Plating:

Sn over 50μ" (1,27μm) Ni or 100μ" (2,54μm) Cu


Current Rating:

1A except T-1S6 is 5A

Note:


Some sizes, styles and options are non-standard, non-returnable.

SC-4P1-, EZ-4P1-




Insertion Depth = .080" to .105" (2,03mm to 2,67mm)
Lead DIA Accepted: .016" to .021" (0,41mm to 0,53mm)
Plating Available = GG, GT, TT

SC-8P1-




Insertion Depth = .085" to .140" (2,16mm to 3,56mm)
Lead DIA Accepted: .016" to .020" (0,41mm to 0,51mm)
Plating Available = GG, GT, TT

SC-1S1-, EZ-1S1-



Insertion Depth = .125" to .157" (3,18mm to 3,99mm)
Lead DIA Accepted = .015" to .022" (0,38mm to 0,56mm)
Plating Available = GG, GT


SC-1P4-, SC-2P4-



Part No.	X DIA	Y	Z REF
SC-1P4-	(0,76) .030	(3,18) .125	(9,53) .375
SC-2P4-	(0,91) .036	(12,95) .510	(19,30) .760

Insertion Depth = .175" (4,45mm) to .215" (5,46mm)
Lead DIA Accepted = .032" (0,81mm) to .038" (0,97mm)
Plating Available = GG, GT

SC-2P8-, SC-2P9-



Part No.	X DIA	Y
SC-2P8-	(2,08) .082	(6,10) .240
SC-2P9-	(2,59) .102	(6,86) .270

Insertion Depth (SC-2P8) = .165" (4,91mm) to .220" (5,59mm)
Lead DIA Accepted (SC-2P8) = .035" (0,89mm) to .045" (1,14mm)
Insertion Depth (SC-2P9) = .170" (4,32mm) to .205" (5,21mm)
Lead DIA Accepted (SC-2P9) = .045" (1,14mm) to .055" (1,40mm)
Plating Available = GG, GT

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[SC-1S1-GG](#) [EZ-5P1-GT](#) [SC-2P3-GT](#)