




DO NOT
SCALE FROM
THIS PRINT

FIG. 1
(FFMD-10-D-XX.XX-01-X SHOWN)



FFMD-XX-X-XX.XX-01-X-X-XXX

No OF POSITIONS
-03, -04, -05, -06, -07, -08, -09,
-10, -13, -14, -15, -16, -17,
-18, -19, -20, -22, -25
END ASSEMBLY
-D: DOUBLE END
-S: SINGLE END
*-T: TRANSFER END

ASSEMBLY LENGTH
(2.00[50.8] MINIMUM)

LEAD STYLE


PLATING OPTIONS
LEAVE BLANK FOR STANDARD
(USE T-1S57-01-T AND C-67-L)
-L: SELECTIVE LIGHT GOLD
(USE T-1S57-01-L AND C-67-L)
-F: FLASH SELECTIVE GOLD
(USE T-1S57-01-F AND C-67-F)
-S: SELECTIVE GOLD
(USE T-1S57-01-S AND C-67-S)

OPTION
-RW: REVERSE WIRING
-BXX: BREAKOUT OPTION
-O: OUTSIDE REVERSED
-M: MIDDLE REVERSED
-R: REVERSE
-DXX: DAISY CHAIN (MINIMUM 2.00[50.8]
1.00[25.4] INCREMENTS)
-SR: STRAIN RELIEF
(NOT AVAILABLE WITH -O, -M,
-R, -DXX OR -BXX)
(SOLD AS ASSEMBLIES ONLY)
TRANSFER OPTION
-N: SOCKET HAS NOTCH POLARIZATION
(-T END ASSEMBLY ONLY)
(LEAVE BLANK FOR -S AND -D
END OPTIONS)
(NOT AVAILABLE ON POSITIONS -02
THRU -04)

*16-25 POS TRANSFER END STRAIN RELIEF NOT RELEASED FOR PRODUCTION

FIG. 2
(FFMD-10-S-XX.XX-01-X SHOWN)
(SAME AS FIG. 1, DIFFERENT AS SHOWN)

XX.XX [XX.XX x 25.4] ±.13[3.2]
(SEE NOTE 7) S




NOTES:
1. S REPRESENTS A CRITICAL DIMENSION.
2. FFSD ASSEMBLY TO BE USED FOR TRANSFER END ONLY.
3. ALL ASSEMBLIES TO BE 100% ELECTRONICALLY TESTED FOR SHORTS AND OPENS.
4. ALL ASSEMBLIES TO BE 100% HI-POT TESTED AT 630V.
5. STRAIN RELIEF TO WITHSTAND 5LB[22N] STRAIGHT PULL.
6. FFMD CABLE ASSEMBLIES ARE LEAD FREE.
7. WHEN CUTTING CABLE TO LENGTH, CONDUCTORS MAY NOT EXTEND PAST THE CABLE INSULATION.

TABLE 1	
ITEM #	PART
1	FFSD-XX-XX-X-N
2	CB-XX-30-7
3	FFMD-XX-XX-X-XX
4	FFMD-XX-01-X-SR
5	FFSR-XX-01
6	FFSR-XX-02
7	FFSD-XX-XX-X-N-SR1
8	FFSD-XX-XX-X-N-SR2

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.
TOLERANCES ARE:
DECIMALS ANGLES
.XX: ±.01 [.3] 2°
.XXX: ±.005 [.13]
.XXXX: ±.0020 [.051]

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 2:1
INSULATOR: PBT, COLOR: BLACK
CONTACT: BeCu
TERMINAL: PHOS BRONZE




520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
.050 X .050 DOUBLE ROW MALE IDC CABLE ASSEMBLY


DWG. NO.
FFMD-XX-X-XX.XX-01-X-X-XXX

BY: T NEWTON 02/15/2008 SHEET 1 OF 5

FIG. 3
(FFMD-10-D-XX.XX-0T-X-SR SHOWN)
(SAME AS FIG. 1, DIFFERENT AS SHOWN)



IN-PROCESS 1
-SR ONLY



IN-PROCESS 2
-SR ONLY




FIG. 4
(FFMD-10-X-XX.XX-0T-X-RW SHOWN)
(SAME AS FIG. 1, DIFFERENT AS SHOWN)




FIG. 6
(FFMD-10-T-XX.XX-0T-X-N SHOWN)
(SAME AS FIG. 1, DIFFERENT AS SHOWN)




FIG. 5
(FFMD-10-X-XX.XX-0T-X-N SHOWN)
(SAME AS FIG. 1, DIFFERENT AS SHOWN)
(FOR -T ONLY)
(IF OPTION IS SPECIFIED USE FFSD-XX-01-X-N)





FIG. 7
(FFMD-10-T-XX.XX-0T-X-N-B05 SHOWN)
(SAME AS FIG. 1, DIFFERENT AS SHOWN)
"XX" = NO. OF CONDUCTORS PER ROW
BROKEN OUT FROM THE FIRST POSITION



PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
.050 X .050 DOUBLE ROW MALE IDC CABLE ASSEMBLY

DWG. NO.
FFMD-XX-X-XX.XX-01-X-X-XXX

BY: T NEWTON 02/15/2008 SHEET 2 OF 5

FIG. 8
(FFMD-10-D-XX.XX-01-X-DXX-O SHOWN)
(SAME AS FIG. 1, DIFFERENT AS SHOWN)
(2.00[50.8] MINIMUM LENGTH, 1.00[25.4] INCREMENTS)




FIG. 9
(FFMD-10-D-XX.XX-01-X-DXX-M SHOWN)
(SAME AS FIG. 1, DIFFERENT AS SHOWN)
(2.00[50.8] MINIMUM LENGTH, 1.00[25.4] INCREMENTS)




FIG. 10
(FFMD-10-T-XX.XX-01-X-N-DXX-O SHOWN)
(SAME AS FIG. 1, DIFFERENT AS SHOWN)
(2.00[50.8] MINIMUM LENGTH, 1.00[25.4] INCREMENTS)





FIG. 11
(FFMD-10-T-XX.XX-01-X-N-DXX-M SHOWN)
(SAME AS FIG. 1, DIFFERENT AS SHOWN)
(2.00[50.8] MINIMUM LENGTH, 1.00[25.4] INCREMENTS)



PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
.050 X .050 DOUBLE ROW MALE IDC CABLE ASSEMBLY

DWG. NO.
FFMD-XX-X-XX.XX-01-X-X-XXX

BY: T NEWTON 02/15/2008 SHEET 3 OF 5

FIG. 12

(FFMD-10-D-XX.XX-01-DXX-R SHOWN)
(SAME AS FIG. 1, DIFFERENT AS SHOWN)
(2.00[50.8] MINIMUM LENGTH, 1.00[25.4] INCREMENTS)





FIG. 13

(FFMD-10-D-XX.XX-01-X-DXX)
(SAME AS FIG. 1, DIFFERENT AS SHOWN)
(2.00[50.8] MINIMUM LENGTH, 1.00[25.4] INCREMENTS)





FIG. 14

(FFMD-10-T-XX.XX-01-X-N-DXX-R SHOWN)
(SAME AS FIG. 1, DIFFERENT AS SHOWN)
(2.00[50.8] MINIMUM LENGTH, 1.00[25.4] INCREMENTS)







FIG. 15

(FFMD-10-T-XX.XX-01-X-N-DXX)
(SAME AS FIG. 1, DIFFERENT AS SHOWN)
(2.00[50.8] MINIMUM LENGTH, 1.00[25.4] INCREMENTS)



PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
.050 X .050 DOUBLE ROW MALE IDC CABLE ASSEMBLY

DWG. NO.
FFMD-XX-X-XX.XX-01-X-X-XXX

BY: T NEWTON 02/15/2008 SHEET 4 OF 5

FIG. 16
(FFMD-10-T-XX.XX-01-X-N-SR SHOWN)
(SAME AS FIG. 1, DIFFERENT AS SHOWN)
(FOR POSITIONS 2-15 ONLY)





FIG. 17
(FFMD-25-T-XX.XX-01-X-N-SR SHOWN)
(SAME AS FIG. 1, DIFFERENT AS SHOWN)
(FOR POSITIONS 16-25 ONLY)
*NOT RELEASED FOR PRODUCTION



PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
.050 X .050 DOUBLE ROW MALE IDC CABLE ASSEMBLY

DWG. NO.
FFMD-XX-X-XX.XX-01-X-X-XXX

BY: T NEWTON 02/15/2008 SHEET 5 OF 5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[FFMD-09-D-06.00-01](#) [FFMD-15-T-08.00-01-N-R](#) [FFMD-16-T-06.00-01-N](#) [FFMD-03-S-03.00-01](#) [FFMD-07-S-12.00-01](#)
[FFMD-16-D-08.00-01](#) [FFMD-03-D-05.00-01](#) [FFMD-06-D-16.00-01](#) [FFMD-07-D-04.00-01-R](#) [FFMD-15-D-20.00-01](#)