

BERGQUIST® LIQUI FORM TLF 4500CGEL-SF

December 2023

Product description

BERGQUIST® LIQUI FORM TLF 4500CGEL-SF provides the following product characteristics:

Technology	Silicone free
Appearance	Gray paste
Cure	Moisture cure
Application	Thermal management TIM (Thermal Interface Material)
Application method	Dispense from cartridge or pails
Operating temperature range, continuous or others	-40 to 125°C

BERGQUIST® LIQUI FORM TLF 4500CGEL-SF is thermally conductive, one-part, curable gel sil-free material.

BERGQUIST® LIQUI FORM TLF 4500CGEL-SF is a one part, high performance, thermally conductivity, silicone-free, room temperature curable gel designed for demanding high reliability applications. Curing (skin formation) can be accelerated with heat. As cured, BERGQUIST® LIQUI FORM TLF 4500CGEL-SF provides a soft, thermally conductive, form-in place elastomer that is ideal for fragile assemblies, capable of filling unique and intricate air voids and gaps. It is ideal for applications where highly reliable vertical gap stability is required. BERGQUIST® LIQUI FORM TLF 4500CGEL-SF requires no mixing or refrigerated storage. This material's unique silicone-free formulation assures a balanced mix of high thermal conductivity, good dispensing efficiency and high performance reliability.

Typical applications

- Automotive electronics (ADAS, EV, ECU)
- Telecommunications
- Devices requiring low assembly pressure
- Computer peripherals
- Between heat-generating semi conductors and a heat sink

Features and benefits

- Thermal Conductivity: 4.5 W/m-K
- 1K curable application gel for enhanced processing and excellent temperature, mechanical, and chemical stability
- Silicone-free formulation
- Optimized shear thinning rheology for enhanced 1K dispense rate
- Excellent form stability (stays in place)
- Ultra-conforming, with excellent wet-out and low assembly stress
- Suitable for low stress interface applications

Typical properties of uncured material

Dispense rate, grams/minute	45
Viscosity, Pa-s:	
Low shear rate 1.0 s ⁻¹ , DIN 53019	520
High shear rate 1,500 s ⁻¹ , ASTM D5099	100
Density, ASTM D792, g/cc	3.1
Shelf life @ 25°C, days	
<150cc cartridges and smaller packaging formats	90
≥150cc cartridges and larger packaging formats	180

Typical cure schedule

Recommended cure

24 hours @ 25°C, 50% RH

Curing (skin formation) can be accelerated with heat. Please contact your Henkel representative for application note.

The above cure profile is a guideline recommendation. These cure conditions (time and temperature) may vary based on customers' experience and specific application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

Typical properties of cured material

Physical properties

Siloxane content, ΣD4-D10, ASTM F2466, ppm	N/D
Heat capacity, ASTM E1269, J/g-°C	0.84
Hardness, Shore 00:	
2 hours @ 100 ⁽²⁾ °C	75
2 weeks @ 25°C, 50% RH	50

Electrical properties

Dielectric Strength, ASTM D149, V/mil	250
Dielectric constant, ASTM D150 @ 1,000 Hz	11
Volume resistivity, ASTM D257, ohm-meter	1×10 ⁷

(2) Henkel custom testing. See app note for details

Thermal properties

Thermal conductivity, ASTM D5470, W/(m-K)	4.5
---	-----

General information

For safe handling information on this product, consult the Material Safety Data Sheet.

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on the specifications of this product.

Configurations available

BERGQUIST® LIQUI FORM TLF 4500CGEL-SF is available with glass beads optional. BERGQUIST® LIQUI FORM TLF 4500CGEL-SF is supplied in:

Cartridges	30cc, 50cc, 150cc, 300cc, 600cc
Pail kits	0.8 gallon, 1.9 gallon (22 kg), 2.1 gallon (25 kg), 4.3 gallons

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Store in sealed, unopened containers with moisture barrier packaging as shipped from Henkel. Ensure material is at ambient conditions prior to dispensing.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\mu\text{m} / 25.4 = \text{mil}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{N/mm}^2 \times 145 = \text{psi}$
 $\text{MPa} \times 145 = \text{psi}$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Additional directions:**Disclaimer**

The information provided in this Technical data sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical data sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.



Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bergquist Company:](#)

[2652102](#) [2680904](#) [TLF4500CGEL-SF-00-240-150CC](#) [TLF4500CGEL-SF-00-240-300CC](#)