

(2,54mm) .100"

SSW SERIES

SSW-130-22-L-S-VS

SSW-116-22-G-D-VS

SMT .025" SQ POST SOCKET

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?SSW

Insulator Material:

Black LCP

Contact Material:

Phosphor Bronze

Plating:

Au or Sn over

50µ" (1,27µm) Ni

Operating Temp Range:

-55°C to +125°C with Gold

-55°C to +105°C with Tin

Contact Resistance:

10 mΩ max

Insertion Depth:

(3,68mm) .145" to

(6,35mm) .250"

Insertion Force:

(Single contact only)

3oz (0,83N) avg.

Withdrawal Force:

(Single contact only)

2.6oz (0,72N) avg.

Max Cycles:

100 with 10µ" (0,25µm) Au


RoHS Compliant:

Yes



Mates With:

TSW, MTSW, HTSW,
HMTSW, MTLW, EW, ZW,
TSS, HTSS, ZSS, TSM,
TSSH, DW, HW



CURRENT RATING	
AMBIENT TEMP	SSW mated with TSW
20°C	6.9A
40°C	6.1A
60°C	5.3A
95°C	3.5A

6 POSITIONS (2x3) POWERED

Processing:

Lead-Free Solderable:


Yes

SMT Lead Coplanarity:

(0,10mm) .004" max

Note: Other Gold plating options available. Contact Samtec.

Note: Some lengths, styles and options are non-standard, non-returnable.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[SSW-105-22-L-D-VS-N](#)