

TABLE 1						
STYLE	TAIL/OPTION	"A"	"B"	TERMINAL #1	TERMINAL #2	TERMINAL #3
-01	-RA	.103 [2.62]	.126 [3.20]	T-1S13-02-XX-2	T-1S13-03-XX-2	T-1S13-17-XX-2
-01	-FC	.139 [3.53]	.126 [3.20]	T-1S13-19-XX-2	T-1S13-22-XX-2	N/A
-01	RA W/END SHROUD	.139 [3.53]	.126 [3.20]	T-1S13-19-XX-2	T-1S13-22-XX-2	N/A
-01	*-FE	.287 [7.29]	.126 [3.20]	T-1S13-22-XX-2	T-1S13-28-XX-2	N/A
-04	-RA	.100 [2.54]	.075 [1.91]	T-1S13-20-XX-2	T-1S13-08-XX-2	N/A
-04	-FC	.150 [3.81]	.075 [1.91]	T-1S13-02-XX-2	T-1S13-03-XX-2	N/A
-04	RA W/END SHROUD	.150 [3.81]	.075 [1.91]	T-1S13-02-XX-2	T-1S13-03-XX-2	N/A
-05	-RA	.090 [2.29]	.065 [1.65]	T-1S13-07-XX-2	T-1S13-13-XX-2	N/A
-05	-FC	.160 [4.06]	.065 [1.65]	T-1S13-02-XX-2	T-1S13-03-XX-2	N/A
-05	RA W/END SHROUD	.160 [4.06]	.065 [1.65]	T-1S13-02-XX-2	T-1S13-03-XX-2	N/A




FIG 1

DIMENSIONS ARE IN INCHES			UNLESS OTHERWISE NOTED		TOLERANCES ARE:	
ONE PLACE DECIMALS ±.1[2.5]		THREE PLACE DECIMALS ±.005[.13]		ANGLES ± 2°		
TWO PLACE DECIMALS ±.01[.3]		FOUR PLACE DECIMALS ±.0020[.051]				

TITLE: 2mm x 2mm RA TERMINAL STRIP ASSEMBLY	DWG NO: TMMH-1XX-XX-XX-X-XX-XX-XXX
SHEET 1 OF 2	

PLOT SCALE: 1 = .140/ DIMSCALE: 1 = .100

TMMH-1XX-XX-XX-X-XX-XX-XXX

No OF POSITIONS
-02 THRU -50
(PER ROW)

LEAD STYLE
-01: .126 [3.20]
-04: .075 [1.91]
-05: .065 [1.65] MIN
(SEE TABLE 1)

PLATING SPECIFICATION
-L: LIGHT SELECTIVE GOLD (USE T-1S13-XX-L-2)
-F: FLASH GOLD (USE T-1S13-XX-F-2)
-S: SELECTIVE GOLD (USE T-1S13-XX-S-2)
-G: GOLD (USE T-1S13-XX-G-2)
-T: TIN (USE T-1S13-XX-T-2)
-H: HEAVY GOLD (USE T-1S13-XX-H-2)
-TM: MATTE TIN (USE T-1S13-XX-T-2)
-LM: LIGHT SELECTIVE GOLD/MATTE TIN TAIL (USE T-1S13-XX-L-2)
-FM: FLASH GOLD/MATTE TIN TAIL (USE T-1S13-XX-F-2)
-SM: SELECTIVE GOLD/MATTE TIN TAIL (USE T-1S13-XX-S-2)


POLARIZATION
SPECIFY POS -XXX TO BE OMITTED

SHROUD OPTION: (AVAILABLE ON -D ROW OPTION ONLY)
-ES: END SHROUDS (SEE FIG. 2- SHT 2, 9 POS MIN)
(NOT AVAILABLE WITH -FC TAIL OPTION)
-EP: GUIDE POST (SEE FIG. 4- SHT 2, 9 POS MIN)
(NOT AVAILABLE WITH -FC TAIL OPTION)
-EL: BOARD LOCK (SEE FIG. 3- SHT 2, 9 POS MIN)
(NOT AVAILABLE WITH -FC TAIL OPTION)

TAIL OPTION
-RA: RIGHT ANGLE
-FC: FLEX CARD (RIGHT ANGLE; -D ROW OPTION ONLY).
-FE: ELEVATED FLEX CARD (RIGHT ANGLE; -D ROW OPTION ONLY).

ROW OPTION
-D: DOUBLE
(USE TMMH-XX-D-X)
-T: TRIPLE
(USE TMMH-XX-T-X)
(AVAILABLE WITH -01 LEAD STYLE ONLY.)

* = TAIL OPTION TO BE USED ON RIGHT ANGLE ONLY




- NOTES:
1. PARTS MAY BE CUT TO POSITION.
 2. MEASURED AT BEND RADIUS, NOT AT END OF PIN.
 3. GOLD PLATING TO BE ON POST, TIN PLATING ON TAIL.
 4. Ⓢ REPRESENTS A CRITICAL DIMENSION.
 5. MINIMUM PUSHOUT FORCE: 1.0 LB.
 6. NOTE DELETED.
 7. MAX CUT FLASH TO BE .020.


PACKAGING VIEW

* ONLY TUBE POSITIONS -05 THROUGH -50


SCALE: .5x




-01-RA
PT-TMMH003-RA
TP-03




-01-FC, -01-FE
PT-TMMH003-RA
TP-03




-04-RA, -05-RA
PT-TMMH003-RA
TP-03



-04-FC, -05-FC
PT-TMMH003-RA
TP-03



-01-T-RA
PT-1-24-09F-109
TP-29



-01/04/05-RA/EX/FE-EX
PT-TMMH004-RA-EX
TP-07

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY:
PURVIS 12-17-96

TMMH-1XX-XX-XX-X-XX-XX-XXX
SHEET 1 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[TMMH-140-04-G-D-RA-ES](#)