



MTMM-125-15-T-S-500

MTMM-112-09-G-S-385


MTMM-110-02-G-S-100

2mm LOW PROFILE STRIPS MTMM SERIES

Mates with:
CLT, SQT, ESO, TLE
SMM, MMS, TCSD


Specifications: MTMM HI-TEMP

Insulator Material:
Black Liquid Crystal Polymer
Terminal Material:
Phosphor Bronze
Current Rating:
3A @ 80°C ambient
Operating Temp Range:
-65°C to +105°C with Tin;
-65°C to +125°C with Gold
Max Processing Temp:
230°C for 60 seconds
Plating:
Sn or Au over 50µ" (1,27µm) Ni




Note:
This Series is non-standard,
non-returnable.

APPLICATIONS




MTMM-1XX-02-X-X-090



MTMM-1XX-15-X-X-680

MTMM	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	POST HEIGHT	OPTION
01 thru 50							
				-G = 20µ" (0,51µm) Gold post Gold flash on tail	-S = Single Row -D = Double Row -Q = Quad Row		"XX" = Polarized Position
				-S = 30µ" (0,76µm) Gold post 150µ" (3,81µm) Tin on tail (Styles -02 thru -08 not available)			
				-T = 150µ" (3,81µm) Tin			

Specify LEAD STYLE from chart.



LEAD STYLE	OAL
-02	.255 (6.48)
-03	.302 (7.67)
-04	.323 (8.20)
-05	.377 (9.58)
-06	.397 (10.08)
-07	.458 (11.58)
-08	.476 (12.08)
-09	.535 (13.59)
-10	.555 (14.10)
-11	.594 (15.09)
-12	.614 (15.60)
-13	.673 (17.09)
-14	.751 (19.08)
-15	.830 (21.08)

-XXX' = Post Height
in inches, .005" (0,13mm) increments

Board Stacking

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[MTMM-103-07-F-D-275](#) [MTMM-110-08-F-S-325](#)