



SC, EZ SERIES

Specifications: SC, EZ

Contact:

BeCu

Shell:

Brass

-GG Plating:

30μ" (0,76 μm) Au over
50μ" (1,27 μm) Ni on contact;
10μ" (0,25 μm) Au over
50μ" (1,27 μm) Ni on shell

-GT Plating:

30μ" (0,76 μm) Au over
50μ" (1,27 μm) Ni on contact;
Sn over 50μ" (1,27 μm) Ni
on shell

-TT Plating:

Sn over 50μ" (1,27 μm)
Ni on contact; Sn over 50μ"
(1,27 μm) Ni on shell

-ST Plating:

10μ" (0,25 μm) Au over
50μ" (1,27 μm) Ni on contact;
Sn over 50μ" (1,27 μm)
Ni on shell

Current Rating:

1A per contact

Contact Resistance:

10 mΩ

Insertion Force (SC):

9oz (2,50 N) avg,
16oz (4,45 N) max

Withdrawal Force (SC):

2.5oz (0,70 N) avg,
1.5oz (0,42 N) min

Insertion Force (EZ):

2.5oz (0,70 N) avg,
5.5oz (1,53N) max

Withdrawal Force (EZ):

2.0oz (0,56 N) avg,
0.35oz (0,10 N) min

Lead DIA Accepted:

.015" to .022"
(0,38 mm to 0,56 mm) and
most IC leads

RECOMMENDED PC HOLE SIZE:

LEAD SIZE	HOLE SIZE
(0,46) .018 DIA	(0,61) .024 DIA
(0,51) .020 DIA	(0,66) .026 DIA
(0,64) .025 DIA	(0,79) .031 DIA
(0,76) .030 DIA	(0,91) .036 DIA
(0,89) .035 DIA	(1,04) .041 DIA
(1,14) .045 DIA	(1,30) .051 DIA
(1,32) .052 DIA	(1,47) .058 DIA
(0,46) .018 SQ	(0,76) .030 DIA
(0,64) .025 SQ	(1,02) .040 DIA
(1,14) .045 SQ	(1,75) .069 DIA
(0,20) .008 x (0,71) .028	(0,89) .035 DIA
(0,25) .010 x (0,51) .020	(0,71) .028 DIA
(0,41) .016 x (0,51) .020	(0,79) .031 DIA
(0,41) .016 x (0,61) .024	(0,89) .035 DIA
(0,41) .016 x (0,79) .031	(1,04) .041 DIA

Note:

Some sizes, styles and
options are non-standard,
non-returnable.

EZ-2P3-GT




SC-8P1-GG




SC-1P1-, SC-6P1-, EZ-1P1-, EZ-6P1-

Part No.	X DIA	Y ±.010	Z ±.015
SC-1P1- EZ-1P1-	(0,51) .020	(3,18) .125	(7,62) .300
SC-6P1- EZ-6P1-	(0,51) .020	(4,57) .180	(8,89) .350

Insertion Depth (SC-1P1, SC-6P1) = .95" to .145" (2,41 mm to 3,68 mm)
Plating Available (SC-1P1) = GG, GT, TT, ST
Plating Available (SC-6P1) = GG, GT




EZ-2P3-



Insertion Depth = .125" to .170" (3,18 mm to 4,32 mm)
Plating Available = GG, GT

SC-1W1-, EZ-1W1-



Part No.	Y ±.010	Z ±.015
SC-1W1-XX-1 EZ-1W1-XX-1	(12,95) .510	(17,86) .703
SC-1W1-XX-2 EZ-1W1-XX-2	(9,14) .360	(14,05) .553
SC-1W1-XX-3 EZ-1W1-XX-3	(6,60) .260	(11,51) .453

Insertion Depth = .125" to .157" (3,18 mm to 3,99 mm)
Plating Available = GG, GT, TT

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292
SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-6083 3766
SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683

SC-1P4-GG

SC-8P1-GT

SC, EZ SERIES

STANDARD, LOW PROFILE & SMT SOCKETS

Specifications:

SC-1P4

Contact:

BeCu

Shell:

Brass

-GG Plating:

20μ" (0,51 μm) Au over 50μ"

(1,27 μm) Ni on contact

-GT Plating:

20μ" (0,51 μm) Au over 50μ"

(1,27 μm) Ni on contact

Current Rating:

5A per contact

Contact Resistance:

10 mΩ

Insertion Force:

6.5oz (1,81 N) avg,

13oz (3,62 N) max

(.032" (0,81 mm) DIA probe)


Withdrawal Force:

3oz (0,83 N) avg,

2oz (0,56 N) min


(.032" (0,81 mm) DIA probe)

SC-5P1-




Insertion Depth = .080" to .150" (2,03 mm to 3,81 mm)
Lead DIA Accepted: .016" to .020" (0,41 mm to 0,51 mm)
Plating Available = GG, GT, TT

SC-3P1




Insertion Depth = .105" to .170" (2,67 mm to 4,32 mm)
Lead DIA Accepted: .015" to .020" (0,38 mm to 0,51 mm)
Plating Available = GG, GT, TT

SC-4P1-, EZ-4P1-




Insertion Depth = .080" to .105" (2,03 mm to 2,67 mm)
Lead DIA Accepted: .016" to .021" (0,41 mm to 0,53 mm)
Plating Available = GG, GT, TT

SC-1P4-



Insertion Depth = .175" to .215" (4,45 mm to 5,46 mm)
Lead DIA Accepted = .032" to .038" (0,81 mm to 0,97 mm)
Plating Available = GG, GT

SC-8P1-



Insertion Depth = .085" to .140" (2,16 mm to 3,56 mm)
Lead DIA Accepted: .016" to .020" (0,41 mm to 0,51 mm)
Plating Available = GG, GT, TT

Note:

Some sizes, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292
SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-6083 3766
SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[SC-1P1-GG](#) [SC-3P1-GT](#) [SC-1P1-GT](#) [SC-1P1-TT](#) [EZ-1W1-GT-1](#) [SC-8P1-TT](#) [EZ-1P1-GG](#) [SC-1W1-GT-1](#) [SC-1W1-GT-3](#) [SC-1W1-TT-2](#) [SC-4P1-GG](#) [SC-5P1-GG](#) [EZ-1P1-GT](#) [EZ-2P3-GG](#) [EZ-4P1-GG](#) [EZ-6P1-GG](#) [SC-1P4-GT](#)
[SC-1W1-GG-2](#)