


DO NOT
SCALE FROM
THIS PRINT



HPF-XX-XX-XX-S-XX-XX

No OF POSITIONS
-02 THRU -20 (PER ROW)



LEAD STYLE
-01: THROUGH HOLE (SEE FIG 4) ☒
-02: SURFACE MOUNT

PLATING SPECIFICATION
-T: TIN (USE C-130-XX-T)
-H: HEAVY GOLD (USE C-130-XX-H)
-TM: MATTE TIN (USE C-130-XX-T)



ROW SPECIFICATION
-S: SINGLE (USE HPF-XX-S)

POLARIZATION
-02 THRU -06, -08, -10 (SEE TABLE 2 FOR AVAILABLE COMBINATIONS) (SEE SHT 3, IN-PROCESS 1 POLARIZED FILL)
= INTERNAL USE ONLY NOT FOR SALE
* = NOT ENGINEERING APPROVED

OPTION (STYLE -02 ONLY)
-LC: LOCKING CLIP (USE LC-05-TM) (SEE SHT 2, FIG 2) (SEE NOTE 9)
* -A: ALIGNMENT PIN (SEE SHT 2, FIG 2) (USE HPF-XX-S-A)
-K: POLYIMIDE FILM PAD (SEE SHT 2, FIG 3) (USE K-DOT-.256-.375-.005)
-TR: TAPE & REEL (14 POS MAX. -02 LEAD STYLE ONLY)



SECTION "A"-"A"



DETAIL 'B'




TABLE 2	
FINISHED GOODS	SUBASSEMBLY
HPF-02-01-T-S	HPF-20-01-T-S-02
HPF-02-02-T-S-XX	HPF-20-02-T-S-02
HPF-03-01-T-S	HPF-20-01-T-S-03
HPF-03-02-T-S-XX	HPF-20-02-T-S-03
HPF-04-01-T-S	HPF-20-01-T-S-04
HPF-04-02-T-S-XX	HPF-20-02-T-S-04
HPF-04-02-H-S-XX	HPF-20-02-H-S-04
HPF-05-02-T-S-XX	HPF-20-02-T-S-05
HPF-06-01-T-S	HPF-20-01-T-S-06
HPF-08-01-T-S	HPF-20-01-T-S-08
HPF-10-01-T-S	HPF-20-01-T-S-10
HPF-08-02-T-S	HPF-20-02-T-S-08
ALL REMAINING CONFIGURATIONS	HPF-20-01-T-S

- NOTES:
1. Ⓢ REPRESENTS A CRITICAL DIMENSION.
2. COPLANARITY TO BE WITHIN :
2-10 POS: .006
11-20 POS: .008
3. BURR ALLOWANCE: .0015 MAX.
4. MAXIMUM CUT FLASH: .020.
5. MINIMUM PUSHOUT FORCE: 1.0 LB.
6. ALL PARTS TO BE TUBE PACKAGED.
7. OPEN PART OF CONTACT FILLED TOWARDS #1 PIN INDICATOR.
8. MINIMUM WALL THICKNESS TO BE .010.
9. DUE TO THE HIGH AMOUNT OF INSERTION FORCE NEEDED, THE -LC OPTION IS NOT COMPATIBLE WITH AUTO PLACEMENT, SAMTEC RECOMMENDS MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH THE -LC OPTION.

FIG 1
HPF-XX-02-XX-S-XX

TABLE 1		
LEAD STYLE	PLATING	
	-T	-H
01	02, 03, 04, 06, 08	N/A
02	02, 03, 04, 05	04

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:
DECIMALS ANGLES
.XX: ±.01 2°
.XXX: ±.005
.XXXX: ±.0020

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.


MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 1.5:1
MATERIAL: VECTRA E130i
COLOR: BLACK
CONTACT: BeCu, 174HT

DESCRIPTION: .200 HI POWER SOCKET ASSEMBLY

DWG. NO. **HPF-XX-XX-XX-S-XX-XX**

BY: DEAN P 01/04/1999 SHEET 1 OF 3

samtec
520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322



NOTE: "M" = USED MEASURED DIMENSION (REF)
 "P" = $\{("M" - .256 [6.50]) / 2\} \pm .020 [.51]$

FIG 3
 -K: POLYIMIDE FILM PAD OPTION
 (SHOWN: HPF-10-02-X-S-K)





FIG 2
 -LC & -A OPTIONS
 (-LC & -A OPTION ONLY AVAILABLE ON -02 LEAD STYLE)
 (SAME AS FIG 1 EXCEPT WHERE SHOWN)

PACKAGING VIEW



TUBE: PT-1-24-02-44
 PLUG: TP-09

SEE NOTES 6 & 7 FOR ADDITIONAL PACKAGING INSTRUCTIONS

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
 CONFIDENTIAL AND PROPRIETARY TO
 SAMTEC, INC. AND SHALL NOT BE REPRODUCED
 OR TRANSFERRED TO OTHER DOCUMENTS OR
 DISCLOSED TO OTHERS OR USED FOR ANY
 PURPOSE OTHER THAN THAT WHICH IT WAS
 OBTAINED WITHOUT THE EXPRESSED WRITTEN
 CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1


samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
 PHONE: 812-944-6733 FAX: 812-948-5047
 e-Mail: info@SAMTEC.com code: 55322








DESCRIPTION:
 .200 HI POWER SOCKET ASSEMBLY

DWG. NO.
HPF-XX-XX-XX-S-XX-XX

BY: DEAN P 01/04/1999 SHEET 2 OF 3

IN-PROCESS 1
FILL C-130-XX-X**STANDARD FILL****POLARIZED OPTION**

■ = DENOTES EMPTY POSITION

-02 POLARIZATION
(7 FINISHED GOODS)
HPF-20-02-XX-S-02 SHOWN**-03 POLARIZATION**
(5 FINISHED GOODS)
HPF-20-02-XX-S-03 SHOWN**-04 POLARIZATION**
(4 FINISHED GOODS)
HPF-20-02-XX-S-04 SHOWN**-05 POLARIZATION**
(3 FINISHED GOODS)
HPF-20-02-XX-S-05 SHOWN**-06 POLARIZATION**
(3 FINISHED GOODS)
HPF-20-02-XX-S-06 SHOWN**-08 POLARIZATION**
(2 FINISHED GOODS)
HPF-20-02-XX-S-08 SHOWN**-10 POLARIZATION**
(1 FINISHED GOODS)
HPF-20-02-XX-S-10 SHOWN**PROPRIETARY NOTE**

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

SHEET SCALE: 1.5:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
.200 HI POWER SOCKET ASSEMBLYDWG. NO.
HPF-XX-XX-XX-S-XX-XX

BY: DEAN P 01/04/1999 SHEET 3 OF 3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[HPF-08-02-H-S](#)